


HARCO PVC C-900 GASKETED FITTINGS

DESIGN DATA


IPS x C-900 ADAPTER (BxS)



(Molded fitting shown)

SIZE	PART No.	STYLE	A	L	WT. (approx.)
4	339-040	Molded	2.7	7.0	2.4
6	339-060	Molded	3.7	8.6	5.0
8	339-080	Fab			28.0


TEE



(Molded fitting shown)

SIZE	PART No.	STYLE	A	L	WT. (approx.)
4x4	312-0404	Molded	10.1	14.2	6.7
6x4	312-0604	Molded	12.3	15.4	11.5
6x6	312-0606	Molded	13.0	17.4	14.5
8x4	312-0804	Molded	14.9	16.3	19.0
8x6	312-0806	Molded	15.4	18.5	23.0
8x8	312-0808	Molded	16.0	20.9	26.0
10x4	312-1004	Fab	22.0	29.3	37
10x6	312-1006	Fab	23.0	30.3	40
10x8	312-1008	Fab	22.5	33.0	43
10x10	312-1010	Fab	22.5	35.5	68
12x4	312-1204	Fab	24.0	32.5	56
12x6	312-1206	Fab	25.0	33.5	60
12x8	312-1208	Fab	26.5	36.5	65
12x10	312-1210	Fab	26.0	38.5	72
12x12	312-1212	Fab	26.0	40.5	99

IPS x C-900 (BxB) ADAPTER



Non-pressure

(Molded fitting shown)

SIZE	PART No.	STYLE	A	L	WT. (approx.)
4	338-040	Molded	6.3	8.9	2.9
6	338-060	Molded	8.3	10.0	6.0
8	338-080	Molded	11.1	11.3	12.5

NOTES:


- All lay lengths & weights are approximate and are subject to change without notice.
- Fabricated fitting configurations may vary.

STYLE LEGEND:

Molded - Molded fittings are Pressure Class 150 unless otherwise noted.

Fab ----- Fabricated fittings are made from sections of C-900 pipe and are not pressure rated.

TAPPED PLUG (NPT Thread)




Use poured concrete thrust blocks only.

(Molded fitting shown)

SIZE	PART No.	STYLE	A	L	WT. (approx.)
4x ³ / ₄	345-403	Molded	5.3	4.5	1.2
4x1	345-404	Molded	5.3	4.5	1.2
4x1 ¹ / ₂	345-406	Molded	5.3	4.5	1.2
4x2	345-408	Molded	5.3	4.5	1.2
6x ³ / ₄	345-603	Molded	7.4	6.4	3.1
6x1	345-604	Molded	7.4	6.4	3.1
6x1 ¹ / ₂	345-606	Molded	7.4	6.4	3.1
6x2	345-608	Molded	7.4	6.4	3.1
8x ³ / ₄	345-803	Molded	9.5	7.3	6.2
8x1	345-804	Molded	9.5	7.3	6.2
8x1 ¹ / ₂	345-806	Molded	9.5	7.3	6.2
8x2	345-808	Molded	9.5	7.3	6.2

PLUG




Use poured concrete thrust blocks only.

(Molded fitting shown)

SIZE	PART No.	STYLE	A	L	WT.(approx.)
4	344-040	Molded	5.3	4.5	1.2
6	344-060	Molded	7.4	6.4	3.1
8	344-080	Molded	9.5	7.3	6.2
10	344-100	Fab	12.3	14.0	21.0
12	344-120	Fab	14.5	14.0	32.0

TRANSITION GASKET C-900 x IPS



Non-pressure

(Molded fitting shown)

SIZE	PART No.	STYLE	WT. (approx.)
4	396-040	Molded	0.3
6	396-060	Molded	0.5
8	396-080	Molded	0.7

CALL FOR OTHER SIZES, CONFIGURATIONS & GASKET MATERIALS.



THE HARRINGTON CORPORATION

P.O. BOX 10335 • LYNCHBURG VIRGINIA 24506 • PLANT 3721 COHEN PLACE • LYNCHBURG VIRGINIA 24501
PHONE: (434) 845-7094 • FAX: (434) 845-8562 • E-mail: sales@harcofittings.com