



## LGR 6000Li

Get the quietest and best-performing compact, easy-transport iSeries dehumidifier your techs will always choose first. The LGR 6000 is perfectly sized for everyday jobs, and it's Dri-Eaz rugged, ready to withstand years of heavy use. It's also amazingly quiet yet removes more water than any other competitive unit in its class.



# FEATURES

- Extreme Dewpoint Technology™ (EDT) delivers the fastest response to changing conditions.
- Easily ductable using built-in snap-ring mount on air outlet.
- Time-saving i-Series control panel displays GPP, inlet and outlet temp and RH plus maintenance prompts.
- Uses all-in-one 4-PRO filter: electrostatic mesh filtration with antimicrobial treatment and odor-fighting carbon.
- Unique spill-proof pump basin keeps in any water left after the final purge cycle.
- Fast 4-bolt access for easy cleaning and preventive maintenance.
- Practically indestructible, rolls up stairs easily and stacks for storage.

# SIZES ▪ OPTIONS

- **103614 (F600):** One unit

# SPECIFICATIONS

- **Water removal AHAM (80°F/60% RH):** 100 pts. | 47.3 liters / day
- **Water removal Saturation (90°F/90% RH):** 204 pts. | 96.5 liters / day
- **Water removal LGR (80°F/20% RH):** 40% higher than competitive units
- **Process air (max.):** 320 CFM
- **Dimensions (H × D × W):** 32.1 × 19.8 × 20.0 in. | 81.5 × 50.3 × 50.8 cm
- **Weight:** 103 lbs. | 46.7 kg
- **Amps:** 6.6A
- **Volts:** 115V
- **Frequency:** 60Hz
- **Power:** 759W
- **Operating range:** 33°F–100°F | 1°C–38°C
- **Noise level (avg.):** 53 dB
- **Drain hose:** 40 ft. | 12.2 m
- **Power cord:** 25 ft. | 7.6 m
- **Housing:** Rotomolded polyethylene
- **Air filter:** 4-PRO filter
- **Safety:** ETL listed CSA 22.2 no. 92
- **Xactimate:** WTRDHM>L