2500 SPECIFICATIONS





Valves 2 in.—66in. shall be resilient wedge type rated for 250 psig cold water working pressure. All ferrous components shall be ductile iron. All NRS valves, in applicable configurations, 2-1/2in.—24in. in diameter shall be Listed by Underwriters Laboratories, Inc. All OS&Y valves in applicable configurations, 3in.—24in. in diameter shall be Listed by Underwriters Laboratories, Inc. Valves 3 in—54 in. shall be in full compliance with ANSI/AWWA C515. The words "DI" or "Ductile Iron" shall be cast on the valve. The wedge shall be ductile iron encapsulated with EPDM rubber and provided with male type guides and polymer guide covers. Bolting shall be Type 304 stainless steel and shall be provided with hexagonal heads with dimensions conforming to ANSI B18.2.1. Metric size, socket head cap screws therefore are not allowed.

- Operating nut shall be constructed of ductile iron and shall have four flats at stem connection to assure even input torque to the stem.
- All gaskets shall be pressure energized O-rings.
- Stem shall be sealed by three O-rings. The top two O-rings shall be replaceable with valve fully open and while subject to full rated working pressure. O-rings set in a cartridge shall not be allowed.
- Valve shall have thrust washers located with (1) above and (1) below the thrust collar to assure trouble-free operation of the valve.
- All internal and external surfaces of the valve body and bonnet shall have a fusion-bonded epoxy coating, complying with ANSI/AWWA C550, applied electrostatically prior to assembly.
- Valves shall be certified to NSF/ANSI Standard 61 and NSF/ANSI 372.
- Valves shall be AMERICAN Flow Control's Series 2500 or 2500-1 Resilient Wedge Gate Valve.

AMERICAN Flow Control Submittal Information

14" - 18" SERIES 2500 RESILIENT WEDGE GATE VALVE NRS TAPPING x MJ ENDS WITH BEVEL GEAR ACTUATOR (TAP X MJ)





91-21395

Size	14"	16"	18"
Α	35.19	39.75	43.00
В	14.94	16.94	18.94
С	.25	.25	.25
D	7.50	8.00	8.50
E	10.25	10.44	11.44
F	3.50	3.50	3.50
G	14.19	16.19	18.13
Н	7.63	7.56	8.43
J	26.00	28.25	32.00
K	13.50	15.13	15.00
Т	18.75	21.25	22.75
U	18.75	21.00	23.25
X	12 - 1.13	16 - 1.13	16 - 1.25
Y	1088	1288	1288
Turns to Open	88	100	112
Tap Size	3/8 NPT	3/8 NPT	3/8 NPT
Maxium Cutter Diameter	14	16	18
Weight	806 lbs.	977 lbs.	1256 lbs.




THE RIGHT WAY

AMERICAN Flow Control P.O. Box 2727 Birmingham, Al. 35202-2727 Phone: 800-326-8051 Fax: 800-610-3569 Email: afcsales@american-usa.co Waterous Company 125 Hardman Avenue South South St. Paul, Mn. 55075-1191 Phone: 888-266-3686 Fax: 800-601-2809 Email: afcsales@american-usa.com

WWW.AMERICAN-USA.COM

Page 1 of 2 TV11003 Issued: 9/27/2019



Construction shown is typical of the 16-inch size with mechanical joint end connections and is illustrative only. Construction of other sizes and end connection types vary slightly. See elsewhere on this drawing for specific details.

D-f N-	D	N4-4:I	
Ref. No.	Description	Material	
1-K	Key for operating nut	Steel	
2-K	Operating Nut	Ductile Iron ASTM A536	
3	O-Ring	Rubber	
4	Upper Thrust Washer	Delrin	
5	Stuffing Box Gasket	Rubber O-Ring	
6	O-Ring	Rubber	
7	Stuffing Box	Ductile Iron ASTM A536	
8	Bonnet	Ductile Iron ASTM A536	
9	Hex Head Bolt	304 Stainless Steel	
10	Throat Flange Gasket	Rubber	
11	Valve Body	Ductile Iron ASTM A536	
12	Stem	Manganese Bronze, ASTM B763, UNS C86700	
13	Wedge Nut	Silicon Bronze, ASTM B584, UNS C87600	
14	Resilient Wedge	EPDM Rubber Encapsulated Ductile Iron ASTM A536	
15	Wedge Cover	Acetal Polymer	
16	Wedge Cover Pin	Acetal Polymer	
17	Hex Head Bolt	304 Stainless Steel	
18	Hex Nut	304 Stainless Steel	
19	Hex Nut	304 Stainless Steel	
20	Pipe Plug	Stainless Steel	
21	Lower Thrust Washer	Delrin	
22	Stud	304 Stainless Steel	
23	Hex Nut	304 Stainless Steel	
25	Key	Hardened Steel	
27	Bevel Gear Actuator	Rotork IB-5 (2:1)	
29	Actuator Gasket	Rubber O-Ring	
30	Hex Head Bolt	Zinc Plated Steel	
31	Washer	Steel	
60-K	Pin for Operating Nut	Stainless Steel	

OPTIONAL MATERIALS ARE AS FOLLOWS

BOLTS and NUTS: 316 Stainless Steel

STEM: Cast NDZ-S Bronze, ASTM B763, UNS C99500

STEM: 304 Stainless Steel STEM: 316 Stainless Steel

Open Direction Left(C.C.W.) Right(C.W.)

NOTES:

- Bolt patterns of class 125 flanged ends are in accordance with ANSI/AWWA C110/A21.10 (ASME B16.1 class 125).
- 2. Mechanical joint ends are in accordance with ANSI/AWWA C111/A21.53 and MSS SP-113.
- 3. Raised alignment ring dimensions of flanged ends on tapping valves are in accordance with MSS SP-60.
- 4. Fusion -bonded epoxy coated in accordance with AWWA C550.
- 5. Certified to NSF/ANSI 61 & 372.
- 6. Meets requirements of AWWA C515 with rated working pressure of 250 psig.



THE RIGHT WAY

AMERICAN Flow Control P.O. Box 2727 Birmingham, Al. 35202-2727 Phone: 800-326-8051 Fax: 800-610-3569 Email: afcsales@american-usa.cor Waterous Company 125 Hardman Avenue South South St. Paul, Mn. 55075-1191 Phone: 888-266-3686 Fax: 800-601-2809 Email: afcsales@american-usa.com

WWW.AMERICAN_USA.COM

Page 2 of 2 TV11003 Issued: 9/27/2019