





PROTECTION





Mirafi[®] 135N

xtile composed of polypropylene fibers

Mirafi[®] 135N is a needlepunched nonwoven geotextile composed of polypropylene fibers, which are formed into a stable network such that the fibers retain their relative position. Mirafi[®] 135N is inert to biological degradation and resists naturally encountered chemicals, alkalis, and acids.

TenCate Geosynthetics Americas Laboratories are accredited by Geosynthetic Accreditation Institute – Laboratory Accreditation Program (<u>GAI-LAP</u>).

Mechanical Properties	Test Method	Unit	Minimum Average Roll Value	
•			MD	CD
Grab Tensile Strength	ASTM D4632	lbs (N)	80 (356)	80 (356)
Grab Tensile Elongation	ASTM D4632	%	50	50
Trapezoid Tear Strength	ASTM D4533	lbs (N)	30 (134)	30 (134)
CBR Puncture Strength	ASTM D6241	lbs (N)	175 (779)	
			Maximum O	pening Size
Apparent Opening Size (AOS)	ASTM D4751	U.S. Sieve (mm)	50 (0.30)	
			Minimum F	Roll Value
Permittivity	ASTM D4491	sec ⁻¹	2.1	
Flow Rate	ASTM D4491	gal/min/ft2 (l/min/m2)	155 (6315)	
	-		Minimum T	est Value
UV Resistance (at 500 hours)	ASTM D4355	% strength retained	70	

Physical Properties	Unit	Roll Sizes		
Roll Dimensions (width x length)	ft (m)	12.5 x 360 (3.8 x 110)	15 x 360 (4.5 x 110)	
Roll Area	yd² (m²)	500 (418)	600 (502)	

Disclaimer: TenCate assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. TenCate disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, materials, or information furnished herewith. This document should not be construed as engineering advice.

Mirafi® is a registered trademark of Nicolon Corporation.

Copyright © 2015 Nicolon Corporation. All Rights Reserved.



