#### **METAL CUTTING CIRCULAR SAW BLADES**

Diameter	No. of Teeth	Application	Hook Angle	Kerf Thickness (mm)	Tooth Grind	Part No.
5-3/8"	30	Ferrous Metal	0°	.063"	ATB	48-40-4070
5-3/8"	50	Non-Ferrous Metal	0°	.063"	ATB	48-40-4075
5-7/8"	90	Stainless Steel	0°	.086"	MATB+FTG	48-40-4080
6-1/2"	48	Ferrous Metal	0°	.063"	MATB	48-40-4015
6-1/2"	60	Non-Ferrous Metal	3°	.075"	MATB	48-40-4005
6-7/8"	52	Non-Ferrous Metal	10°	.071"	MATB	48-40-4006
6-7/8"	36	Ferrous Metal	0°	.065"	MATB	48-40-4016
7-1/4"	48	Non-Ferrous Metal	5°	.071"	TCG	48-40-4132
7-1/4"	-	Ferrous Metal	-	.063"	-	48-40-4140
8"	42	Ferrous Metal 3/32" and thicker	0°	.073"	MATB	48-40-4515
8"	50	Ferrous Metal 3/32" and thinner	0°	.073"	MATB	48-40-4520
8"	60	Aluminum, 1/4" - 2" Bar Stock, 1/4" - 1-1/4" Flat Stock	10°	.073"	TCG	48-40-4530
8"	60	Aluminum, 1/4" and under Bar and Flat Stock	0°	.073"	TCG	48-40-4540
10"	80	Non-Ferrous Metal, Plastic	-5°	.102"	TCG	48-40-4168
14"	72	Ferrous Metal	0°	.086"	ATB	48-40-4505
14"	90	Stainless Steel	0°	.086"	MATB+FTG	48-40-4510

# **CIRCULAR SAW ACCESSORIES**

### **CIRCULAR SAW ACCESSORIES**

Description	Part No.
Dust Collection Kit	49-22-8105
Extension Kit	49-22-8108
Hold Down Bar Kit	49-22-8100
Mid-Way Fence Kit	49-22-8110

Description	Part No.
Quick Stop Gauging Kit	49-22-8102
Riser Support	48-08-0360
Tool Stand	48-08-0350

Description	Part No.
Wedge Clamps	48-08-0380
Wheel Kit	49-22-8106
Work Center	48-08-0450

## **HOLE SAWS**

### **HOLE SAW SELECTION GUIDE**

Identify the material to be cut in the columns below

Choose the appropriate product RECOMMENDED or ACCEPTABLE

		STAINLESS STEEL	METAL	ALUMINUM & OTHER NON-FERROUS METALS	DUCT	CAST IRON	WOOD WITH NAILS	CEILING Tile	PLASTER/ Drywall	PVC & Plastics	CLEAN WOOD	FIBERGLASS	CEMENT BOARD	TILE	BRICK & BLOCK	GRANITE
			1				THE STATE OF	7	THE	4	NO.				W W	
	CARBIDE TEETH															
	BI-METAL															
S	CARBIDE GRIT															
HOLE SAWS	DIAMOND GRIT															
웊	RECESSED LIGHT															
	ADJUSTABLE HOLE CUTTER															
	IMPACT HOLE SAWS															
впѕ	THUNDERBOLT®															
PILOT BITS	CARBIDE TIPPED															

## **HOLE DOZER™ WITH CARBIDE TEETH HOLE SAWS**

### **OVERVIEW**

MILWAUKEE® HOLE DOZER™ with Carbide Teeth Hole Saws provide 50X life in extreme multi-material cutting applications when compared to bi-metal hole saws. Built utilizing a tough carbide grade combined with a durable 4 TPI design, yielding the best tooth durability and life in stainless steel, abrasive materials and fastener-embedded wood. Cutting depth is 1.62", allowing clearance to handle cuts in all materials. With a Thermoset Coating to reduce friction and drag during cutting, users benefit from faster cutting and increased cordless efficiency. Slug removal is made easy with the PLUG JACK™. The PLUG JACK™ enhances user productivity by providing best access and leverage to remove material slugs. HOLE DOZER™ with Carbide Teeth hole saws are made in the USA.

### **FEATURES**

- 50X Life in extreme multi-material applications (Stainless Steel, Abrasives, Fastener Embedded Wood)
- 4 TPI Design gives best durability and life in extreme multi-material applications
- Thermoset Coating reduces friction and drag, increasing overall speed and cordless efficiencies



