RESI-PAC[™]



A RESI-RISER[™] completely enclosed in a metal cabinet and finished with a white powder coating.



DIMENSIONS

	DESCRIPTION	1"	1-1/4"	1-1/2"	2"
A	Height	18-1/4"	18-1/4"	ТВА	ТВА
В	Width	14"	14"	14"	14"
C	Depth	4-5/8"	4-5/8"	4-5/8"	4-5/8"
_	Drain Size	1/2"	1"	1"	1"

MODEL NUMBERS

PART #	WITH INLINE CHECK VALVE	WITH SWING CHECK VALVE	WITH PRESSURE RELIEF VALVE	WITH CPVC ADAPTERS
1"				
RIRP100-IRR4-TD	х		х	х
RIRP100-SRR4-TD		х	х	х
1-1/4"				
RIRP125-IRR4-TD	х		х	х
RIRP125-SRR4-TD		х	х	х

FEATURES & BENEFITS

- Eliminates the need for an access panel as well as the return trip to install the access panel
- Dry wall extends up to the cabinet, giving a clean finish
- Resi-Riser is protected throughout the construction phase and after completion
- Includes built-in head box, eliminating the need for a red head box installed on the exterior of the wall
- Door interior includes a record of system inspections and a hydraulic calc plate
- Can be recessed in a 2" x 4" wall or mounted on the surface
- White powder-coat finish blends well with most finishes or may be painted over
- Comes with all necessary openings for electrical and piping penetration
- Key lock and handle are optional
- Includes: Screwdriver lock

INLINE SPRING CHECK VALVE

COMPONENTS

	DESCRIPTION	MATERIAL
1	Nut	Stainless Steel
2	Spring Cap	Stainless Steel
3	Spring	Stainless Steel
4	O-Ring Seat	Rubber
5	Clapper, Spring-Loaded	Brass
6	Body	Brass
7	Washer	Teflon™

DIMENSIONS

	1"	1-1/4"	1-1/2"	2"
A	1-9/16"	2"	2-1/8"	2-3/4"
В	3-1/4"	3-5/8"	4"	5"
C	1-3/16"	1-9/16"	1-3/4"	2-3/16"

