

### SAFETY DATA SHEET

## **REED Tapping Compound**

Issuing Date 09-09-2016

Revision Date 08-03-2020

#### 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product Identifier Product Name	REED Tapping Compound
Other means of identification Synonyms	No information available

#### Recommended use of the chemical and restrictions on use

Identified uses	Lubricant
-----------------	-----------

Uses advised against Consumer use

#### Details of the supplier of the Safety Data Sheet

#### Manufacturer/Supplier:

Reed Manufacturing Company 1425 West Eighth Street - PO Box 1321 Erie, Pennsylvania 16512-1321 USA (800) 666-3691 (814) 452-3691 Email: <u>reedsales@reedmfgco.com</u>

Made in cooperation with Lubrication Engineers Inc. 1919 E. Tulsa Wichita, KS 67216

#### **Emergency Telephone Number:**

ChemTel Inc. (800) 255-3924 (US/Canada/Puerto Rico) +1 (813) 248-0585 (International)

Issuing Date 09-09-2016

Revision Date 08-03-2020

#### 2. HAZARDS IDENTIFICATION

#### **Classification**

#### **OSHA Regulatory Status**

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

#### Label Elements

Emergency Overview			
Signal Word			
None			
	Hazard Statements		
	None		
Appearance Beige	Physical state Paste	Odor Hydrocarbon-like	
Precautionary Statements – Prevention	None		
Response	None		
Eyes	None		
Skin	None		
Inhalation	None		
Ingestion	None		
Fire	None		
Spill	None		
Storage	None		
Disposal	None		
Hazards not otherwise classified (HNOC)	None		
<ul> <li>MAY BE HARMFUL IF SWALLOWED</li> <li>Toxic to aquatic life with long lasting effects</li> <li>Toxic to aquatic life</li> </ul>			

#### **3. COMPOSITION/INFORMATION ON INGREDIENTS**

The producer of REED Tapping Compound declares that it contains less than 3% DMSO extractable material by IP-346.

Issuing Date 09-09-2016

Revision Date 08-03-2020

4. FIRST AID MEASURES		
First Aid Measures		
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.	
Skin Contact	Wash off immediately with soap and plenty of water removing all contaminated clothes and shoes. Consult a physician if necessary.	
Inhalation	Consult a physician. If not breathing, give artificial respiration.	
Ingestion	Do NOT induce vomiting. Drink plenty of water.	
Most important symptoms and effe	ects, both acute and delayed	
Symptoms	None known.	
Indication of any immediate medica	al attention and special treatment needed	
Notes to Physician	Treat symptomatically.	
5. FIRE-FIGHTING MEASURE	S	
Flash Point	252° C / 485.6° F	
Suitable Extinguishing Media	Water spray, Carbon dioxide (CO2), Foam, Dry chemical	
Unsuitable Extinguishing Media	Do not use a solid water stream as it may scatter and spread fire.	
Specific Hazards Arising from the Chemical	Thermal decomposition can lead to release of irritating gases and vapors.	
<u>Explosion Data</u> Sensitivity to Mechanical Impac Sensitivity to Static Discharge	<b>ct</b> Not impact sensitive. May be ignited by friction, heat, sparks or flames.	
Protective Equipment and Precautions for Firefighters	Wear self-contained breathing apparatus and protective suit.	
NFPA Health haz	ard 1 Flammability 1 Stability 1	
6. ACCIDENTAL RELEASE N	IEASURES	
Personal precautions, protective e	guipment and emergency procedures	
Personal Precautions	Use personal protective equipment. Do not touch or walk through spilled material. Remove all sources of ignition.	
Environmental Precautions		
Environmental Precautions	Beware of vapors accumulating to form explosive concentrations. Vapors can accumulate in low areas. Prevent further leakage or spillage if safe to do so. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.	
	Version-EN0	

Issuing Date 09-09-2016	Revision Date 08-03-2020
Methods and material for contai	nment and cleaning up
Methods for Containment	Prevent further leakage or spillage if safe to do so. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container.
Methods for Cleaning up	Use personal protective equipment. Contain the spill. Soak up with inert absorbent material Pick up and transfer to properly labeled containers. Clean contaminated surface thoroughly
7. HANDLING AND STORA	AGE
Precautions for safe handling	
Advice on safe handling	Handle in accordance with good industrial hygiene and safety practice. When using, do not eat, drink or smoke. For personal protection see section 8.
Conditions for safe storage, incl	luding any incompatibilities
Technical measures/Storage conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in a bunded area
Incompatible products.	Strong oxidizing agents. Strong acids. Strong bases.
8. EXPOSURE CONTROLS	PERSONAL PROTECTION
Control parameters	
Exposure Guidelines	This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.
Appropriate engineering control	<u>Is</u>
Engineering Measures	Showers Eyewash stations Ventilation systems
Individual protection measures,	such as personal protective equipment
Eye/Face Protection	Eye protection not needed during typical product use conditions. Wear eye protection as appropriate when handling the bulk formulation.
Skin and Body Protection	Long sleeved clothing. Protective gloves.
Respiratory Protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice. When using, do not eat, drink or smoke. Remove and wash contaminated clothing before re-use.
9. PHYSICAL AND CHEMI	

#### 9.1. Information on basic physical and chemical properties

Physical state	
Appearance	
Odor	
Odor threshold	

Paste Beige Hydrocarbon-like no information available

Issuing Date 09-09-2016

Revision Date 08-03-2020

	6 - 8
pH	no data available
Melting point/freezing point	no data available
Boiling Point/Range	$252 \degree C / 485.6 \degree F$
Flash Point	no data available
Upper Flammability Limit	no data available
Lower Flammability Limit	No data available
Vapor Pressure	< 1 (Air = 1)
Vapor Density	0.95
Specific Gravity	negligible
Water solubility	no data available
Partition Coefficient: n-octanol/water	no data available
Autoignition Temperature	no data available
Decomposition Temperature	no data available
Viscosity, kinematic	no data available

#### **10. STABILITY AND REACTIVITY**

<u>Reactivity</u>	No information available
Chemical stability	Stable under recommended storage conditions.
Possibility of Hazardous Reactions	None under normal processing.
Conditions to Avoid	Heat, flames and sparks. Contact with other chemicals
Incompatible Materials	Strong oxidizing agents. Strong acids. Strong bases.

Hazardous Decomposition Products Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke)

#### **11. TOXICOLOGICAL INFORMATION**

#### Information on likely routes of exposure

Product Information	Product does not present an acute toxicity hazard based on known or supplied information	
Inhalation	May cause irritation of respiratory tract.	
Eye Contact	Contact with eyes may cause irritation.	
Skin Contact	May cause irritation.	
Ingestion	There is no data available for this product.	
Component Information	No information available	
Information on toxicological effects		
Symptoms	No information available.	

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

The producer of REED Tapping Compound declares that it contains less than 3% DMSO extractable material by IP-346.

Issuing Date 09-09-2016	Revision Date 08-03-2020		
Sensitization	No information available.		
Mutagenic Effects	No information available.		
Carcinogenicity	No information available.		
Reproductive toxicity	No information available.		
Target Organ Effects	Target Organ Effects         Respiratory system, Eyes, Skin.		
Numerical measures of toxicity -	Product Information		
The following values are calculated based on chapter 3.1 of the GHS document .ATEmix (oral)5000 mg/kgATEmix (dermal)20000 mg/kg			
12. ECOLOGICAL INFORMATION			
<u>Ecotoxicity</u>	None known		
Persistence and Degradability	<b>bility</b> No information available.		
<b>Bioaccumulation</b>	No information available.		
Mobility	The product is insoluble and floats on water.		

Other Adverse Effects	No information available
Other Auverse Lifects	NO INICITIALION AVAILADIE

### **13. DISPOSAL CONSIDERATIONS**

Waste treatment methods	
Waste Disposal Methods	Should not be released into the environment. Dispose of in accordance with local regulations.
Contaminated Packaging	Do not re-use empty containers. Empty containers should be taken to an approved waste handling site for recycling or disposal.

### 14. TRANSPORT INFORMATION

DOT

Not regulated

Issuing Date 09-09-2016

Revision Date 08-03-2020

#### **15. REGULATORY INFORMATION**

International Inventories	
TSCA	Complies
DSL/NDSL	Complies
NDSL	Complies
EINECS	Not determined
ELINCS	Not determined
ENCS	Complies
IECSC	Complies
KECL	Not determined
PICCS	Complies
AICS	Complies

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
 EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
 ENCS - Japan Existing and New Chemical Substances
 IECSC - China Inventory of Existing Chemical Substances
 KECL - Korean Existing and Evaluated Chemical Substances
 PICCS - Philippines Inventory of Chemicals and Chemical Substances
 Australian Inventory of Chemical Substances

#### **U.S. Federal Regulations**

#### SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

#### SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

#### **Clean Water Act**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

#### **CERCLA**

This material does not contain any components with a CERCLA RQ.

#### U.S. State Regulations

#### California Proposition 65

This product does not contain any Proposition 65 chemicals.

#### U.S. State Right-to-Know Regulations

This product does not contain any substances regulated by state right-to-know regulations.

NFPA Health hazard 1 Flammability 1 Stability 1

Issuing Date 09-09-2016

Revision Date 08-03-2020

#### **16. OTHER INFORMATION**

Issuing Date Revision Date Reason for revision 09-09-2016 08-03-2020 Updated section 2, 5, 6, 9, 16

#### **Disclaimer**

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

SDS is available at <u>www.reedmfgco.com</u>.

**End of Safety Data Sheet**