



Mueller® A-3 Machine Saddles

Mueller A-3 Machine Saddles*

Pipe O.D. range**		Kind and type of pipe***				Saddle Part Number
		Cast iron, ductile iron, cast iron O.D. PCV	Steel	A-C		
in.	mm			Class 100	Class 150	
6.56-7.13	167.0-181.0	6"	-	-	-	75908
6.94-7.50	176.0-191.0	-	6"	6"	6"	46704
8.00-8.63	203.0-219.0	-	8"	-	-	45384
8.88-9.38	226.0-238.0	8"	-	-	-	75909
9.19-9.63	233.0-245.0	-	-	8"	8"	43293
10.13-11.25	257.0-286.0	10"	10"	10"	-	75910
11.88-13.50	302.0-342.0	12"	-	-	10"	40236
13.38-14.00	340.0-356.0	-	14"	12"	-	43364
14.13-16.25	359.0-413.0	14"	16"	14"	12"	75911
16.00-18.75	406.0-476.0	16"	18"	16"	14"	40238
18.13-22.75	461.578.0	18"/20"	20"	-	16"	40240
22.50-27.50	572.0-699.0	24"	24"	-	-	40241
27.75-35.00	654.0-889.0	30"	30"	-	-	75912
34.00-58.00	864.0-1470.0	36"/42"/48"	36"	-	-	75914

* Use pipe O.D. range as a guide to select saddles for pipe not listed in chart.

** These saddles are suitable for pipe meeting the following specifications:

- Centrifugally cast pipe, classes 50-250 ANSI/AWWA C106/A21.6; ANSI/AWWA C108/A21.8; Federal specification WW-P-421.
- Pit cast pipe, classes 50-250 ANSI/AWWA C102/A21.2.
- A-C pipe, classes 100 and 150 ASTM C296, AWWA C400.
- Ductile iron pipe, classes 50-56 ANSI/AWWA C151/A21.51.
- Steel pipe, schedule 40 ASTM B36.10.
- Cast iron O.D. PVC plastic pipe AWWA C900.



WARNING: Use on A-C pipe, which contains a known carcinogen, requires appropriate protective equipment and procedures be employed.