







SHOCKS ACTIVE VIBRATION CONTROL® SYSTEM

reduces vibration felt by the user at the handles.

SHOCKS

20% LESS

VIBRATION

compared to hammers

without such systems.





PERFORM & PROTECT™ grinding, cutting, and drilling shrouds reduce the amount of air-borne dust exposure, increase user visibility, and cut down on tool maintenance costs.

DEWALT offers 220+ OSHA Table 1 Compliant dust solutions within our PERFORM & PROTECT™ line.



KICKBACK BRAKE™ engages when a pinch, stall, or bind-up event is sensed to shut the grinder off.

E-CLUTCH

E-CLUTCH® SYSTEMThe DEWALT anti-rotation E-Clutch® system, offers technology capable of

detecting the motion of the tool. This feature senses the motion of the tool and shuts it down if necessary. The red indicator LED illuminates when the E-Clutch® system is engaged.

LANYARD READY

tool in case it is dropped.

LANYARD READY™ integrated solutions to rigid structures when working at height with a maximum lanyard length of 2m, helping to secure the

to tether select corded and cordless tools

1" Pistol Grip SDS Plus® Rotary Hammer Kit

D25133K



SPECIFICATIONS	
Amps	8 A
Impact Energy	2.6 Joules**
No Load Speed	0-1100 rpm
Blows / Min	0-4600 bpm
Vibration Measurement	-
Vibration Control	No
Torque Control	Yes, Integral Clutch
Optimal Drilling Range	5/32" - 5/8"
Tool Weight (Tool only)	5.7 lbs
Service Contract	1 Years Free Service
Includes	360° Side Handle with Depth Rod and Kit Box

CDECIEICATIONS

1" D-Handle SDS Plus® Rotary **Hammer Kit**

D25262K



SPECIFICATIONS	
Amps	8 A
Impact Energy	2.8 Joules**
No Load Speed	0-1500 rpm
Blows / Min	0-5540 bpm
Vibration Measurement	9.6 m/s ²
Vibration Control	Yes, SHOCKS™
Torque Control	Yes, Integral Clutch
Optimal Drilling Range	5/32" - 5/8"
Tool Weight (Tool only)	6.6 lbs
Service Contract	2 Years Free Service
Includes	360° Side Handle with Depth Rod and Kit Box

1-1/8" D-Handle SDS Plus® **Rotary Hammer Kit**

D25263K



SPECIFICATIONS	
Amps	8.5 A
Impact Energy	3.0 Joules**
No Load Speed	0-1450 rpm
Blows / Min	0-5350 bpm
Vibration Measurement	9.8 m/s ²
Vibration Control	Yes, SHOCKS™
Torque Control	Yes, Integral Clutch
Optimal Drilling Range	1/4" - 3/4"
Tool Weight (Tool only)	6.6 lbs
Service Contract	2 Years Free Service
Includes	360° Side Handle with Depth Rod and Kit Box

1-1/8" L-Shape SDS Plus® Rotary Hammer Kit

D25333K



PERFORM	011001/0
PROTECT	SHOCKS K
777777	VALABATA

SPECIFICATIONS	
Amps	8.5 A
Impact Energy	3.5 Joules**
No Load Speed	0-1000 rpm
Blows / Min	0-4480 bpm
Vibration Measurement	7.5 m/s ²
Vibration Control	Yes, SHOCKS™
Torque Control	Yes, Integral Clutch
Optimal Drilling Range	1/4" - 7/8"
Tool Weight (Tool only)	8.1 lbs
Service Contract	2 Years Free Service
Includes	360° Side Handle and Kit Box