EP Branch Multi-port Tee

Submittal Information Revision B: April 10, 2009

Project Information

Job Name:

 Job Name.

 Location:
 Part No. Ordered:

 Engineer:
 Date Submitted:

Submitted By:

Approved By:

Contractor:


Manufacturer's Representative:

Technical Data

Material:	UDEL GF120			
Maximum Temperature (no pressure):	320°F			
Maximum Working Temperature/Pressure:	210°F at 150 psi			
Maximum Manifold Flow for 34" Outlet:	7.5 gpm @ 8 fps 3.75 gpm @ 4 fps			
Maximum Manifold Flow for 1" Outlet:	16.5 gpm @ 8 fps 6.6 gpm @ 4 fps			

Product Information and Application Use

The Uponor EP Branch Multi-port Tee is used in hot and cold domestic potable water distribution systems. The EP Branch Multi-port Tee is available with 34" or 1" ProPEX[®] inlets.¹ All outlets are configured with 1/2" ProPEX connections.



\checkmark	Description	Part Number	А	В	С	D	Weight
	34" EP Branch Multi-port Tee, 3 outlets	Q2237550	5.15"	1.62"	1.25"	34" ProPEX	1.10 lbs.
	34" EP Branch Multi-port Tee, 4 outlets	Q2247550	6.40"	1.77"	1.25"	34" ProPEX	1.13 lbs.
	34" EP Branch Multi-port Tee, 6 outlets	Q2267550	8.90"	1.62"	1.25"	34" ProPEX	1.24 lbs.
	1" EP Branch Multi-port Tee, 6 outlets	Q2261050	9.30"	2.00"	1.25"	1" ProPEX	1.24 lbs.

Installation

Any product designed to mount 1" copper pipe (for the ³/₄" EP Branch Multi-port Tee) or 1¹/₄" copper pipe (for the 1" EP Branch Multi-port Tee) may be used as a mounting bracket. For more information, refer to the Uponor Professional Plumbing Installation Guide.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14- and 61-certified; ICC ESR 1099

Related Applications

PEX-a Plumbing Systems

Contact Information

Uponor, Inc. 5925 148th Street West Apple Valley, MN 55124 USA Phone: (800) 321-4739 Fax: (952) 891-1409 www.uponor-usa.com Uponor Ltd. 2000 Argentia Rd., Plaza 1, Ste. 200 Mississauga, ON L5N 1W1 CANADA Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca

uponor