SANI-21 TM PVC SEWER PIPE SPECIFICATION DATA

D3034 & F679 SEWER SPECIFICATION DATA

Diamond gravity sewer pipe 4 inches through 60 inches shall be made of compounds conforming to material requirements of ASTM D3034 and ASTM F679 in accordance with ASTM D1784. Diamond PVC Sewer Pipe meets all the dimensional, chemical, and physical requirements as outlined in ASTM D3034 and ASTM F679. A listing to CSA B182.2 is available for most of these sizes. A complete listing by manufacturing plant is available upon request.

The pipe sizes 4 inches through 60 inches are made with an integral bell "water-tight" joint that meets the requirements of ASTM D3212 and that utilizes a Rieber gasket system for sealing that meets the requirements of ASTM F477.


Each male end shall be beveled to facilitate joining and referencing marked for proper insertion depth. Diamond furnished lubricant is to be used in the joining process.

SANI-21TM PHYSICAL PROPERTIES OF ASTM D3034 & F679

Property	ASTM TEST	Minimum 12454/12364				
PIPE MATERIALS: PIPE SHALL BE MADE OF PVC PLASTIC HAVING A MINIMUM CELL CLASSIFICATION OF 12454 OR 12364 AS DEFINED IN SPECIFICATION D1784.						
Specific Gravity	D792	1.40/1.40				
Tensile Strength, psi	D638	7,000/6,000				
Tensile Modulus, psi	D638	400,000/500,000				
IZOD Impact Strength,	D256	.65ft., lb./in.				

SHORT FORM Specification for Diamond PVC Solid-Wall Sewer Pipe SDR 26 or SDR 35 or PS 46 or PS 115
All PVC Solid-Wall Sewer Pipe shall be made of compounds conforming to ASTM D1784 manufactured in
accordance with the material requirements of ASTM D3034 or ASTM F679. All PVC Sewer Pipe must meet
dimensional, chemical, and physical requirements as outlined in ASTM D3034 or ASTM F679. Joints shall meet the
requirements of ASTM D3212 and shall be formed using Rieber Technology. PVC Sewer Pipe shall be installed
according to the requirements of ASTM D2321, Uni-Bell's Uni-Pub 6 and the manufacturer's recommendations.

RIEBER JOINT ILLUSTRATION











SANI-21 TM PVC SEWER PIPE LOADING DATA

 $SANI-21^{TM}$

LOADING ASTM D3034 & F679 LOADING CHART (SDR26 / PS115)

Nominal Pipe Size in. (mm)	Outside Diameter Inches	Min. Wall Inches	Bundle Quantity	*Feet Per Truckload		
				14′	22′	
SDR26/PS115						
4" (100)	4.215	.162	69	23,184	24,288	
6" (150)	6.275	.241	24/32	10,080	11,264	
8" (200)	8.400	.323	18/24	5544/6048	5808/6336	
10" (250)	10.500	.404	12/15	3402	3564	
12" (300)	12.500	.481	16	2688	2816	
15" (375)	15.300	.588	6	1512	1584	
18" (450)	18.701	.671	2/3/4/6	1050		
21" (525)	22.047	.791	4	672		
24" (600)	24.803	.889	4	672		
27" (675)	27.953	1.002	3	378		
30" (750)	32.000	1.148	3	378/252		
36" (900)	38.300	1.373	2	168		
42" (1050)	44.500	1.596	2	168		
48" (1200)	50.800	1.954	1	84		
54" (1350)	57.560	2.064	1	42		
60" (1500)	61.610	2.210	1	42		

Prices are subject to a firm policy of "Price in effect at time of shipment on regular purchases"

[&]quot;Possession of this page does not constitute an offer of sale"

