GUARANTEED TOUGH?

20V MAX* METAL CUTTING SAWS

Also Includes: (2) 20V MAX* XR® Lithium Ion Batteries (5.0 Ah), Charger, and Kit Box

Batteries and Charger Sold Separately

5-1/2" Metal Cutting Circular Saw

DCS373B



SPECIFICATIONS	
Voltage	20V MAX*
No Load Speed	3700 rpm
Blade Diameter	5-1/2"
Depth of Cut at 90°	1-11/16"
Tool Weight (Tool only)	7.0 lbs
Includes	Circular Saw Blade and Blade Change Wrench

20v

XR® Brushless Deep Cut Band Saw Specifications

DCS374B



SPECIFICATIONS	
Voltage	20V MAX*
Ft / Min	490 ft/min
Blade Length	44-7/8"
Maximum Capacity	4-3/4"
Tool Length	20-3/4"
Tool Weight (Tool only)	12.4 lbs
Includes	18 TPI Blade and Blade Tracking Wrench





DCS374P2

Band Saw

20v XR

DCS371B



SPECIFICATIONS	
Voltage	20V MAX*
Ft / Min	570 ft/min
Blade Length	32-7/8"
Maximum Capacity	2-1/2"
Tool Length	15"
Tool Weight (Tool only)	8.0 lbs
Includes	14/18 TPI Blade and Blade Tracking Wrench

AVAILABLE

AVAILABLE

DCS373B

DCS373P2

DCS373P2

AVAILABLE

DCS371B	Batteries and Charger Sold Separately
DCS371P1	Also Includes: (1) 20V MAX* XR® Lithium Ion Battery (5.0 Ah), Charger, and Kit Box
DCS3711	Blade Guard for One-Handed Use with DCS371 Includes Brush, and Brush Caps





DCS371P2

DCS3711

XR® Brushless Dual Switch Deep **Cut Band Saw**

DCS376B

20v



SPECIFICATIONS	
Voltage	20V MAX*
Ft / Min	490 ft/min
Blade Length	44-7/8"
Maximum Capacity	4-3/4"
Tool Length	20-3/4"
Tool Weight (Tool only)	12.4 lbs
Includes	18 TPI Blade and Blade Tracking Wrench

AVAILABLE

DCS376B Batteries and Charger Sold Separately Also Includes: (2) 20V MAX* XR® Lithium Ion Batteries (5.0 Ah), Charger, and Kit Box DCS376P2



DCS376P2

18 GA Swivel Head **Double Cut Shear** DCS491B

20v X



SPECIFICATIONS	
Voltage	20V MAX*
Strokes / Min	0-2450 spm
Minimum Cutting Radius	4-1/2"
Capacity in Steel	18 GA
Tool Weight (Tool only)	3.9 lbs
Includes	Blade Change Wrench

AVAILABLE DCS491B Batteries and Charger Sold Separately Also Includes: (2) 20V MAX* XR® Lithium Ion Batteries (4.0 Ah), DCS491M2 and Charger



DCS491M2

