



Google Nest Protect

Let's see what it takes for Nest Protect to think, speak and alert you.



Color



White

Dimensions

- W: 1.5 in (3.85 cm)
- H: 5.3 in (13.4 cm)
- D: 5.3 in (13.4 cm)

Certification

- Nest Protect has been tested to comply with safety standards UL 2034, UL 217, and NFPA-72 set out by UL and California State Fire Marshal

Sensors

- Split-Spectrum smoke sensor
- 10-year electrochemical carbon monoxide sensor
- Temperature
- Humidity
- Occupancy (120° field of view up to 20 ft)
- Ambient light
- Accelerometer
- Microphone

Audio

- Speaker loudness: 80 dB @ 3 ft (1 m) @ 1kHz

Operating temperature

- The alarm should not be installed in locations where the normal ambient temperature is below 40°F (4°C) or exceeds 100°F (38°C)
- Humidity range: 20% RH to 80% RH (non condensing)

Battery

- Battery model: Six long-life AA batteries (Energizer® Ultimate Lithium "L91")
- Wired model: Three long-life backup AA batteries (Energizer® Ultimate Lithium "L91")

External buttons

- RGB color ring with 6 LEDs

Horn

- 85 dB SPL @ 10 ft (3 m)

Wireless

- 802.11b/g/n (2.4GHz) Wi-Fi
- 802.15.4 (2.4GHz)
- Bluetooth® low energy

Warranty

- 2-year limited warranty. For help, visit nest.com/support