Location:



YMMONS[®] TempControl[®]



7-700 Thermostatic Mixing Valve **Specification Submittal**


Specification	Modifications			
TempControl thermostatic mixing valve made from lead free** metal components. Features serviceable integral check stops (see table 1 for flow rates).	 NI Rough nickel finish P Polished chrome highlight finish W Wall mounting bracket 			
Temperature control range: 70°F - 150°F (21.1°C - 65.6°C)	Note: Append appropriate -suffix to model number.			
Approach temperature: 5°F (-15°C) **According to US Senate bill S.3874, the term "lead free" is defined as follows: "not more than a weighted average of 0.25 percent lead when used with respect to the wetted surfaces of pipes, pipe fittings, plumbing fittings, and fixtures"	Coordinating Model Numbers □ T-425-700 3" bimetal dial thermometer □ BV-700/900 Volume control shut-off valve □ SV-700 Solenoid valve □ TF-700 Tee fitting			
Compliance	□ WHA-1 Water hammer arrestor Warranty			
-ASME A112.18.3/CSA B125.3-12 -ASSE 1017 -NSF/ANSI 61.9, NSF/ANSI 372	Limited Lifetime - to the original end purchaser in consumer/residential installations. 5 Years - for industrial/commercial installations. Refer to www.symmons.com/warranty for complete warranty information.			

Flow Rate Chart


TABLE 1: FLOW RATE - gpm (L/min)								
VALVE M MODEL	MIN. FLOW	MIN. FLOW RATE	PRESSURE DIFFERENTIAL - psi (kPa)					
	RATE*		5 psi (34 kPa)	10 psi (69 kPa)	20 psi (138 kPa)	25 psi (172 kPa)	30 psi (207 kPa)	45 psi (310 kPa)
7-700	0.5 gpm (1.9 L/min)	13 gpm (49 L/min)	25 gpm (95 L/min)	43 gpm (163 L/min)	57 gpm (216 L/min)	62 gpm (235 L/min)	66 gpm (250 L/min)	77 gpm (292 L/min)

^{*}Minimum flow rate when valve is installed at or near the hot water source with recirculated tempered water and continuously operating circulating pump.

Dimensions



T	TempControl Valve Sizes					
Мо	del No.	Inlet	Outlet			
7	-700	1-1/4"	1-1/2"			
	Measurements					
Α	1/2", 13 mm					
В	1-15/16", 49 mm					
С	9-13/16", 243 mm					
D	7-11/16", 195 mm					
Е	2-15/16", 75 mm					
F	4-7/8", 124 mm					
G	1-15/16", 49 mm					
Н	1-5/16", 33 mm					
Н	1-5/16", 33 mm					



Note: Dimensions subject to change without notice.