
**F-400** Page 3

# **EXPLODED VIEW, PARTS LIST AND SPECS**

### **EXPLODED VIEW**



#### **PARTS LIST**

Item	Catalog Number	Description	Qty
1	F-4019	1/4" FPT Adapter (PP)	2
1	F-4001NS	3/8" FPT Adapter (PP)	2
1	F-4003NS	1/2" FPT Adapter (PP)	2
2	90003-119	O-ring, 117, (Viton)**	2
3	-	Float (SS)*	1
4	F-4004	Guide wire, (SS)*	1
5	-	Meterbody (Acrylic)	1

Shading indicates item not sold separately

\*Hastelloy C-276 Option Available \*\*EP Option Available SS = # 316 Stainless Steel PP = Polypropolyne

#### **METER SPECS**

Scale	Permanent dual scale silkscreen		
Max Pressure	See Temperature vs. Pressure chart*		
Max Temperature	See Temperature vs. Pressure chart*		
Height	8.1875" (208.0mm)		
Width	1.25" (31.75mm)		
Accuracy	± 5% of full scale reading		

## **Application Notes**

Although meters may be suitable for other chemicals, Blue-White cannot guarantee their suitability. It is the responsibility of the user to determine the suitability of the flowmeter in their application. **Flowmeters are tested and calibrated for water only.** 

#### Maintenance

The "Exploded View" drawing illustrates assembly of the F-400N series meter. If your flowmeter needs to be cleaned refer to this drawing when reassembling the unit. The tapered tube may be cleaned with a soft bottle brush. Use a MILD soap and water solution for cleaning purposes. Note the floats "up" position.