

Polyester MULETAPE®

Description

Flat, woven, polyester tape used for installing fiber optic, copper, and coaxial cables in underground conduit.

Features & Benefits

- ▲ Lubricated for easy pulling and reduced friction
- ▲ Durably printed with sequential footage or meter markings*
- ▲ Available in a variety of pulling strengths from 200 to 6,000 lbs. (91-2727 kg)
- ▲ Low elongation for enhanced worker safety
- ▲ Lightweight and easily blown into conduit or innerduct
- ▲ Available in splice-free lengths up to 100,000 ft. (30 km) for faster, easier installation
- ▲ Packaged on sturdy wooden or plastic reels
- ▲ Easily spliced using conventional methods or the MULEKNOT™



Please refer to NEPTCO's applications bulletin for instructions on splicing using a MULEKNOT.

POLYESTER MULETAPE PRODUCT ORDERING INFORMATION

PRODUCT	STRENGTH		TYPICAL BOWLINE STRENGTH		TYPICAL MULEKNOT STRENGTH		MINIMUM REEL LENGTHS		MAXIMUM REEL LENGTHS		APPROX. WIDTH
	lbs	(kg)	lbs	(kg)	lbs	(kg)	ft	(km)	ft	(km)	
WP200N**	200	(91)	110	(50)	150	(68)	3000	(1)	100,000	(31)	1/8"
WP400P	400	(182)	190	(86)	300	(136)	3000	(1)	100,000	(31)	1/4"
WP600P	600	(273)	360	(164)	468	(213)	3000	(1)	100,000	(31)	3/8"
WP900P	900	(409)	480	(218)	770	(350)	3000	(1)	100,000	(31)	1/2"
WP1250P	1250	(568)	760	(345)	900	(409)	3000	(1)	70,000	(21)	1/2"
WP1800P	1800	(818)	830	(377)	1400	(636)	3000	(1)	50,000	(15)	5/8"
RP1800P	1800	(818)	830	(377)	1400	(636)	3000	(1)	3,000	(1)	3/8"
WP2500P	2500	(1136)	1300	(591)	1800	(818)	3000	(1)	25,000	(8)	3/4"
RP3300P	3300	(1500)	1900	(864)	2900	(1318)	1000	(.3)	3,000	(1)	1/2"
RP4000P	4000	(1818)	2300	(1045)	3500	(1591)	1000	(.3)	3,000	(1)	5/8"
RP6000P	6000	(2727)	3080	(1400)	5000	(2273)	1000	(.3)	3,000	(1)	3/4"

* All products are also available unprinted

** Product is only available unprinted

PLEASE SEE REVERSE SIDE FOR ADDITIONAL INFORMATION

