

Mirafi® FW-Series Woven Geotextiles for Engineered Filtration

TenCate develops and produces materials that function to increase performance, reduce costs and deliver measurable results by working with our customers to provide advanced solutions.

The Difference Mirafi® FW-Series Engineered Filtration Geotextiles Make:

- **Engineered Filtration.** Resists clogging while maintaining flow rates in high gradient and dynamic flow conditions.
- **Durability.** High survivability rating in aggressive installation and loading conditions along with excellent resistance to chemicals in aggressive environments.
- **Soil Interaction.** Superior soil confinement resulting in greater load distribution.
- **Unique Constructions.** Manufactured with highly UV stabilized multifilament fibers which provide uniform opening size (AOS) while maintaining high long-term flow rates. Mirafi® FW-Series geotextiles are manufactured with specialized processes to produce unique physical and hydraulic properties not possible with standard geotextiles, woven or nonwoven.
- **Seams.** Panels can be sewn together in

the factory or field, providing cross-roll direction strength to facilitate installation.

APPLICATIONS

Mirafi® FW-Series engineered filtration geotextiles are designed for long-term performance in problematic soil or site conditions to ensure clogging resistance, soil retention in erosion control, and subsurface drainage applications. Mirafi® FW-Series geotextiles are used underneath rip rap or concrete revetment systems along inland waterways and coastal shorelines to protect spillways and embankment dams from overtopping flow, encapsulating cut-off drains and collection systems surrounding landfills, filtration within dams. The geotextile is used adjacent to roadways and other critical structures, encapsulating leachate collection systems under landfills while maintaining long-term clogging resistance, and encapsulating edge drains for critical structures in problematic soils.

INSTALLATION GUIDELINES*

BANK STABILIZATION / ROCK (ARMOR) UNDERLAYMENT Geotextile Placement
Place the geotextile in close contact with the soil, eliminating folds or excessive wrinkles



Mirafi® FW Woven Geotextile

both longitudinally and transversely. The geotextile need not be placed in tension before covering with riprap or other materials. Use care in placing the geotextile to avoid possible damage.

The geotextile can be joined by overlapping or sewing. Anchor the geotextile firmly at the top of the slope using an anchor trench. For maximum effectiveness, the trench should be at least 1m (3ft) from the crest of the slope and at least 0.6m (2ft) deep. Thoroughly compact soil in the trench to ensure good anchorage. When placing the geotextile along a stream or other places where water movements are expected, anchor the toe of the geotextile in a similar fashion as at the top to prevent scour beneath it.

* These guidelines serve as a general basis for installation. Detailed instructions are available from your TenCate representative.




Mirafi® FW Woven Geotextiles for Engineered Filtration

Property / Test Method	Units	FW300	FW402	FW403	FW404	FW500 ¹	FW700
MECHANICAL PROPERTIES							
Minimum Average Roll Value							
Grab Tensile Strength							
ASTM D4632							
MD	lbs (N)	400 (1780)	365 (1624)	425 (1891)	400 (1780)	375 (1669)	370 (1647)
CD	lbs (N)	335 (1491)	200 (890)	350 (1558)	315 (1402)	375 (1669)	250 (1113)
MD Elongation	%	20	24	21	15	15	15
CD Elongation	%	15	10	21	15	8	15
Trapezoid Tear Strength							
ASTM D4533							
MD	lbs (N)	145 (645)	115 (512)	145 (645)	150 (668)	120 (534)	100 (445)
CD	lbs (N)	125 (556)	75 (334)	125 (556)	165 (734)	120 (534)	60 (267)
CBR Puncture Strength							
ASTM D6241	lbs (N)	1250 (5563)	675 (3004)	1340 (5963)	1150 (5118)	1200 (5340)	950 (4228)
HYDRAULIC PROPERTIES							
Minimum Roll Value							
Percent Open Area							
COE-02215	%	8	10	6	1	3	4
Permittivity							
ASTM D4491	sec ⁻¹	1.50	2.10	0.96	0.90	0.20	0.28
Flow Rate							
ASTM D4491	gal/min/ft ² (l/min/m ²)	115 (4685)	145 (5907)	70 (2852)	70 (2852)	15 (611)	18 (733)
Apparent Opening Size							
(AOS) ASTM D4751	US Sieve (mm)	30 (0.60)	40 (0.425)	40 (0.425)	40 (0.425)	50 (0.30)	70 (0.212)
Minimum Test Value							
UV Resistance after 500 hrs.							
ASTM D4355	% Strength	90	90	90	90	70	90
Packaging							
Roll Width	ft (m)	12.5 (3.8)	12.5 (3.8)	12.5 (3.8)	15 (4.57)	15 (4.57)	12 (3.7)
Roll Length	ft (m)	300 (91)	300 (91)	300 (91)	300 (91.4)	300 (91.4)	300 (91)
Area	yd ² (m ²)	417 (348)	417 (348)	417 (348)	500 (418)	500 (418)	400 (334)

¹ Cross direction yarns are slit film


Mirafi® FW Woven Geotextiles



Shoreline Erosion Control



Leachate Collection System



Cut-off/Interceptor Drain Along a Roadway

TenCate Geosynthetics Americas assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. TenCate Geosynthetics Americas disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, materials, or information furnished herewith. This document should not be construed as engineering advice.

Mirafi® is a registered trademark of Nicolon Corporation.

© 2017 Nicolon Corporation. All Rights Reserved.

PDS.FW0117

365 South Holland Drive Tel 800 685 9990 Fax 706 693 4400
Pendergrass, GA 30567 Tel 706 693 2226 www.mirafi.com



TENCATE
materials that make a difference