

## EK05S / EK07S Shallow Well Jet Pump

The EK05S and EK07S feature the famous Flint & Walling "Service Plus" motor in a Uni-frame flange design.

The Buna-n quadraseal is reusable and provides a positive seal between the pump case and motor bracket.

Diffusers are corrosion and abrasion resistant, and provide precision alignment with the impeller for maximum performance.

Impellers are precision balanced and ultra-smooth for high efficiency.

Standard shaft seal with ceramic and silicon carbide face is selfadjusting throughout the seal life.

Patented uni-frame motor bracket is designed to accept any NEMA J motor if motor replacement is ever necessary.

Automatic overload senses both start and run winding heat for complete winding protection.



Count on Flint & Walling's versatile, powerful jet pumps and "ServicePlus" motors to deliver more water in rural areas at full city pressures.





## **PERFORMANCE**

Model	НР	Suction Lift (FT)	Pressure Switch Setting	Capacity - U.S. Gallons per Hour Discharge Pressure (PSI)				Suction	Discharge
				20	30	40	50	Pipe	Pipe
EK05S	1/2 HP	5	20-40	10.5	9.5	5.8	4.0	1-1/4 in.	3/4 in.
		15		7.6	7.3	4.5	2.5		
		25		4.5	4.2	3.5	2.0		
EK07S	3/4 HP	5	20-40	15.5	15.0	10.0	5.8		
		15		11.9	11.7	9.1	3.8		
		25		6.0	5.8	5.2	2.0		

Maximum Pump Case Pressure = 150 PSI