


# Lovibond® Water Testing Tintometer® Group



## MD 100 Chlorine, powder reagents

Precise water control with proven and compact measuring system



The MD 100 has several key features that make it a favorite among users.

### Waterproof Design

The IP 68 design of this instrument ensures that the MD 100 remains water tight for up to 1 hour at 0.1 meter. Don't worry about dropping the instrument into a body of water - it floats!

### Accurate, Reproducible Results

The optical system of the MD 100 utilizes LEDs and interference filters which quickly gives you results that you can be confident in. You always measure in the spectral peak.

### User Calibration Mode

A one-point calibration is possible. Additionally, all MD 100 instruments have the ability to display readings directly in ABS or %T units.

### One-time-Zero Function

Don't waste time waiting for your instrument to Zero after each test. When testing a new sample, zero the instrument once and all subsequent tests of that sample do not require you to re-zero the instrument.

### Automatic Data Storage with Transfer Capabilities

The MD 100 automatically stores the last 16 readings with time and date stamp. These results can be transferred to a spreadsheet using the IRiM accessory.

- High-precision optics
- High accuracy and reproducibility through precision interference filter (5 nm)
- Industry specific parameter combinations available

Part Number: 276010

### Ergonomic Design

Whether you're using the MD 100 out in the field or in the lab, the design of the instrument makes it easy to handle and view the display. If you're using the instrument in the lab, the rubber feet on the bottom of the housing eliminates the need for two hand operation or to chase your instrument around the workbench.

### Factory Programmed

All MD 100 instruments are supplied ready to use with up to 14 calibration curves. All you need to do is select the test you need, prepare your sample and test!

### Scroll Driven Menu System

The simple interface allows you to quickly reach the test you need. When the instrument is turned on, it will automatically display the last test used.

### 2-Year Warranty

## Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Pool Public | Pool Services | Power and Energy

## Application

Boiler Water | Cooling Water | Disinfection Control | Drinking Water Treatment | Pool Water Control | Pool Water Treatment | Raw Water Treatment | Waste Water Treatment

## MD 100 Chlorine, powder reagents

The MD 100 colorimeter is a single parameter colorimeter for water quality analysis. This line of rugged, waterproof instruments is lightweight and ideal for field testing or for use in the laboratory.

Chlorine is one of the most popular water quality testing parameters and the MD 100 Chlorine Colorimeter offers a testing solution to fit a wide variety of industries and applications.

This instrument is pre-programmed with two testing ranges for testing Free, Total and Combined Chlorine. Both ranges use the DPD method and utilize Lovibond® Powder Pack Reagents.

## Measuring Range

Test Name	Measuring Range	Chemical Method
Chlorine HR PP	0.1 - 8 mg/l Cl <sub>2</sub> <sup>a)</sup>	DPD
Chlorine PP	0.02 - 2 mg/l Cl <sub>2</sub> <sup>a)</sup>	DPD

## Technical Data

<b>Optics</b>	LEDs, interference filters (IF) and photo sensor in transparent sample chamber. Depending on the version, up to 3 different interference filters are used. Wavelength specifications of interference filters: 430 nm $\Delta\lambda = 5$ nm 530 nm $\Delta\lambda = 5$ nm 560 nm $\Delta\lambda = 5$ nm 580 nm $\Delta\lambda = 5$ nm 610 nm $\Delta\lambda = 6$ nm 660 nm $\Delta\lambda = 5$ nm
<b>Wavelength Accuracy</b>	± 1
<b>Photometric Range</b>	-2500 - 2500 mAbs
<b>Photometric Accuracy</b>	3 % FS (T = 20 °C – 25 °C)
<b>Operation</b>	Foil keypad
<b>Display</b>	backlit LCD (on keypress)
<b>Suitable Vials</b>	Round Cuvettes 24 mm
<b>Calibration</b>	factory calibration and user calibration. Reset to factory calibration possible
<b>Interfaces</b>	Infrared
<b>Internal Storage</b>	internal ring memory for 16 data sets
<b>Power Supply</b>	4 micro batteries (AAA)
<b>Battery Life Time</b>	approx. 17 hours
<b>Auto – OFF</b>	Yes
<b>Clock</b>	Real Time Clock and Date
<b>Portability</b>	Portable
<b>Environmental Conditions</b>	Temperature: 5 - 40 °C rel. humidity: 30 - 90 % (non condensing)
<b>Compliance</b>	CE
<b>Protection Class</b>	IP 68
<b>Dimensions</b>	155 x 75 x 35 mm
<b>Weight</b>	260 g

## Delivery Scope

- Instrument in plastic case
- Chlorine Free Powder Packs
- Chlorine Total Powder Packs
- 4 micro batteries (AAA)
- 3 round cuvettes (glass) with lid
- 2 cuvettes (plastic) with lid
- Sealing rings
- Brush
- Instruction manual
- Quick Start Guide
- Certificate (COC)
- Warranty information

## Accessories

Title	Part Number
Water sampler, AF 631	170500
Micro batteries (AAA), set of 4	1950026
Multy cuvette-2, set of 12	197600
Round cuvette 24 mm, set of 12	197620
Sealing ring for round vials 24 mm, set of 12	197626
Round cuvette 24 mm, set of 5	197629
Cleaning cloth	197635
Round cuvette 16 mm, set of 10	197665
Adapter for round cuvettes 16 mm	19802190
Mixing cylinder, 25 ml	19802650
Infrared data transmission modul IRiM	214050
Verification Standard Kit MD 100 / 200	215670
Reference Standard Kit Chlorine - VARIO 0.2 and 1.0	275660
Stirring rod, 13 cm length	364100
Stirring rod, 10 cm length	364109
Stirring rod, 13 cm length, set of 10	364120
Stirring rod, 10 cm length, set of 10	364130
Membrane filter set for use when preparing samples, 25 membrane filters 0.45 µm, 2 syringes 20 ml	366150
500 ml bottle, AF 631	375069
Brush, 11 cm length	380230
Measuring beaker, 100 ml	384801
Cuvette stand for 6 round cuvettes Ø 24 mm	418951
Cuvette stand for 10 round cuvettes Ø 16 mm	418957
Plastic funnel with handle (white)	471007
ValidCheck Chlorine 1,5 mg/l	48105510
Basic price for calibration certificate for each unit	999845
Additionally for each method	999855

---

**Tintometer GmbH**

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
Fax: +49 (0)231/94510-30  
sales@lovibond.com  
www.lovibond.com  
Germany

**The Tintometer Limited**

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

**Tintometer China**

Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

**Tintometer South East Asia**

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

**Tintometer Brazil**

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@tintometer.com.br  
www.lovibond.com.br  
Brazil

**Tintometer Inc.**

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.com  
USA

**Tintometer India Pvt. Ltd.**

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

**Tintometer Spain**

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain

Technical changes without notice  
Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies