For Residential and Commercial Applications

Job Name	Engineer / Architect	
Job Location	Wholesaler	
Submittal Date	Contractor	

BWB0 .57" ID Braided Water Heater Connectors

Use: For use in exposed locations only to connect water heaters and other water connected devices to the water supply. Not intended for use with recirculating water systems that produce continuous use temperatures above 115° F. For those applications use our CopperFlexTM series connectors.

Design Features:

- Corrosion resistance to harsh chemicals found in common household cleaning and plumbing repair products
- **Strong and flexible.** The polymer braid exhibits greater elasticity than stainless steel braiding, significantly increasing the flexibility of the connector
- No kinking, no crimping. The polymer braided jacket is specially engineered to bend freely without kinking or crimping the connector
- Won't work harden even with repeated bending
- No dielectric union needed with installation as the braiding and rubber are constructed of non-conductive materials
- Nut provides a full thread engagement resulting in a secure connection
- Available for PEX connections






Pressure: water pressures up to 125 PSI maximum

OPERATING SPECIFICATION					
	12"	15"	18"	24"	
Flow Coefficient (Cv)	5.9	5.8	5.6	5.4	

 ΔP (Pressure Drop) = GPM²/Cv² for Example: 24" length connector @ 10 GPM $\Delta P = 10^2 / 5.4^2 = 100 / 29.16 = 3.43$ psi

CONNECTOR MATERIAL SPECIFICATIONS		
Inner Hose	Rubber	
Braiding	Coated yarn	
Barb	Brass	
Ferrule	Brass	

CONNECTOR MATERIAL SPECIFICATIONS		
Nut	Brass	
End Fitting	Brass	
Washer	Rubber	



BWB0 .57" ID Braided Water Heater Connectors

Part Listing: BWB0-12 .57" ID X 12" connector with 3/4" FIP x 3/4" FIP end fittings BWB0-15 .57" ID X 15" connector with 3/4" FIP x 3/4" FIP end fittings BWB0-18 .57" ID X 18" connector with 3/4" FIP x 3/4" FIP end fittings


BWB0-18 X .57" ID X 18" connector with 3/4" FIP x 3/4" FIP end fittings, cut case

BWB0-24 .57" ID X 24" connector with 3/4" FIP x 3/4" FIP end fittings


BWB0-24 X .57" ID X 24" connector with 3/4" FIP x 3/4" FIP end fittings, cut case

BWB0-18PX .57" ID X 18" connector with 3/4" FIP x 3/4" PEX end fittings
BWB0-24PX .57" ID X 24" connector with 3/4" FIP x 3/4" PEX end fittings

BWB0 Series



BWB0-PX Series



PART DIMENSIONS (Inches)					
Connector Length – Nut by Nut					
Model	DIM.	12"	15"	18"	24"
BWB0	Α	12.00 / 13.00	15.00 / 16.00	18.00 / 19.00	24.00 / 25.00
BWB0-PX	Α			19.00 / 20.00	25.00 / 26.00

Listings & Certifications:

 IAPMO listed to ASME A112.18.6 / CSA B125.6 (includes NSF/ANSI372 and NSF61)







This specification and all information contained herein is the confidential and exclusive property of Brasscraft Manufacturing Company and shall not be disclosed to others without the written consent of Brasscraft Mfg. Co. This specification must be returned to Brasscraft Mfg. Co. if requested.

