CATALOG NUMBER:

CP3B12115ACLLV11

9/16'

600

120/240 VAC 1Ø 3W; 200 AMPS Maximum, (See main circuit breaker rating).

Rainproof - Type 3R, Steel (G90) enclosure painted light green Enclosed Industrial Control - Suitable only for use as Service Equipment

The short circuit current rating is 10,000 RMS symmetrical amperes maximum at 240 VAC maximum. Watthour meter is not included in the short circuit rating.

CIRCUIT BREAKERS DIRECTORY							
NO.	AMP	POLE	DESCRIPTION	NO.	AMP	POLE	E DESCRIPTION
1			THIS SPACE NOT AVAILABLE	2	200	2	MAIN
3			THIS STREET NOT TWILE BEE	4	200		IVITALIA
5	60		LIGHTING	6	15	1	CONTROL
7		2		8			

Replacement circuit breakers data: CIRCUIT BREAKERS: MAIN: SIEMENS TYPE QNR

#3-1/0

BRANCH BREAKERS: SIEMENS TYPE QP, GE TYPE THQL (70A MAX) Replacement circuit breakers must be of the same type and rating.


GE CONTACTORS MUST BE FED FROM GE TYPE THQL BRANCH BREAKERS

TERMINAL INFORMATION: USE AL/CU CONDUCTORS! USE MORE THAN ONE CONDUCTOR PER OPENING WHERE INDICATED FOR EQUIPMENT

GROUND ONLY!

50

1/4-20 72 TORQUE LB-IN. FIELD WIRED CONNECTORS **BUS CONNECTIONS** BELLEVILLE AWG SMALL HOLE LARGE HOLE 5/16-18 145 SCREW **TORQUE** WASHER SOCKET #6 - MAX TORQUE WIRE SIZE 1/0 - MAX 3/8-16 240 LB-IN. NUTS SIZE LB-IN. SLOTTED #14-10 20 35 THREAD 1/2-13 265 HEX 10-24 30 5/16' 275 HEAD 25 40 **FORMING** HEAD 10-24 CU 50 BREAKER CONNECTIONS SCREWS 3/8' 375 #6 45 SCREWS 35 SCREWS SCREW TORQUE LB-IN 1/4-20 ΑL 50 1/2" 500 45 #4 #10 20 1/4-20 CU 72





Field installed conductors shall be 60°C, 75°C, or 90°C sized to 60°C rating for 100 Amps or less.

