

## For Residential and Commercial Applications

Job Name		Engineer / Architect	
Job Location		Wholesaler	
Submittal Date		Contractor	

## BL12-\*\*WA Speedi Plumb® PLUS Braided Washing Machine Connector – Female Hose Thread

**Use:** For use in potable water distribution systems in accessible locations only.

**Design Features:**

- **Superior corrosion resistance** to harsh chemicals found in common household cleaning and plumbing repair products
- **More flexible than stainless steel**, the braided polymer-coated fibers bend freely without kinking or crimping
- **Tough inner core** is reinforced to resist chlorine and chloramine leaching and deterioration
- **Nitrile rubber washers** provide a large pliable sealing surface and ensures a long lasting water tight connection
- **8-sided pneumatic crimp** provides greater dependability for realible nut-to-hose connections
- **100% Compliant** to California and Vermont “low-lead” requirements ✓

**Operating Specifications:**

**Temperature:** 40°- 140° F, intermittent to 180° F

**Pressure:** 125 psi maximum


**Tubing Diameter:** 0.450" I.D. (0.660" O.D.)

### MATERIAL SPECIFICATIONS

<b>Inner Hose</b>	EPDM or reinforced PVC
<b>Braiding</b>	PVC coated polyester yarn
<b>Barbs</b>	Compliant brass
<b>Ferrules</b>	Zinc plated 1008 steel
<b>Nuts</b>	C36000 brass
<b>Washers</b>	Nitrile rubber



Patents  
5,803,129 &  
5,899,236



**Part Listing:**

<input type="checkbox"/>	BL12-48WA	3/4" Female Hose Thread x 3/4" Female Hose Thread x48" Length, sleeve
<input type="checkbox"/>	BL12-48WA B	3/4" Female Hose Thread x 3/4" Female Hose Thread x48" Length, bulk
<input type="checkbox"/>	BL12-48WA F	3/4" Female Hose Thread x 3/4" Female Hose Thread x48" Length, flag labeled
<input type="checkbox"/>	BL12-60WA	3/4" Female Hose Thread x 3/4" Female Hose Thread x60" Length, sleeve
<input type="checkbox"/>	BL12-60WA B	3/4" Female Hose Thread x 3/4" Female Hose Thread x60" Length, bulk


This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

**BrassCraft®**

# BL12-\*\*WA Speedi Plumb® PLUS Braided Washing Machine Connector – Female Hose Thread

## Part Listing (con't):

- |                          |               |  |
|--------------------------|---------------|--|
| <input type="checkbox"/> | BL12-60WA PX2 | 3/4" Female Hose Thread x 3/4" Female Hose Thread x60" Length, 2 per bag, cutcase of 5 |
| <input type="checkbox"/> | BL12-72WA     | 3/4" Female Hose Thread x 3/4" Female Hose Thread x 72" Length, sleeve                 |
| <input type="checkbox"/> | BL12-72WA B   | 3/4" Female Hose Thread x 3/4" Female Hose Thread x 72" Length, bulk                   |
| <input type="checkbox"/> | BL12-72WA F   | 3/4" Female Hose Thread x 3/4" Female Hose Thread x 72" Length, flag labeled           |



PART DIMENSIONS (Inches)	
Model	DIM. A
BL12-48WA	48.0 / 49.0
BL12-60WA	60.0 / 61.0
BL12-72WA	72.0 / 73.0

## Listings & Certifications:

- IAPMO listed to ASME A112.18.6-2003 (File # 0452)
- CSA listed to ASME A112.18.6-2003 / CSA B125 (File # 204593)
- CSA approved to California Health & Safety Code 116875 and Vermont Bill S.152 (Project # 2174785)



This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

**BrassCraft®**