## **Brass Cap**



## Description

FPPI's Brass caps feature all cast or forged construction of B124 brass alloy and is complete with a gasket. Each cap is accurately machined and will provide years of service. Our pin lug design is compatible with all fire service pin lug hydrant wrenches. Each cap is shipped complete with a brass chain and "S' type hook for attachment to hydrant or hose type valve equipped for this use. Protects male threads and discourages the introduction of debris into the hydrant or valve. Suitable for fire protection or industrial use.

## Installation

Each cap is easily threaded in a clockwise fashion onto the male thread. Prior to installation of the cap make sure the male threads are clean and free of debris and the water way being covered is clean and clear of debris. Tighten using two pin lug type hydrant wrenches. Tested to a maximum working pressure of 300 PSI.

## **Specifications**

Material: B124 Brass

Size:

2 1/2" FNST

**FBCT** 

**FQST** 

FONT

FPHX

FTEM

FCLV

FDET 1 1/2" FNST

1 1/2" FNPSH

3" FNST

Finish:

Rough Brass

