# **GUARANTEED TOUGH**<sup>®</sup>

## 60V MAX\* FLEXVOLT® SAV

Batteries and Charger Sold Separately

Battery (6.0 Ah), Charger, and Kit Bag

DCS575T2

Also Includes: (1) 20V/60V MAX\* FLEXVOLT® Lithium Ion

Also Includes: (2) 20V/60V MAX\* FLEXVOLT® Lithium Ion Batteries (6.0 Ah), Charger, and Kit Bag

# Brushless 7-1/4" Circular Saw



Voltage

No Load Speed

Blade Diameter

**Dust Port Diameter** 

Depth of Cut at 45°

Depth of Cut at 90°

Max Rip to Right of Blade

Max Rip to Left of Blade

Tool Weight (Tool only)

SPECIFICATIONS

Arbor Size

Includes

Voltage No Load Speed

Includes

Blade Diameter

**Bevel Capacity** 

Depth of Cut at 45°

Depth of Cut at 90°

Tool Weight (Tool only)

DWS5023

SPECIFICATIONS

Brushless 12" Double Bevel Compound Sliding Miter Saw
DHS790AB



Brushless 8-1/4" Table Saw DCS7485B



Brushless 6-1/2" TrackSaw™	
DCS520B	





#### TrackSaw<sup>™</sup> Blades and Attachments

DWS5020







DWS5022

SPECIFICATIONS	
Voltage	60V MAX*
No Load Speed	5800 rpm
Blade Diameter	7-1/4"
Bevel Capacity	0°-57°
Bevel Detents	45° and 22.5°
Depth of Cut at 45°	2"
Depth of Cut at 90°	2-9/16"
Tool Weight (Tool only)	7.6 lbs
Includes	Circular Saw Blade and Blade Change Wrench

SPECIFICATIONS	
Voltage	120V MAX*
Amps (with AC Adapter)	15 A
No Load Speed	3800 rpm
Blade Diameter	12"
Arbor Size	5/8" or 1"
Vertical Capacity	6-3/4"
Nested Crown Capacity	7-1/2"
45° Cross-Cut Capacity	4" x 8"
90° Cross-Cut Capacity	2"x 16" (with back fence)
Tool Weight (Tool only)	56.0 lbs
Cut Line System	XPS LED
Includes	120V AC Adapter, 12" Carbide Blade, Blade Change Wrench, and Dust Bag

60V MAX\*

5800 rpm

8-1/4"

5/8"

2-1/2

1-3/4"

2-1/2"

24"

12"

48.0 lbs

60V MAX\*

6-1/2"

0°-47°

1-5/8"

2-1/8"

12.1 lbs

DWS5025

2500 - 4200 rpm

Circular Saw Blade and Blade Change Wrench

Carbide Blade, Blade Guard, Riving Knife, Miter Gauge, (2) Blade Change Wrenches, Rip Fence, and Push Stick

## DCS575T1 **AVAILABLE** DHS790AB Batteries and Charger Sold Separately Also Includes: (2) 20V/60V MAX\* FLEXVOLT® Lithium Ion Batteries (6.0 Ah), and Dual Port Fast Charger DHS790AT2

**AVAILABLE** 

DCS575B

DCS575T1

DCS575T2



DHS790AT2

### AVAILABLE

DCS7485B	Batteries and Charger Sold Separately
DCS7485T1	Also Includes: (1) 20V/60V MAX* FLEXV0LT® Lithium Ion Battery (6.0 Ah), and Fast Charger



DCS7485T1

## AVAILABLE

DCS520B	Batteries and Charger Sold Separately
DCS520T1	Also Includes: (1) 20V/60V MAX* FLEXVOLT® Lithium Ion Battery (6.0 Ah), Charger, and TSTAK® Kit Box
DCS520ST1	Also Includes: (1) 20V/60V MAX* FLEXVOLT $^{\circ}$ Lithium Ion Battery (6.0 Ah), Charger, 59" Track, and TSTAK* Kit Box
DCS520T1	



AVAILABLE	
DWAF16542	Precision Ground Woodworking Blade for TrackSaw <sup>™</sup> System- 42T
DW\$5020	46" TrackSaw™ Track
DW\$5022	59" TrackSaw™ Track
DW\$5023	102" TrackSaw™ Track
DWS5025	TrackSaw™ Track Bag
DWS5026	TrackSaw™ Track Clamps
DWS5029	TrackSaw™ Replacement Zero-Clearance Anti-Splinter Strip
DWS5031	TrackSaw <sup>™</sup> Router Adapter
DWS5032	TrackSaw™ Replacement Friction Strip

60V MAX\* FLEXVOLT® SAWS