

# **SPECIFICATIONS**

Product Description: Part Number: Style: VENTILATION BLOWER, DC 9515-DC AXIAL FAN 16" (40.6 cm)

# **GENERAL DESCRIPTION:**

Designed for applications requiring a large amount of output. This standard model blower has a ½ HP motor with an efficient sixblade impeller in a rugged metal housing. This unit is constructed to be powered by a 12 volt car or truck battery for portable convenience.

#### **CONSTRUCTION:**

- Complete unit epoxy powder coated in orange
- Interchangeable flange for intake or exhaust side mounting
- 18 gauge cold rolled steel housing
- Integrated carrying handles
- Zinc plated grill
- Equipped with four rubber feet
- 15' (4.57 m) power cord with heavy duty battery clamps
- Easily accessible inline fuse
- Can be used with Adaptor Reducer (PN: 9600-50) used with 8" (20.3 cm) duct

#### MOTOR:

HP:	½ HP
Voltage:	12V DC
RPM:	1750
Current Draw:	39A
Fuse:	60A

#### FAN:

• Glass Reinforced Polypropylene (PPG), six blade with aluminum hub

#### **DUCTING:**

- Retractable, non-collapsible design
- Single-ply, PVC coated, vinyl and polyester materials, temp. resistant up to 180° F (82.2° C)
- Class 1 hard drawn spring steel wire helix that meets ASTM 227 specs

## **BLOWER DIMENSIONS:**

Length	Width	Height	Weight
18" (45.7 cm)	18" (45.7 cm)	19" (48.2 cm)	47 lbs (21.3 kg)

## **FLOW RATES:** (CFM calculated using 15' (4.57 m) of 16" (40.6 cm) ducting)

Free Air	One 90° Bend	Two 90° Bends
CFM (m <sup>3</sup> /hr)	CFM (m <sup>3</sup> /hr)	CFM (m³/hr)
2929 (4976)	1981 (3366)	1762 (2994)

