


PRODUCT RANGE - PIPE

aquatherm blue pipe® SDR 17.6 MF

Material: fusiolen® PP-R faser-composite

In accordance with:


- NSF-14
- CSA-B137.11
- ICC AC 122
- ICC ESR 1613
- ASTM F 2389



Appearance: Blue with light green stripe.

NSF system certification: Including fittings, connection pieces, and connection techniques.

Fields of application: Cooling distribution, condenser water, industrial applications, compressed air, and limited heating applications.



Pipe ^a		Diameter ^b	Wall thickness	Internal diameter	Water capacity	Weight ^c
Part no.	Dimension (ND — OD)	d (mm)	s (mm)	d _i (mm)	gal/ft	lb/ft
2570126	4" — 125 mm	125	7.1	110.8	0.776	1.8
2570130	6" — 160 mm	160	9.1	141.8	1.272	2.93
2570134	8" — 200 mm	200	11.4	177.2	1.986	4.57
2570138	10" — 250 mm	250	14.2	221.6	3.105	7.11
2570142	12" — 315 mm	315	17.9	279.2	4.930	11.25
2570144	14" — 355 mm	355	20.1	314.8	6.267	14.25
2570146	16" — 400 mm	400	22.7	354.6	7.952	18.10
2570148	18" — 450 mm	450	25.5	399.0	10.068	22.86
2570150	20" — 500 mm	500	28.4	443.2	12.422	28.27
2570152	22" — 560 mm	560	31.7	496.6	15.596	35.31
2570154	24" — 630 mm	630	35.7	558.6	19.733	44.71

^a ½" - 4" pipes come in standard 13 ft lengths (4 m). Pipes 6" and larger come in standard 19 ft lengths (5.8 m).

^b To calculate exact dimensions of the pipe in imperial inches, divide the metric measurement by 25.4.

^c To calculate the weight of the pipe in kg/m, multiply the measurement by 1.5.