



## Combination Drench Shower and Halo™ Eyewash or Eye/Face Wash

## **Key Features**

- Halo™ and SpinTec™ deliver the most effective shower and eye/face washdown coverage and spray pattern
- Industry's only self-draining design The Aquaduct™
- Separate supply and waste pipes meets plumbing requirements
- Ergonomic hand activation eyewash paddle easy to reach from any direction
- Fully-assembled and factory-tested eyewash or eye/face wash with hinged dust covers
- Yellow transparent plastic and stainless steel bowl covers available
- Barrier free options are available
- Universal identification sign and inspection tag included
- SpinTec showerheads are covered by one or more of the following patents: 8,113,446;
   7,806,348; 8,490,895; D594,089; D669,555; Reg. Comm. Des. D001079560-0001.
   Other patents pending.
- Halo is covered by one or more of the following patents: 9,700,484; 9,314,398; D662220; D673298; D662605; D685920; D662219; and D671228. Other patents pending.

## **Specifications**

Standard and Barrier-Free Combination Drench Shower/Eyewash or Eye/Face Wash Units save space and fit easily into any work environment. Shower valve operates quickly by a pull rod with a triangular handle. Shower provides a superior washdown with a more even spray pattern. Halo eyewash or eye/face wash, operated by an ergonomic, highly visible push handle, provides effective wash down coverage and spray pattern. Integral strainer reduces debris in the water and also prevents clogging.



This plumbing fixture is not intended to dispense water for human consumption through drinking or for preparation of food or beverages.

## **Product Compliance**


### Classified by UL to

ANSI/ISEA Z358.1-2014



### Listed by UL to

- Uniform Plumbing Code (UPC)
- International Plumbing Code (IPC)





Page 1 of 4 5/5/2022
This information is subject to change without notice.
Bradley\_SafetyCombi\_S19314Series

View Latest Version

© 2022 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com





## Combination Drench Shower and Halo™ Eyewash or Eye/Face Wash

### **Pipe and Fittings**

Piping to 1-1/4" NPT (BSPP) water supply inlet on unit. Piping to 1-1/4" NPT (BSPP) drain outlet for eyewash. 11/4" piping assembly manufactured of one of the following materials:

- Galvanized steel with BradTect<sup>®</sup> safety yellow coating
- Type 304 corrosion resistant stainless steel
- Type 316 corrosion-resistant stainless steel


#### **Ball Valve**

1" stay-open shower ball valve and ½" stay-open eye and eye/face wash valve manufactured of the following materials and supplied with either type 304 or 316 stainless steel pull rod and handle:

- Chrome-plated brass
- Type 316 stainless steel

#### SpinTec™ Showerhead

Standard showerhead is 3.1" (78.7mm) diameter highly visible yellow impact-resistant plastic. Optional 10" (254mm) diameter yellow impact-resistant plastic or 10¾" (273mm) diameter corrosion-resistant stainless steel shroud. High performance Type 304 or Type 316 corrosion-resistant stainless steel showerhead measures 1½" (38mm) in diameter. SpinTec drench showerhead features integral 22 GPM (83.3 L) flow control (exceeds minimum water flow of 20 GPM (75.7L) at 30 PSI (2.0 bar)), conserving water and helping to accurately size your tepid water system.



#### Evewash

The Halo eyewash system offers a high performance rinsing platform that provides rapid relief to an individual's eyes that have been injured by chemicals or particulate. The eyewash includes an integral 5.1 GPM (19.2 L) flow control, providing water at a safe velocity while maintaining its effectiveness (exceeds minimum water flow of 0.4 GPM (1.5 L) at 30 PSI (2.0 bar)). The eyewash is protected by flip open dust covers that open when the product is activated or by a full bowl dust cover that activates the unit when it is opened. Safe, steady water flow under varying water supply conditions from 30–90 PSI (2.0-6.1 bar) is assured by integral flow control in the sprayhead assembly.

#### **Eve/Face Wash**

The Halo eye/face wash system offers a high performance rinsing platform that provides rapid relief to an individual's eyes and face that have been injured by chemicals or particulate. This system provides the most complete face wash available in the market. The eye/face wash includes an integral 5.1 GPM (19.2 L) flow control, providing water at a safe velocity while maintaining its effectiveness (exceeds minimum water flow of 3.0 GPM (11.4 L) at 30 PSI (2.0 bar)). The eye/face wash is protected by flip open dust covers that open when the product is activated or by a full bowl dust cover that activates the unit when it is opened. Safe, steady water flow under varying water supply conditions from 30–90 PSI (2.0-6.1 bar) is assured by integral flow control in the sprayhead assembly. Sprayheads are made from an impact resistant ABS plastic or from durable 304/316 stainless steel with electro-polished finish.

#### **Bowl and Dust Cover**

Bowl is constructed of yellow impact-resistant plastic, Type 304 corrosion-resistant stainless steel or Type 316 corrosion-resistant stainless steel. Optional dust cover is constructed of transparent yellow impact-resistant plastic, Type 304 corrosion-resistant stainless steel or Type 316 corrosion-resistant stainless steel.

#### Activation

Type 304 Stainless steel push handle with optional aluminum or type 304 stainless steel foot pedal. Type 316 stainless steel push handle with optional Type 316 stainless steel foot pedal.

#### **Drench Hose**

Perforated sprayhead with protective sprayhead cover is ABS plastic and provides soft spray for cleansing eyes and face. Chrome-plated brass valve with extended handle stays open once handle is squeezed. 8' (2438mm) yellow reinforced thermoplastic hose has %" NPT male thread. Burst strength is 450 PSI (31 bar). Attachment Kit includes ½" NPT supply, fittings and hanger for attaching hose to eyewashes or drench showers. The sprayhead contains an antimicrobial agent to protect the sprayhead.

#### **Backflow Prevention**

Series N9 dual-check backflow preventer has a chrome-nickel plated brass body and includes atmospheric vent for continuous pressure applications. The check valve comes with 3/8" female dual NPT female inlet and outlet connections. It can sustain a maximum pressure of 125 PSI (8.6 bars). The check valve is certified to CSA B64.8.

Series 9D dual-check backflow preventer with intermediate atmospheric vent can be used under continuous pressure. The primary check valve uses a rubber disc seating adjacent to a mating rubber part to ensure tight closing. A second check valve employs a rubber disc-to-metal seating.






## Combination Drench Shower and Halo™ Eyewash or Eye/Face Wash

# **Halo Configurator**

Standard	Selections (Must select one from each category)	
Configuration	ı	
A	6" Drain Height, Barrier Free 👲	
В	24" Drain Height	
C	24" Drain Height, Barrier Free 🕭	
0	6" Drain Height, Standard	
Pipe Material		
A	NPT, Yellow BradTect Galvanized Steel	
В	NPT, All 304 Stainless Steel	
C	NPT, All 316 Stainless Steel <sup>1</sup>	
D	NPT, Chrome-Plated	
F	BSPP, Yellow BradTect Galvanized Steel <sup>2</sup>	
G	BSPP, All 304 Stainless Steel <sup>2</sup>	
Н	BSPP, All 316 Stainless Steel <sup>2</sup>	
J	BSPP, Chrome-Plated <sup>2</sup>	
Ball Valve		
1	Stay-Open Shower and Eyewash, Chrome-Plated Brass	
2	Stay-Open Shower and Eyewash, 316 SS	
Showerhead		
Α	Plastic Showerhead	
В	Plastic Showerhead with Plastic Shroud	
C	Plastic Showerhead with Stainless Steel Shroud	
D	304 SS High Performance Showerhead	
E	316 SS High Performance Showerhead	
Eyewash – Eye/Face Wash		
A	Halo Eyewash <sup>3</sup>	
В	Halo Eye/Face Wash <sup>3</sup>	
D	Halo Eyewash, 304 SS Yoke	
E	Halo Eye/Face Wash, 304 SS Yoke	
F	304 SS Halo Eye/Face Wash, 304 SS Yoke 4	
G	Halo Eyewash, 316 SS Yoke	
Н	Halo Eye/Face Wash, 316 SS Yoke	
J	316 SS Halo Eye/Face Wash, 316 SS Yoke 4	

Bowl and Dust Cover		
A	Plastic Bowl, No Dust Cover	
В	Plastic Bowl, Plastic Dust Cover	
D	304 SS, No Dust Cover	
E	304 SS, 304 SS Dust Cover	
F	304 SS, Plastic Dust Cover	
G	316 SS, No Dust Cover	
Н	316 SS, 316 SS Dust Cover	
J	316 SS, Plastic Dust Cover	
0	No Bowl or Dust Cover	
Activation		
Α	300 SS Handle and Pull Rod	
В	316 SS Handle and Pull Rod <sup>1</sup>	
С	300 SS Handle with 300 SS Foot Pedal <sup>1</sup>	
D	300 SS Handle with 316 SS Foot Pedal 1	
E	316 SS Handle with 316 SS Foot Pedal <sup>1</sup>	
Drench Hose a	and Backflow Prevention	
Α	Drench Hose Kit with Vacuum Breaker	
В	Drench Hose Kit with N9 Backflow Preventer	
С	Drench Hose Kit with 9D Backflow Preventer	
D	Drench Hose Kit without Backflow Preventer	
Z	Drench Hose Ready	
0	No Drench Hose and No Backflow Prevention	
Freeze and Sc	ald Protection	
N	Anti-Freeze Valve 5	
P	Anti-Scald Valve	
R	Anti-Freeze and Anti-Scald Valves <sup>5</sup>	
Z	Anti-Freeze and Anti-Scald Valve Ready <sup>5</sup>	
0	No Anti-Freeze Valve and No Anti-Scald Valve	

- Not available with barrier-free configurations or with chrome plated pipe.
- Not available in the U.S.
- Not available with 316 SS Ball Valve (Option 2).
- Must select stainless steel pipe and ball valve when stainless steel eye/face wash is required.
- Includes frost-proof ball valves.





All selections made through the configurator are only UL certified to ANSI/ISEA Z358.1



NPT = National Pipe Thread

© 2022 Bradley

Page 3 of 4 5/5/2022 This information is subject to change without notice. Bradley\_SafetyCombi\_S19314Series

View Latest Version


P.O. Box 309, Menomonee Falls, WI 53052-0309 +1 262 251 6000 800 BRADLEY (800 272 3539) bradleycorp.com


Type 304 and 316 Stainless Steel



## S19314 Shown with Plastic Bowl and Showerhead

(mm)







All dimensions assume standard thread engagement. Variations in manufacturing allow for +/-  $\frac{1}{2}$ "(3mm) per threaded joint. To find the tolerance of a dimension, add the number of thread joints across the length of the dimension and multiply it by  $\frac{1}{2}$ " (3mm).