

# S59-3130 (HL130) Thermostatic High-Low Valves

- Lead-Free Brass Design †
- Reliable Liquid-Filled Thermostat with 10-Year Warranty
- Integral Strainer Checkstops on Inlets
- Adjustable Set Point within Temperature Range
- Accurate Temperature Control to within ±3° F
- Positive Shutoff of Flow in the Event of Cold Supply Line Failure or Thermostat Failure
- · Easy Installation and Serviceability
- Dirt and Lime Resistant
- · Factory Assembled and Tested
- Universal Mounting Capability
- · Dial Thermometer
- Cabinet Features:
  - 18 Gauge Body & Door
  - Left-Hand Hinge
  - Cylinder Lock
  - Inlet/Outlet Knock-Out Holes for Mounting Flexibility
  - Stainless Steel or Baked White Enamel Finishes
  - Surface-Mounted or Recessed Style with Flange

# **Valve Specifications**

#### **Maximum Operating Pressure**

125 PSI (860 kPA)

#### **Maximum Inlet Temperature**

200° F (93° C)

| Temperatu | re Range                         | Set Point      |
|-----------|----------------------------------|----------------|
| Std.      | 90° F (32° C) to 120° F (49° C)  | 110° F (43° C) |
| High      | 110° F (43° C) to 140° F (60° C) | 130° F (54° C) |

#### Flow Capacities - GPM

| Model    | Min.  | Pressure Drop – PSI |      |      |      |       |       |       |  |  |
|----------|-------|---------------------|------|------|------|-------|-------|-------|--|--|
|          | Flow* | 5                   | 10   | 15   | 20   | 30    | 45    | 60    |  |  |
| S59-3130 | 4.0   | 40.0                | 58.0 | 71.0 | 83.0 | 102.0 | 126.0 | 147.0 |  |  |

#### Flow Capacities - L/Min

| Model     | Min.  | Pressure Drop – Bar |       |       |       |       |       |       |  |  |
|-----------|-------|---------------------|-------|-------|-------|-------|-------|-------|--|--|
|           | Flow* | .5                  | 1.0   | 1.5   | 2.0   | 2.5   | 3.0   | 4.0   |  |  |
| \$59-3130 | 15.0  | 184.5               | 265.0 | 327.0 | 380.0 | 427.0 | 470.0 | 546.0 |  |  |

<sup>\*</sup>Recirculation system only (See diagram on Page 2). When properly installed near the hot water source with a **continuously operating** recirculation pump, the valve will maintain set temperature with a .5 GPM (2.0 L/Min) draw from the plumbing system.

#### **Product Compliance**



### Listed by IAPMO R&T to

- ASSE 1017, CSA B125.3
- Uniform Plumbing Code (UPC),
- National Plumbing Code of Canada and
- International Plumbing Code (IPC)



# Listed by ASSE International to

• ASSE 1017



### Listed by NSF International to

• NSF/ANSI 372

Certified to

Standard product selections contained within this document are third party CERTIFIED to NSF/ANSI 372 meeting the Lead-Free content requirement. Any product configured with custom options will be COMPLIANT with NSF/ANSI 372 meeting the Lead-Free content requirement.

Page 1 of 4 10/14/2019
This information is subject to change without notice.
Bradley\_TMV\_HighLow\_HL130



| Valve Model |                                    |
|-------------|------------------------------------|
| Model       | Description                        |
| □ S59-3130  | High-Low Thermostatic Mixing Valve |

| Configurable Valve         | Model (select one)                                  |
|----------------------------|---|
| Model                      | Description   |
| □ HL130                    | HL130 Thermostatic Mixing Valve with Options        |
| □ CAB-HL130                | HL130 Thermostatic Mixing Valve Cabinet Only        |
| Optional Valve Sele        | ections   |
| Finish                     |   |
| □R                         | Rough Brass (standard)                              |
| □ C                        | Chrome Plated                                       |
| Thermostat                 | 0   |
| □                          | Standard Range Thermostat<br>High Range Thermostat  |
|                            | riigii naiige illeiliiostat                         |
| Bracket<br>□ B             | Wall Mounting Bracket                               |
|                            | None  |
| Piped Assembly             |   |
| □ P                        | Piped Assembly with Inlet and Outlet Shutoff        |
| □ N                        | Piped Assembly with Outlet Shutoff                  |
| □ 0                        | None  |
| Optional Cabinet Se        | elections   |
| Cabinets (includes bracket |   |
| □ SS                       | Surface Mount Stainless Steel                       |
| □ RS                       | Recessed Stainless Steel                            |
| □ SE<br>□ RE               | Surface Mount White Enamel<br>Recessed White Enamel |
|                            | None  |
| Window                     |   |
| □ <b>W</b>                 | Plexi-Glass Window in Door                          |
| □ 0                        | None  |


† Wetted surface contains less than .25% lead

Engineer's Approval

© 2019 Bradley P.O. Box 309, Menomonee Falls, WI 53052-0309 800 BRADLEY (800 272 3539) +1 262 251 6000 bradleycorp.com




Recirculation Diagram (mm)



#### **Dimensions**

| Model     | A           | В             | С         | D           | E        | F            | G             | Н            | I         | X <sup>NPT</sup> | Y <sup>NPT</sup> | Z <sup>NPT</sup> |
|-----------|-------------|---------------|-----------|-------------|----------|--------------|---------------|--------------|-----------|------------------|------------------|------------------|
| \$59-3130 | 2-3/4" (70) | 10-1/2" (267) | 14" (356) | 1-3/4" (45) | 5" (127) | 6-5/8" (169) | 13-1/2" (343) | 4-7/8" (124) | 22" (559) | 1-1/4"           | 1-1/2"           | 3/4"             |




Page 2 of 4 10/14/2019 This information is subject to change without notice. Bradley\_TMV\_HighLow\_HL130

P.O. Box 309, Menomonee Falls, WI 53052-0309 800 BRADLEY (800 272 3539) +1 262 251 6000 bradleycorp.com




# **Dimensions — HL130 Surface-Mounted Cabinet**

(mm)









Page 3 of 4 10/14/2019 This information is subject to change without notice. Bradley\_TMV\_HighLow\_HL130

© 2019 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com

# Dimensions — HL130 Recessed Cabinet

(mm)





Page 4 of 4 10/14/2019 This information is subject to change without notice. Bradley\_TMV\_HighLow\_HL130

© 2019 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com