Spec Sheet #S00059 ® June 2005

megabubble®

Leak Detector



DESCRIPTION

High viscosity formula produces large, easily detected high strength blue bubbles with excellent cling properties for easier detection of gas leaks on pipes, fittings, tanks, coils, cylinders, pressure vessels, valves, etc. Longer lasting bubbles remain on surface allowing extra time for detecting even the smallest and slowest of gas leaks. Will not harm or stain metal, rubber or plastic surfaces. Non-toxic, non-corrosive formula can be used in lines carrying air, oxygen, nitrogen, natural or propane gas, carbon dioxide, refrigerants, and most other gases. Useful temperature range from -50°F to +200°F.

For most convenient application use Product 45802 32 oz. spray applicator bottle or 45804 16 oz. spray applicator bottle.

SIZES AND PACKING				
STOCK NO.	SIZE	PACKING	WEIGHT/CASE	
45801	8 oz. dauber bottle	24	14.8 lbs.	
45802	32 oz. spray bottle	12	30.0 lbs.	
45803	1 gal. refill	4	38.0 lbs.	
45804	16 oz. spray bottle	12	16.5 lbs.	



megabubble® Leak Detector

APPROVALS AND LISTINGS

MIL-L-25567D

SPECIFIC USES

Megabubble is used to detect gas leaks on pipelines, fittings, tanks, coils, cylinders, pressure vessels, valves, and other hard surfaces.

SPECIFIC APPLICATIONS*

Megabubble may be used to detect leaks of gas, air, compressed air, nitrogen, natural gas, refrigerants, CO2, and almost all other known gases.

-50° to +200°F.

Blue liquid, odorless

PHYSICAL PROPERTIES

Working temperature range: Appearance/color/odor:

WARNINGS OR CAUTIONS

- Read all cautions and directions carefully before using product.
- KEEP OUT OF REACH OF CHILDREN.

DIRECTIONS FOR USE

- Apply megabubble directly to pipe joint, solder joint, valve stem or any other part being checked.
- 2. Visually inspect all joints, fittings, gaskets, flanges, seams and corroded surfaces which may have perforation. Megabubble indicates where leaks are located. Very small leaks may need a minute or longer to produce a detectable bubble cluster.
- 3. Repeat if desired leak detection depends on careful inspection. Surfaces can be re-wetted and rechecked.
- 4. Do not dilute this product. Use directly from container.
- 5. If using dauber, keep free of dirt and foreign matter. If using spray and nozzle becomes clogged, remove and rinse with warm water.
- Remove excess megabubble residue with water spray or wipe off with damp rag.



MATERIAL SAFETY INFORMATION

FOR MORE INFORMATION ON THIS PRODUCT, REQUEST MATERIAL SAFETY DATA SHEET (MSDS) #59.

For Delivery by Fax	Call 1-800-942-4636
Internet	See MSDS section of www.herchem.com
Mail	Contact Hercules at address below or any Hercules representative

HMIS Hazard Warning 0-0-0-A

INGREDIENTS	CAS#
Propylene Glycol	57-55-6
NJ-T.S.R. #31348300 5002	P. 5060P. 5061P

*For special applications which may not be covered on this or other Hercules literature, please contact Hercules Technical Services Department by phone 1-800-221-9330, or fax 1-800-333-3456, or visit our technical database web-site at www.herchem.com.



Hercules Chemical Company, Inc.

111 South Street, Passaic, NJ 07055-9100 Phone: 800-221-9330 • Fax: 800-333-3456 e-mail: info@herchem.com http://www.herchem.com ISO 9001: 2000 Certified

