## **PFWG Series**



## **Water Test Gauge**



PFWG300L

## **Product Features**

- Accuracy : ± 2.5% of Span ( Grade B ANSI B40.1 )
- Black Corrosion Resistant Paint Steel Case with Flat Glass Window
- Dual Scale: psi/kPa
- CRN Registered : 0F13895.5C / 0F13897.5
- Operating Temperature : Ambient:  $-4^{\circ}\mathrm{F}$  to  $140^{\circ}\mathrm{F}$  ( $-20^{\circ}\mathrm{C}$  to  $60^{\circ}\mathrm{C}$  )

Media: max. 158°F (70°C)

- Bourden Tube Style except PFGG15K
- Water Test Gauge uses 3/4" NH Connection

✓ For Submittal	Model Number	Description	Diameter Face (in)	psi	kPa
	PFWG300L	Water Test Gauge	2-1/2 in	0-300#	0-2000#
	PFWGI300L	Water Test Gauge with Memory Pointer	2-1/2 in	0-300#	0-2000#

## Warranty and Codes

This PROFLO product carries a 1-year limited warranty.