

## 20-100: STANDARD PATTERN BRONZE WATER GAUGES



## **OVERVIEW**

Use for all types of liquid level verification; available with 3/8" or 1/2" NPT male pipe connections. Aluminum or plastic composition hand wheels; EPDM gauge glass gaskets standard. Other glass gaskets available. Automatic ball checks help prevent the loss of fluids should the glass be broken.

## **FEATURES**

- Ball checks standard on 20-150 models
- Equipped with two copper guard rods
- Standard 1/4" needle drain valve in lower arm
- Rated: 125 psig @ 350°F, 300 psig @ 100°F (See note!)
- CRN Registered OF6616.5C

Part	Pipe	Glass O.D.	Wt./100	
Number	Size (in.)	& Length	(lbs.)	Wheel Type
20-101	3/8	5/8 x 10	145	ALUMINUM
20-102	3/8	5/8 x 10	145	COMPOSITION
20-104	1/2	5/8 x 12	160	ALUMINUM
20-105	1/2	5/8 x 12	160	COMPOSITION
20-150*	1/2	5/8 x 12	160	ALUMINUM
20-151*	1/2	5/8 x 12	160	COMPOSITION

Note: Service ratings are subject to pressure/temperature ratings of gauge glass and glass gaskets.

\* Automatic ball valves

## **OPTIONS**

Suffix Number	Specification		
-00	Standard gauge w/ standard glass & rod		
-01	Top only		
-02	Bottom only		
-03	Standard gauge less glass & rod		
-10	For special gauges w/ non-standard glass and rod lengths		