Victaulic® FireLock NXT™ Dry Valve Series 768N





Patented

1.0 PRODUCT DESCRIPTION

Available Sizes:

• 1½ – 8" /40 – 200 mm

Pressure Class:

• Up to 300 psi/2068 kPa/20 Bar

Minimum Air Pressure:

• 13 psi/90 kPa/.90 Bar

Acutation Options:

- Series 776 Low Pressure Actuator
- Optional: Series 746-LPA Dry Accelerator

Valve Configurations:

- Bare
- Pre-trimmed: Completely assembled with all necessary trim components.
- Vic-Quick Riser: Pre-trimmed and includes:
 - Shut Off Valve (1 ½"/40 mm: Series 728 Ball Valve, 2" 8"/50 200 mm: Series 705 FireLock Butterfly Valve)
 - Pre-set high or low air and alarm pressure switches
 - Drain kit
- Fire-Pac Series 745 (refer to Victaulic submittal 30.23)

Pipe Preparation:

• Victaulic Original Groove System

Application/Media:

• For use on fire protection systems only.

2.0 CERTIFICATION/LISTINGS













NOTE

CCC approval for DN80, DN100, DN150, DN200.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.



3.0 SPECIFICATIONS - MATERIAL

Body: Ductile iron conforming to ASTM A536, grade 65-45-12.


Clapper: Aluminum bronze UNS-C95500 **Latch:** Aluminum bronze UNS-C95500

Shafts: Stainless 17-4

Clapper Seal: Peroxide cured EPDM, ASTM D2000

Bushings/Seat O-rings: Nitrile **Springs:** Stainless Steel (300 Series)

Diaphragm: Peroxide cured EPDM with fabric reinforcement



The 1½-inch/48.3-mm and 2-inch/60.3-mm valve sizes contain washers under the heads of the cover plate bolts.

Item	Description				
1	Valve Body				
2	Clapper				
3	Clapper Seal				
4	Seal Ring				
5	Seal Washer				
6	Seal Retaining Ring				
7	Seal Assembly Bolt				
8	Clapper Spring				
9	Clapper Shaft				
10	Clapper Shaft Bushing and O-Ring (Qty. 2)				

Item	Description				
11	Cover Plate				
12	Cover Plate Gasket				
13	Cover Plate Bolts				
14	Latch				
15	Latch Spring				
16	Latch Spring Bushing and O-Ring (Qty. 2)				
17	Diaphragm				
18	Diaphragm Cover				
19	Diaphragm Cover Cap Screws (Qty. 8)				
20	Latch Shaft				



3.0 SPECIFICATIONS - MATERIAL (CONTINUED)

Standard Trim Package:

- Series 776 Low Pressure Actuator The Series 776 Low Pressure Actuator is pneumatically actuated and requires only 13 psi/90 kPa minimum air pressure, regardless of the system supply pressure. This actuator allows the system to operate with a low air or gas pressure of 7 psi/48 kPa.
- All required pipe nipples and fittings standard galvanized finish
- All standard trim accessories
- All required gauges

Optional Trim Package: Black Trim for Foam Systems – If the valve is intended for use in a foam system, black trim must be ordered, per NFPA requirements. Specify this requirement on the order.

Optional Accessories:

Alarm Pressure Switch – Alarm Pressure Switches are designed to activate electrical alarms and control panels when a sustained flow of water occurs (such as with an open sprinkler). Included in VQR trim.

Air Supervisory Pressure Switch – Air Pressure Supervisory Switches are used to monitor low and high system air pressure and are factory pre-set. Included in VQR trim.

Series 746-LPA Dry Accelerator – The Series 746-LPA Dry Accelerator is required when the Series 768N Dry Valve is installed in large systems to improve response time. Refer to Victaulic submittal 30.64.

Series 760 Water Motor Alarm – The Series 760 Water Motor Alarm is a mechanical device that sounds when a sustained flow of water occurs (such as with an open sprinkler). Refer to Victaulic submittal 30.32.

Series 75B Supplemental Alarm Device – The Series 75B Supplemental Alarm Device is designed to provide a continuous alarm for systems equipped with a mechanical device. Refer to Victaulic submittal 30.33.

Series 75D Water Column Kit – The Series 75D Water Column Kit is designed to minimize residual water in the riser from collecting above the clapper. Refer to Victaulic submittal 30.34.

Air Supply System – The air supply system contains all components for establishing and maintaining air in the system. The compressor, low-pressure alarms, ball valves, and required trim are included in the air supply system.

3

Air Compressor (See page 6 for more on the Victaulic Series 7C7 Compressor Package)


Air Maintenance Trim Assembly

Fire Alarm Control Panels

Drain Connection Kit – Included in VQR option.



3.0 SPECIFICATIONS - MATERIAL (CONTINUED)




Item	Description				
1	Series 768N FireLock NXT Dry Valve				
2	FireLock Rigid Coupling				
3	Water Supply Main Control Valve				
4	Drip Cup				
5	Water Supply Main Drain Valve – Flow Test				
6	System Pressure Gauge/Gauge Valve Assembly				
7	System Main Drain Valve				
8	Series 746-LPA Dry Accelerator Assembly				
8a	Series 746-LPA Dry Accelerator ¼-Turn Vent Ball Valve				
8b	Series 746-LPA Dry Accelerator Isolation Ball Valve				
9	Air Supervisory Pressure Switch				
10	Air Manifold				
11	Series 776 Low-Pressure Actuator				
11a	Auto Vent Sleeve of Series 776 Low-Pressure Actuator				

Item	Description			
12	Charge Line Pressure Gauge/Gauge Valve Assembly			
13	Priming Manifold Assembly			
13a	Charge Line Ball Valve			
13b	Alarm Test Ball Valve			
13c	Auto Drain Sleeve			
14	Series 760 Water Motor Alarm Assembly			
15	Alarm Pressure Switch			
16	Alarm Manifold Assembly			
16a	Ball Drip Plunger			
17	Water Supply Pressure Gauge/Gauge Valve Assembly			
18	Victaulic Air Maintenance Trim Assembly (AMTA)			
18a	Slow-Fill Ball Valve of the Victaulic AMTA			
18b	Fast-Fill Ball Valve of the Victaulic AMTA			

31.80 8826 Rev N Updated 03/2021 © 2021 Victaulic Company. All rights reserved.



4.0 DIMENSIONS



Size	Dimensions						Weight						
												Approx.	(Each)
Nominal	Α	A1	В	С	D	D1	E	F	G	н	K	Without Trim	With Trim
inches	inches	inches	inches	inches	inches	inches	inches	inches	inches	inches	inches	lbs	lbs
DN	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	kg	kg
1½	9.00	16.37	31.50	9.25	15.25	10.00	9.25	3.25	10.25	21.75	6.00	16.7	43.0
DN40	228.60	415.80	800	235	387	254	235	83	260	552	152	7.6	19.5
2	9.00	13.83	31.50	9.25	16.25	10.00	9.25	3.25	10.25	21.75	6.00	17.0	43.0
DN50	228.60	351.28	800	235	413	254	235	83	260	552	152	7.7	19.5
2½	12.61	16.51	29.75	11.25	17.25	9.75	9.75	4.00	6.25	23.75	6.50	41.0	65.0
	320.29	419.35	756	286	438	248	248	102	159	603	165	18.7	29.5
76.1 mm	12.61	16.51	29.75	11.25	17.25	9.75	9.75	4.00	6.25	23.75	6.50	41.0	65.0
	320.29	419.35	756	286	438	248	248	102	159	603	165	18.7	29.5
3	12.61	16.51	29.75	11.25	17.25	9.75	9.75	4.00	6.25	23.75	6.50	41.0	65.0
DN80	320.29	419.35	756	286	438	248	248	102	159	603	165	18.7	29.5
4	15.03	19.85	31.50	13.50	20.00	11.25	11.00	4.75	4.50	25.75	8.00	59.0	95.0
DN100	381.76	504.19	800	343	508	286	279	121	114	654	203	26.7	43.0
165.1 mm	16.00	22.13	31.00	14.00	23.25	11.75	11.25	4.50	4.25	27.00	8.25	80.0	116.0
	406.40	562.10	787	356	591	298	286	114	108	686	210	36.2	52.6
6	16.00	22.13	31.00	14.00	23.25	11.75	11.25	4.50	4.25	27.00	8.25	80.0	116.0
DN150	406.40	562.10	787	356	591	298	286	114	108	686	210	36.2	52.6
8	17.50	23.02	32.75	14.75	25.75	12.50	12.25	4.75	4.25	29.00	9.25	122.0	158.0
DN200	444.50	584.71	832	375	654	318	311	121	108	737	235	55.3	71.6

NOTES

- The "A" dimension is the actual takeout dimension of the valve body.
- The "A1" dimension is the actual takeout dimension of the valve body with water supply main control valve.
- For systems with the optional Series 746-LPA Dry Accelerator, add 11.50 inches/292 mm to the "B" dimension to account for the additional height.
- The "D" and "D1" dimensions are not fixed measurements. The drip cup can be rotated to provide more clearance at the back of the trim.
- Components shown as dotted lines denote optional equipment.
- The recommended drain connection kit (shaded in orange) is for reference and takeout dimensions. This drain connection comes standard when the VQR assembly is ordered.




victaulic.com 5

5.0 PERFORMANCE

Hydraulic Friction Loss

The chart below expresses the flow of water at 65°F/18°C through an open valve.



Frictional Resistance

The chart below expresses the frictional resistance of Victaulic Series 768N FireLock NXT.

Dry Valve in equivalent feet of straight pipe.

Nominal Size	Actual Outside Diameter	Equivalent Length of Pipe
inches	inches	feet
DN	mm	meters
1 ½	1.900	3.00
DN40	48.3	0.914
2	2.375	9.00
DN50	60.3	2.743
21/2	2.875 73.0	8.00 2.438
76.1 mm	3.000 76.1	8.00 2.439
3	3.500	17.00
DN80	88.9	5.182
4	4.500	21.00
DN100	114.3	6.401
165.1 mm	6.500 165.1	22.00 6.706
6	6.625	22.00
DN150	168.3	6.706
8	8.625	50.00
DN200	219.1	15.240

Cv Values:

Cv values for flow of water at $+60^{\circ}F/+16^{\circ}C$ through a fully open valve are shown in the table below.

Formulas for Cv values

 $\Delta P = Q^2/Cv^2$ $Q = Cv \times \sqrt{\Delta}P$

Where:

Flow Coefficient	Cv
Q (Flow)	GPM
ΔP (Pressure Drop)	psi

Valve	Size	Full Open
Nominal Size	Actual Outside Diameter	Flow Coefficient
inches	inches	Cv
DN	mm	K _v
1 ½	1.900	60
DN40	48.3	52.0
2	2.375	110
DN50	60.3	95.0
2 1/2	2.875	180
	73.0	156.0
76.1 mm	3.000	180
70.1 mm	76.1	156.0
3	3.500	200
DN80	88.9	173.0
4	4.500	350
DN100	114.3	302.8
165.1 mm	6.500	1000
105.111111	165.1	865.0
6	6.625	1000
DN150	168.3	865.0
8	8.625	1500
DN200	219.1	1499.1



5.0 PERFORMANCE (CONTINUED)

Air Supply Requirements

- Minimum: 13 psi/90 kPA/.9 Bar regardless of the system water pressure
- Maximum Recommended: 18 psi/124 kPa/1.24 Bar
- Multiple Series 768N FireLock NXT Dry Valves with a common air supply:
 - Isolate systems with a Victaulic spring –loaded, soft-seated ball check valve to ensure air integrity and serviceability of each system.
- Sizing the compressor:
 - Engineer/system designer is responsible
 - Entire system must be charged to the required air pressure within 30 minutes to meet NFPA requirements
 - An oversized compressor will slow down or possibly prevent valve operation
 - Compressor filling the system too fast:
 - May be necessary to restrict the air supply
 - Ensure that air exhausted from an open sprinkler or manual release valve is not replaced by the air supply system as fast as it is exhausted
- Compressor Requirements
 - Base or Riser Mounted Compressors:
 - "On" or "low" pressure setting: 13 psi/90 kPA/.9 Bar
 - "Off" or "high" pressure setting: 18 psi/124 kPa/1.24 Bar
 - Victaulic Series 7C7 riser mounted and pre-set for pressure requirements (refer to Victaulic <u>submittal 30.22</u>).
 - If the compressor is not equipped with a pressure switch, the Series 757P Air Maintenance Trim Assembly with pressure switch should be installed (refer to Victaulic <u>submittal 30.36</u>).
- Shop Air or Tank-Mounted Air Compressors:
 - Series 757 Regulated Air Maintenance Trim Assembly should be installed (refer to Victaulic <u>submittal 30.35</u>)
 - 13 psi/90 kPA/.9 Bar should be used as the set point for the air regulator
 - The compressor cut-in (turn-on) pressure setting should be at least 5 psi/34kPa/34 Bar above the set point of the air regulator.
 - Exploded View Trim: Series 757 Regulated Air Maintenance Trim Assembly (refer to Victaulic <u>submittal 30.35</u>)
- Compressor Requirements and settings for systems installed with series 746 or series 746-LPA dry accelerators
 - A tank-mounted air compressor with a Series 757 Regulated AMTA must be used to supply air to system installed with a Series 746 or Series 746-LPA Dry Accelerator.
 - In the event a compressor becomes inoperative, a properly sized tank-mounted air compressor provides the greatest protection, since air can be supplied continuously to the sprinkler system for an extended time period.



<u>victaulic.com</u> 7

6.0 NOTIFICATIONS

WARNING













- Read and understand all instructions before attempting to install, remove, adjust, or maintain any Victaulic piping products.
- Depressurize and drain the piping system before attempting to install, remove, adjust, or maintain any Victaulic piping products.
- Wear safety glasses, hardhat, and foot protection.

Failure to follow these instructions could result in death or serious personal injury and property damage.

7.0 REFERENCE MATERIALS

30.35: FireLock™ Air Maintenance Trim Assembly Series 757 Submittal

30.36: FireLock™ Air Maintenance Trim Assembly Series 757P Submittal

30.22: FireLock® Compressor Package Series 7C7 Submittal

30.32: FireLock™ Water Motor Alarm Series 760 Submittal

30.64: FireLock™ Dry Accelerator Series 746-LPA

30.65: FireLock™ Low Pressure Actuator Series 776 Submittal

I-768N: FireLock NXT™ Dry Valve Series 768N Installation Manual

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be constructed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installatio

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.

31.80 8826 Rev N Updated 03/2021 © 2021 Victaulic Company. All rights reserved.

