

For Residential and Commercial Applications


Job Name		Engineer / Architect	
Job Location		Wholesaler	
Submittal Date		Contractor	

46 Series Flare x Female Iron Pipe Adapter

Use: For use with fuel, oil, liquefied petroleum (LP) and natural gas lines. Designed for use with aluminum, copper, brass and welded steel tubing that can be flared.

Design Features:

- **Recommended for higher pressures** than those covered by compression fittings
- **Resist mechanical pull out**
- **Available in a broad range of sizes**



Operating Specifications:

Temperature: -65° - 250° F at maximum operating pressures

Working Pressure: see chart below

Vibration: Good vibration resistance*



*Recommend long flare nuts when greater vibration resistance is required

MAXIMUM WORKING PRESSURES										
Service Conditions	Tube O.D.	Type of Tubing and Wall Thickness (Inches)								
		Copper – Dead Soft (Seamless)					Copper – Half Hard (Seamless)			
		.030"	.032"	.035"	.049"	.065"	.032"	.035"	.042"	.049"
Safety Factor 4-1	1/8	4300		5000			5000			
	3/16	2850		3300			3400			
	1/4	2100	2250	2500			2500			
	5/16		1800	2000			2000			
	3/8		1500	1650			1700	1850		
	1/2		1100	1250		2000	1250	1400		2600
	5/8			1000	1400	1800	1000			1500
	3/4			850	1150	1500			1100	1700
Safety Factor 6-1	7/8									1100
	1/8	2800		3350			3400			
	3/16	1900		2200			2250			
	1/4	1430	1500	1650			1700			
	5/16		1200	1300			1350			
	3/8		100	1100			1100	1200		
	1/2		750	825		1550	850	925		1750
	5/8			650	930	1200	675			1000
	3/4			550	775	1000			725	1100
	7/8									750

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®

41S Series Flare Nuts - Short

MATERIAL SPECIFICATIONS	
Fitting Body	C36000 brass

Part Listing:

☐	46-3-2	3/16" OD Flare x 1/8" F.I.P.
☐	46-3-2 B	3/16" OD Flare x 1/8" F.I.P., bulk
☐	46-4-2	1/4" OD Flare x 1/8" F.I.P.
☐	46-4-2 B	1/4" OD Flare x 1/8" F.I.P., bulk
☐	46-4-4	1/4" OD Flare x 1/4" F.I.P.
☐	46-4-4 B	1/4" OD Flare x 1/4" F.I.P., bulk
☐	46-4-6	1/4" OD Flare x 3/8" F.I.P.
☐	46-4-6 B	1/4" OD Flare x 3/8" F.I.P., bulk
☐	46-4-8	1/4" OD Flare x 1/2" F.I.P.
☐	46-5-2 B	5/16" OD Flare x 1/8" F.I.P., bulk
☐	46-5-4	5/16" OD Flare x 1/4" F.I.P.
☐	46-5-4 B	5/16" OD Flare x 1/4" F.I.P., bulk
☐	46-6-2	3/8" OD Flare x 1/8" F.I.P.
☐	46-6-2 B	3/8" OD Flare x 1/8" F.I.P., bulk
☐	46-6-4	3/8" OD Flare x 1/4" F.I.P.
☐	46-6-4 B	3/8" OD Flare x 1/4" F.I.P., bulk
☐	46-6-4WN	3/8" OD Flare x 1/4" F.I.P. with flare nut - short
☐	46-6-6	3/8" OD Flare x 3/8" F.I.P.
☐	46-6-6 B	3/8" OD Flare x 3/8" F.I.P., bulk
☐	46-6-6WN	3/8" OD Flare x 3/8" F.I.P. with flare nut - short
☐	46-6-8	3/8" OD Flare x 1/2" F.I.P.
☐	46-6-8 B	3/8" OD Flare x 1/2" F.I.P., bulk
☐	46-6-8WN	3/8" OD Flare x 1/2" F.I.P. with flare nut - short
☐	46-6-12	3/8" OD Flare x 3/4" F.I.P.
☐	46-6-12 B	3/8" OD Flare x 3/4" F.I.P., bulk
☐	46-8-4	1/2" OD Flare x 1/4" F.I.P.
☐	46-8-4 B	1/2" OD Flare x 1/4" F.I.P., bulk
☐	46-8-6	1/2" OD Flare x 3/8" F.I.P.
☐	46-8-6 B	1/2" OD Flare x 3/8" F.I.P., bulk
☐	46-8-6WN	1/2" OD Flare x 3/8" F.I.P. with flare nut - short
☐	46-8-8	1/2" OD Flare x 1/2" F.I.P.
☐	46-8-8 B	1/2" OD Flare x 1/2" F.I.P., bulk
☐	46-8-12	1/2" OD Flare x 3/4" F.I.P.
☐	46-8-12 B	1/2" OD Flare x 3/4" F.I.P., bulk
☐	46-10-6	5/8" OD Flare x 3/8" F.I.P.
☐	46-10-6 B	5/8" OD Flare x 3/8" F.I.P., bulk


41S Series Flare Nuts – Short

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®

Part Listing:

☐	46-10-8	5/8" OD Flare x 1/2" F.I.P.
☐	46-10-8 B	5/8" OD Flare x 1/2" F.I.P., bulk
☐	46-10-8WN	5/8" OD Flare x 1/2" F.I.P. with flare nut - short
☐	46-10-12	5/8" OD Flare x 3/4" F.I.P.
☐	46-10-12 B	5/8" OD Flare x 3/4" F.I.P., bulk
☐	46-12-8	3/4" OD Flare x 1/2" F.I.P.
☐	46-12-8 B	3/4" OD Flare x 1/2" F.I.P., bulk
☐	46-12-12	3/4" OD Flare x 3/4" F.I.P.
☐	46-14-12	7/8" OD Flare x 3/4" F.I.P.



PART DIMENSIONS (Inches)			
Model	Straight Threads	DIM. A	HEX. B
46-3-2	3/8-24	.95	9/16
46-4-2	7/16-20	1.03	9/16
46-4-4	7/16-20	1.09	5/8
46-4-6	7/16-20	1.25	13/16
46-4-8	7/16-20	1.20	7/8
46-5-2	1/2-20	1.05	9/16
46-5-4	1/2-20	1.25	11/16
46-6-2	5/8-18	1.25	11/16
46-6-4	5/8-18	1.09	11/16
46-6-6	5/8-18	1.00	5/8
46-6-8	5/8-18	1.31	15/16

PART DIMENSIONS (Inches)			
Model	Straight Threads	DIM. A	HEX. B
46-6-12	5/8-18	1.39	1-1/8
46-8-4	3/4-16	1.41	3/4
46-8-6	3/4-16	1.06	13/16
46-8-8	3/4-16	1.19	15/16
46-8-12	3/4-16	1.55	1-1/8
46-10-6	7/8-14	1.59	1-1/8
46-10-8	7/8-14	1.60	1-1/8
46-10-12	7/8-14	1.62	1-1/8
46-12-8	1-1/16-14	1.75	1-3/16
46-12-12	1-1/16-14	1.75	1-3/16
46-14-12	1-1/4-12	1.94	1-5/16

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

BrassCraft®