3M Scotch-WeldTM Rubber Toughened Instant Adhesives RT300B \cdot RT3500B

Technical Data	May, 2011
Product Description	3M TM Scotch-Weld TM Rubber Toughened Instant Adhesives are formulated with a unique elastomer that maximizes impact, vibration, peel, and thermal cycling resistance while providing tough flexible bonds. These adhesives are ideally suited for bonding flexible substrates and dissimilar materials.
Specific Features	• 3M [™] Scotch-Weld [™] Rubber Toughened Instant Adhesive RT300B (formerly PR80) is a medium viscosity black, rubber toughened cyanoacrylate.
	• 3M TM Scotch-Weld TM Rubber Toughened Instant Adhesive RT3500B (formerly PR10) is a high viscosity, black, rubber toughened cyanoacrylate. It is formulated to provide a more flexible bond than standard cyanoacrylates and has good gap-filling capabilities.

$3M^{\text{TM}} Scotch-Weld^{\text{TM}}$ **Rubber Toughened Instant Adhesives**

RT300B • RT3500B

Typical Uncured Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	3M™ Scotch-Weld™ Rubber Toughened Instant Adhesives	
-	RT300B	RT3500B
Color	Black	Black
Base	Ethyl Hybrid	Ethyl Hybrid
Appearance	Liquid	Liquid
Specific Gravity (g/ml)	1.1	1.1
Viscosity (cps)	300 - 1,000 ³	1,000 - 3,000 ¹ 5,000 - 10,000 ²
Time to Handling Strength (sec)	20 - 50	20 - 90
Full Cure Time (hr)	24	24

¹Brookfield RVT, #3 spindle @ 20 rpm.

²Brookfield RVT, #3 spindle @ 2.5 rpm.

³Brookfield LFT, #2 spindle.

Note: The following technical information and data should be considered representative or **Typical Cured** typical only and should not be used for specification purposes. **Properties**

	3M™ Scotch-Weld™ Rubber Toughened Instant Adhesives	
	RT300B	RT3500B
Continuous Temperature Range (°F)	-65 to 200	-65 to 200
Intermittent Temperature Range (°F)	-65 to 250	-65 to 250
Gap Fill (in)	0.004	0.008
Overlap Shear Strength (psi)⁴	1,500	1,300

⁴ASTM D1002 (grit-blasted steel).

$\begin{array}{l} \textbf{3M}^{\text{TM}} & \textbf{Scotch-Weld}^{\text{TM}} \\ \textbf{Rubber Toughened Instant Adhesives} \\ \text{RT300B} \bullet \text{RT3500B} \end{array}$

Handling Information	 Surface Preparation For optimum strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. However, the amount of surface preparation depends on the required bond strength and the environmental aging resistance desired by the user. Typical quick surface preparation would include wiping with a clean solvent (such as isopropyl alcohol*), abrading the surface with a clean fine abrasive, and then wiping again with a clean solvent to remove loose particles. Directions for Use 			
	3. Bond speed is typically very fast so ensure that parts are properly aligned before dispensing.			
	4. Product is normally hand applied from the bottle. Apply sparingly to one surface and press parts firmly together until handling strength is achieved. As a general rule, as little cyanoacrylate as possible should be used. Over application will result in slower cure speed and lower bond strength.			
	Cured Bond Characteristics 1. Full bond strength will typically be achieved within a 24 hour cure time.			
	 Low humidity or low temperature conditions will slow down the cure rate. After curing, 3MTM Scotch-WeldTM Rubber Toughened Instant Adhesive bonds are suitable for use at temperatures up to 200F (93°C) continuously, intermittently up to 250°F (121°C). At 220°F (105°C) the bond will be approximately 40% of the strength at room temperature. 			
	 Cyanoacrylate bond resistance to most oils and solvents is excellent. Long term humidity, moisture, or water immersion may affect the strength of a cured cyanoacrylate bond depending on the substrates and the bond gap. Testing is recommended to evaluate the effect. 			
	*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.			
	Storage	For short term storage (<30 days), keep adhesive in a cool (60°F to 80°F [16°C to 27°C]), dry place out of direct sunlight. Keep containers tightly covered and free of moisture. Refrigeration (40°F [4°C]) gives optimum long term storage stability.		
Shelf Life	3M [™] Scotch-Weld [™] Rubber Toughened Instant Adhesives can be expected to have a shelf life of six months from the date of shipment from 3M when stored under refrigerated conditions.			

$3M^{\text{TM}} Scotch-Weld^{\text{TM}}$ **Rubber Toughened Instant Adhesives**

RT300B • RT3500B

Precautionary Information	Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 800-362-3550 • 877-369-2923 (Fax) www.3M.com/industrial



3M and Scotch-Weld are trademarks of 3M Company. Printed in U.S.A. ©3M 2011 78923671594 (5/11)