


## 12,000 BTU/H SINGLE ZONE OUTDOOR UNIT

SUBMITTAL COVER SHEET

#### 



CAPACITIES		
Cooling Capacity (BTU/hr)	Rated <sup>1</sup>	12000
	Minimum	3800
	Maximum	12800
Heating Capacity (BTU/hr)	Rated <sup>2</sup>	12000
	Minimum	4500
	Maximum	13100

EFFICIENCY DATA	
SEER	21.5
EER	14.0
HSPF	11.5

#### **PRODUCT FEATURES**

- Variable Speed Inverter Compressor
- Auto Restart
- Base Pan Heater

OUTDOOR TEMPERATURE OPERATION	
Cooling	–13 °F – 122 °F (–25° C – 50° C)
Heating	–13 °F – 86 °F (–25° C – 30° C)

ELECTRICAL DATA		
Voltage/Phase/Frequency	208–230V, 1 Phase, 60 Hz	
Voltage Range	187-253V	
Recommended Breaker (Amps)	15	
Minimum Circuit Ampacity (Amps)	12	
Minimum Wire Size	16 AWG	
Rated Current - Cooling (Amps) <sup>1</sup>	4.05	
Rated Current - Heating (Amps) <sup>2</sup>	4.72	

<sup>1</sup>Measured at 95 °F. <sup>2</sup>Measured at 47 °F.





# 12,000 BTU/H SINGLE ZONE OUTDOOR UNIT

SPECIFICATIONS - DRA1U12S1A

S	YST	ΈM	DA <sup>-</sup>	ΓА	

STSTEMDATA	
Refrigerant Type	R-410A
Refrigerant Charge (oz.)	40.6
Oil Type	VG74
Oil Charge (oz.)	12.5 (370 ml)
Design Pressure (PSIG)	550/340

LINE SET REQUIREMENTS		
Connection Type	Flare	
Liquid	Ø1/4" (Ø6.35mm)	
Gas	Ø1/2" (Ø12.7mm)	
Pre-Charge Length	25'	
Maximum Length	82'	
Minimum Length (One Indoor Unit)	10'	
Max. Height Differential Between Indoor and Outdoor Unit	33'	
Additional Refrigerant (oz/ft)	0.16	

OUTDOOR UNIT FAN DATA	
Airflow (CFM)	1176
Sound Pressure (dB(A))	55
Туре	DC
RLA (A)	0.4


# OUTDOOR UNIT DIMENSIONS Unit Dimensions Width 31 1/2" Depth 13 1/8" Height 21 13/16"


	Height	21 15/10
Carton Dimensions	Width	36"
	Depth	15 3/8"
	Height	24 1/2"
Net Weight	80.5 lbs.	
Gross Weight	86.2 lbs.	


### 12,000 BTU/H SINGLE ZONE OUTDOOR UNIT




ODU DIMENSIONS - DRA1U12S1A









ΝΟΤΕ

Illustrations in this document are for explanatory purposes. The actual shape of your mini-split equipment may vary slightly.