



Class 3 Zipper Front Hooded Sweatshirt

Stock Number - S78122	Compliance Standards: ANSI/ISEA 107 Type R, Class 3
	Garment Detail: Sweatshirts are set-in sleeve construction with full cut shoulder and 180 degree sleeve-to-body angle. Sweatshirt has black elasticized knit sleeve cuffs and waist, zipper front, attached two-ply 3 panel hood with drawcord, and two black front handwarmer pockets.

Garment Type: High visibility zipper front hooded sweatshirt.	Reflective Tape: ANSI/ISEA 107 compliant 2" silver glass bead tape.
Sizes: S, M, L, XL, 2X, 3X, 4X, 5X	
Color: Fluorescent Yellow-Green / Black	Configuration: Harness tape layout with 1 horizontal band on body and 2 bands on each sleeve.
Material: Fluorescent yellow-green material is 8.4 oz. 100% Polyester. Black material is 8.4 oz. 100% Polyester.	Labels/Tags: 1. Woven label sewn at neck displays Tingley logo and size. 2. Printed hangtag with style, size, and UPC bar code. 3. Label sewn into left front hem displays stock number. Care instructions, fabric composition, lot and date codes are located on the reverse.
Seam Construction: Stitched.	
Closure Type: Zipper front.	Packaging: Side loaded vented polyethylene bag
Pockets: 1. Two black handwarmer pockets on sizes M-5X 2. Two fluorescent yellow-green pockets on size Small to conform to ANSI/ISEA 107 minimum background requirements for Type R, Class 3 garments.	Other:

Dimensions	S	M	L	XL	2X	3X	4X	5X
Chest	42"	46"	50"	54"	58"	62"	66"	70"
Length	28"	29"	29.5"	30"	31"	32"	33"	34"
Sleeve Length	34"	35.5"	36.5"	37.5"	38"	38.5"	39.5"	40"

Case Pack: 12 each	
Case Dimensions / Weight:	
S = 23"(L) X 14"(W) X 15"(H) / 21 lbs.	2X = 25"(L) X 16"(W) X 15"(H) / 27 lbs.
M = 23"(L) X 14"(W) X 15"(H) / 23 lbs.	3X = 25"(L) X 16"(W) X 15"(H) / 28 lbs.
L = 23"(L) X 14"(W) X 15"(H) / 24 lbs.	4X = 27"(L) X 17"(W) X 15"(H) / 29 lbs.
XL = 25"(L) X 16"(W) X 15"(H) / 25 lbs.	5X = 27"(L) X 17"(W) X 15"(H) / 31 lbs.