


24,000 BTU/H SINGLE ZONE OUTDOOR UNIT

SUBMITTAL COVER SHEET

DDG JEGT NAME	
PROJECT NAME	
LOCATION	
ARCHITECT	
ENGINEER	
CONTRACTOR	
REFERENCE	
SUBMITTED BY	DATE



CAPACITIES		
Cooling Capacity (BTU/hr)	Rated ¹	24000
	Minimum	6850
	Maximum	24500
Heating Capacity (BTU/hr)	Rated ²	25000
	Minimum	7200
	Maximum	27500

EFFICIENCY DATA	
SEER	21.5
EER	12.5
HSPF	11.0

PRODUCT FEATURES

- Variable Speed Inverter Compressor
- Auto Restart
- Base Pan Heater

OUTDOOR TEMPERATURE OPERATION	
Cooling	–13 °F – 122 °F (–25° C – 50° C)
Heating	–13 °F – 86 °F (–25° C – 30° C)

ELECTRICAL DATA		
Voltage/Phase/Frequency	208–230V, 1 Phase, 60 Hz	
Voltage Range	187-253V	
Recommended Breaker (Amps)	25	
Minimum Circuit Ampacity (Amps)	18	
Minimum Wire Size	16 AWG	
Rated Current – Cooling (Amps) ¹	8.4	
Rated Current - Heating (Amps) ²	10.1	

¹Measured at 95 °F.

 $^{^2}$ Measured at 47 °F.







24,000 BTU/H SINGLE ZONE OUTDOOR UNIT

SPECIFICATIONS - DRA1U24S1A

SYSTEM DATA	
Refrigerant Type	R-410A
Refrigerant Charge (oz.)	82.9
Oil Type	VG74
Oil Charge (oz.)	22.7 (670 ml)
Design Pressure (PSIG)	550/340

LINE SET REQUIREMENTS		
Connection Type	Flare	
Liquid	Ø3/8" (Ø9.52mm)	
Gas	Ø5/8" (Ø15.9mm)	
Pre-Charge Length	25'	
Maximum Length	164'	
Minimum Length (One Indoor Unit)	10'	
Max. Height Differential Between Indoor and Outdoor Unit	82'	
Additional Refrigerant (oz/ft)	0.32	


OUTDOOR UNIT FAN DATA	
Airflow (CFM)	2235
Sound Pressure (dB(A))	61
Туре	DC
RLA (A)	0.6


OUTDOOR UNIT DIMENSIONS		
Unit Dimensions	Width	37 1/4"
	Depth	16 1/8"
	Height	31 7/8"
Carton Dimensions	Width	42 15/16"
	Depth	19 11/16"
	Height	34 1/8"
Net Weight	141.1 lbs.	
Gross Weight	152.1 lbs.	





24,000 BTU/H SINGLE ZONE OUTDOOR UNIT

ODU DIMENSIONS - DRA1U24S1A











NOTE

Illustrations in this document are for explanatory purposes. The actual shape of your mini–split equipment may vary slightly.

3