

REFRIGERATION

Undercounter/Freestanding 15"W. Ice Machine



Standard Features & Accessories

All models include

- Produces up to 65 lbs. of clear ice per day
- 26 lb. capacity ice bin
- 1" x 1-1/8" x 1-1/4" cube size
- LED light
- LED control panel
 - O Power On/Off
 - Check water alert
 - O Time to clean alert
- Water quality sensor

- Stainless steel exterior cabinet
- Tru-Flush™ design
- Agency certified for outdoor use
- Self-closing door
- 90° door stop option
- Black kickplate with stainless steel cover
- Adjustable leveling legs

Model Options



FGIM515/FPIM515 Professional Door Panel (PIDP15)

FINISH DETAILS FOR FGIM/FPIM MODEL

- Accepts optional Professional door panel
- Professional door panel available in stainless steel (SS)
- Professional door panels must be ordered left hinge (LH) or right hinge (RH)



FGIM515/FPIM515 Designer Door Panel (DIDP15)

FINISH DETAILS FOR FGIM/FPIM MODEL

- Accepts optional Designer door panel
- Designer door panel available in stainless steel (SS)
- Designer door panels must be ordered left hinge (LH) or right hinge (RH)



FGIM515/FPIM515 Custom Panel

FINISH DETAILS FOR FGIM/FPIM MODEL

- Handle not included—opt for custom handle, or purchase a Viking Professional Series or Designer Series handle kit (see Installation Notes & Accessories).
- Accepts 3/4"-thick custom wood front
- See Custom Panels section for more information and additional specifications.



REFRIGERATION 🛠

Undercounter/Freestanding 15"W. Ice Machine



Please see
Installation Notes &
Accessories
for important
information,
including drain
pump and handle
kits.

Dimensions & Specifications

PRODUCT DIMENSIONS



FGIM515/FPIM515 Professional Door Panel (PIDP15)




FGIM515/FPIM515 Designer Door Panel (DIDP15)



FGIM515/FPIM515 Custom Panel

See **Custom Panels** section for more information and additional specifications.



	FGIM515	All Models	FPIM515
Overall width	14-7/8" (37.8 cm)		
Overall height	33-7/8" (86.0 cm) min. to 34-7/8" (88.6 cm) max.		
Overall depth (from rear)			
To front of handle	25-1/4" (64.1 cm)		
With door open		37-3/4" (95.9 cm)	
Approx. ship weight	113 lbs. (51.2 kg)		118 lbs. (53.5 kg)







Dimensions & Specifications

DOOR SWING



FGIM515/FPIM515 Professional Door Panel (PIDP15)





FGIM515/FPIM515 Designer Door Panel (DIDP15)




FGIM515/FPIM515 Custom Panel

See **Custom Panels** section for more information and additional specifications.











REFRIGERATION A

Undercounter/Freestanding 15"W. Ice Machine



UTILITY REQUIREMENTS



Not applicable



ELECTRICAL

- 6' (1.8 m), 3-wire cord with grounded, 3-prong plug attached to product
- 115V/60 Hz; 15amp dedicated circuit
- Max. amp usage-5.0



PLUMBING

- Inlet waterline requirements-1/4" (0.64 cm) OD copper tubing
- 20 psi min.; 80 psi max.

Installation Requirements

ACCESS REQUIREMENTS



FGIM515/FPIM515 **Professional Door Panel** (PIDP15)




FGIM515/FPIM515 Designer Door Panel (DIDP15)



FGIM515/FPIM515 **Custom Panel**

See Custom Panels section for more information and additional specifications.



	All models		
Cutout width	15" (38.1 cm)		
Cutout height	34-1/4" (86.4 cm) min. to 35-1/4" (89.5 cm) max.		
Cutout depth	24" (61.0 cm)		



REFRIGERATION Undercounter/Freestanding 15"W. Ice Machine



Installation Notes & Accessories

Door Panel Kits

- For use with custom panel ice machine
- Kit includes one door panel and installation hardware
 Order "R" for right hinge or "L" for left hinge

Model	Description	Approx. ship wt. lbs. (kg)
PIDP15L-SS	Professional door panel LH (Stainless Steel)	14 (6.3)
PIDP15R-SS	Professional door panel RH (Stainless Steel)	14 (6.3)
DIDP15L-SS	Designer door panel LH (Stainless Steel)	14 (6.3)
DIDP15R-SS	Designer door panel RH (Stainless Steel)	14 (6.3)

Handle Kits

- For use with custom panel ice machine
- For use on locally supplied custom panel
- Handles allow custom panel products to coordinate with other Professional and Designer products
- Kit includes one handle and installation hardware

Model	Description	Approx. ship wt. lbs. (kg)
PHK30-SS	Professional handle (Stainless Steel)	6 (2.7)
DDHK29-SS	Designer handle (Stainless Steel)	5 (2.3)

Drain Pump Kit

• For use with FGIM ice machine when floor drain is not available

Model	Description	Approx. ship wt. lbs. (kg)
DP-FGIM	Drain pump	2 (0.9)

Compliance Information



WARRANTY SUMMARY*

- Two-year full warranty—complete unit
- Six-year full warranty—sealed refrigeration system (includes compressor, condenser, dryer/strainer, evaporator, and connecting tubing)
- Twelve-year limited warranty—sealed refrigeration system
- Ninety-day limited warranty—cosmetic parts such as glass, painted, and decorative items

^{*}For complete warranty see Use & Care Guide. Warranty valid on Viking products shipped within the United States and Canada.

