Date Printed: 1/12/2022 Page 1 / 6

Safety Data Sheet



* Trusted Quality Since 1921 * www.rustoleum.com

1. Identification

IC LSPR 12PK FLUORESCENT PURPLE **Product Name:**

MARKING

Product Identifier: 1669838V

Recommended Use: Marking Paint

Rust-Oleum Corporation Supplier:

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Rust-Oleum Canada (ROCA) 200 Confederation Parkway Concord, ON L4K 4T8

Canada

Emergency Phone: 800-387-3625

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700 **Revision Date:** 1/11/2022

Supercedes Date: 5/13/2021

Rust-Oleum Corporation Manufacturer:

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

2. Hazards Identification

Classification

Symbol(s) of Product



Signal Word

Danger

Possible Hazards

46% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

Carcinogenicity, category 1B

Flammable Aerosol, category 1 H222 Extremely flammable aerosol. H317 May cause an allergic skin reaction. Skin Sensitizer, category 1 H340

Germ Cell Mutagenicity, category 1A May cause genetic defects. H350

Effects on or via Lactation H362 May cause harm to breast-fed children.

Gases under Pressure; Compressed Gas H280 Contains gas under pressure; may explode if heated.

GHS LABEL PRECAUTIONARY STATEMENTS

P201 Obtain special instructions before use.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. NO

May cause cancer.

SMOKING.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

P260 Do not breathe dust/fume/gas/mist/vapors/spray. Date Printed: 1/12/2022 Page 2 / 6

P263 Avoid contact during pregnancy/while nursing.

P264 Wash hands thoroughly after handling.

P272 Contaminated work clothing should not be allowed out of the workplace.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P321 For specific treatment see label.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local, regional and national regulations.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.
P308+P313 IF exposed or concerned: Get medical advice/attention.
P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
P410+P403 Protect from sunlight. Store in a well-ventilated place.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C (122°F).

GHS SDS PRECAUTIONARY STATEMENTS

P270 Do not eat, drink or smoke when using this product.

P363 Wash contaminated clothing before reuse.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	CAS-No.	<u>Wt.%</u>	GHS Symbols	GHS Statements
Naphtha, Petroleum, Hydrotreated Light	64742-49-0	18	GHS08	H304
Propane	74-98-6	17	GHS04	H280
Hydrous Magnesium Silicate	14807-96-6	8.5	Not Available	Not Available
n-Butane	106-97-8	8.0	GHS04	H280
Acetone	67-64-1	7.1	GHS02-GHS07	H225-319-332-336
n-Butyl Acetate	123-86-4	3.6	GHS02-GHS07	H226-336
Hydrotreated Light Distillate	64742-47-8	2.6	GHS08	H304
Xylenes (o-, m-, p- Isomers)	1330-20-7	1.5	GHS02-GHS07	H226-315-319-332
n-Heptane	142-82-5	1.0	GHS02-GHS07- GHS08	H225-304-315-336
Octane	111-65-9	1.0	GHS02-GHS07- GHS08	H225-304-315-336
Polymer Resin	PROPRIET ARY	0.7	GHS08	H340-362-373
Stoddard Solvent	8052-41-3	0.5	GHS06-GHS08	H304-331-372
Ethylbenzene	100-41-4	0.4	GHS02-GHS07- GHS08	H225-304-332-351-373
Methyl Ethyl Ketoxime	96-29-7	0.1	GHS05-GHS06- GHS07-GHS08	H302-312-315-317-318-331-336 -350-370-373

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

Date Printed: 1/12/2022 Page 3 / 6

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: Water spray may be ineffective. Closed containers may explode when exposed to extreme heat due to buildup of steam. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN -7°C (20°F). EXTREMELY FLAMMABLE LIQUID AND VAPOR!

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Full protective equipment including self-contained breathing apparatus should be used. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120°F (49°C). Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL- TWA	OSHA PEL- CEILING
Naphtha, Petroleum, Hydrotreated Light	64742-49-0	20.0	N.E.	N.E.	N.E.	N.E.
Propane	74-98-6	20.0	N.E.	N.E.	1000 ppm	N.E.
Hydrous Magnesium Silicate	14807-96-6	10.0	2 mg/m3	N.E.	N.E.	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Acetone	67-64-1	10.0	250 ppm	500 ppm	1000 ppm	N.E.
n-Butyl Acetate	123-86-4	5.0	50 ppm	150 ppm	150 ppm	N.E.
Hydrotreated Light Distillate	64742-47-8	5.0	N.E.	N.E.	N.E.	N.E.
Xylenes (o-, m-, p- Isomers)	1330-20-7	5.0	100 ppm	150 ppm	100 ppm	N.E.
n-Heptane	142-82-5	5.0	400 ppm	500 ppm	500 ppm	N.E.
Octane	111-65-9	5.0	300 ppm	N.E.	500 ppm	N.E.
Polymer Resin	PROPRIETARY	1.0	N.E.	N.E.	N.E.	N.E.
Stoddard Solvent	8052-41-3	1.0	100 ppm	N.E.	500 ppm	N.E.
Ethylbenzene	100-41-4	1.0	20 ppm	N.E.	100 ppm	N.E.
Methyl Ethyl Ketoxime	96-29-7	1.0	10 ppm	N.E.	N.E.	N.E.

PERSONAL PROTECTION

Date Printed: 1/12/2022 Page 4 / 6

ENGINEERING CONTROLS: Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits. Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance:	Aerosolized Mist	Physical State:	Liquid
Odor:	Solvent Like	Odor Threshold:	N.E.
Specific Gravity:	0.869	рН:	N.A.
Freeze Point, °C:	N.D.	Viscosity:	N.D.
Solubility in Water:	Slight	Partition Coefficient, n-octanol/	N.D.
Decomposition Temp., °C:	N.D.	water:	N.D.
Boiling Range, °C:	-37 - 537	Explosive Limits, vol%:	0.9 - 13.0
Flammability:	Supports Combustion	Flash Point, °C:	-96
Evaporation Rate:	Faster than Ether	Auto-Ignition Temp., °C:	N.D.
Vapor Density:	Heavier than Air	Vapor Pressure:	N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

Hazardous Decomposition: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: No Information

EFFECTS OF OVEREXPOSURE - INHALATION: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation. Constituents of this product include crystalline silica dust which ,if inhalable, can may cause silicosis, a form of progressive pulmonary fibrosis. Inhalable crystalline silica is listed by IARC as a group I carcinogen (lung) based on sufficient evidence in occupationally exposed humans and sufficient evidence in animals. Crystalline silica is also listed by the NTP as a known human carcinogen. Constituents may also contain asbestiform or non-asbestiform tremolite or other silicates as impurities, and above de minimus exposure to these impurities in inhalable form may be carcinogenic or cause other serious lung problems.

EFFECTS OF OVEREXPOSURE - INGESTION: Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. IARC lists Ethylbenzene as a possible human carcinogen (group 2B).

Date Printed: 1/12/2022 Page 5 / 6

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
64742-49-0	Naphtha, Petroleum, Hydrotreated Light	>5000 mg/kg Rat	>3160 mg/kg Rabbit	>4951 mg/L Rat
14807-96-6	Hydrous Magnesium Silicate	6000	Ň.E.	30
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
64742-47-8	Hydrotreated Light Distillate	>5000 mg/kg Rat	>2000 mg/kg Rabbit	>5000 mg/L Rat
1330-20-7	Xylenes (o-, m-, p- Isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
142-82-5	n-Heptane	N.E.	3000 mg/kg Rabbit	>73.5 mg/L Rat
111-65-9	Octane	N.E.	N.E.	>24.88 mg/L Rat
8052-41-3	Stoddard Solvent	N.E.	>3000 mg/kg Rabbit	>5.5 mg/L Rat
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat
96-29-7	Methyl Ethyl Ketoxime	930 mg/kg Rat	1100 mg/kg Rabbit	>4.83 mg/L Rat

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Do not incinerate closed containers. This product as supplied is a USEPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
UN Number:	N.A.	1950	1950	N.A.
Proper Shipping Name:	Paint and Related Spray Products in Ltd Qty	Aerosols	Aerosols, flammable	Aerosols
Hazard Class:	N.A.	2	2.1	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	Yes	Yes	Yes	Yes

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Gas under pressure, Carcinogenicity, Respiratory or Skin Sensitization, Germ cell mutagenicity

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical NameCAS-No.Xylenes (o-, m-, p- Isomers)1330-20-7Ethylbenzene100-41-4

Date Printed: 1/12/2022 Page 6 / 6

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from

the United States:

Chemical NameCAS-No.Castor oil, sulfated, sodium salt68187-76-8

U.S. State Regulations:

California Proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 4 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 4 Instability: 0

Maximum Incremental Reactivity: 0.69

SDS REVISION DATE: 1/11/2022

REASON FOR REVISION: Substance and/or Product Properties Changed in

Section(s):

02 - Hazard Identification

03 - Composition / Information on Ingredients 08 - Exposure Controls / Personal Protection

11 - Toxicological Information 15 - Regulatory Information Product Composition Changed Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.