

Trimble. water

WIRELESS MULTI-CHANNEL RECORDING TELEMETRY UNIT FOR UNDERGROUND PRESSURE, FLOW AND IMPULSE MONITORING



UNDERGROUND MONITORING IN HARSH ENVIRONMENTS

The Telog Ru-32imA provides real-time monitoring and alarming of pressure, flow sensors, valves, and meters found in harsh environments typical of water distribution and wastewater collection systems such as underground water vaults. When you combine the Telog Ru-32imA RTU with a Trimble Telog software option, you have a powerful system of wireless water infrastructure monitoring that is consistently delivering real-time data from the field straight to your desktop. Imagine...all your data on one platform straight to your computer screen.

In addition to monitoring the pressure on the two pressure channels, the impulse recording option feature of the Trimble Telog Ru-32imA unit stores the waveform of captured pressure transient (impulse) waves detected on the monitored network. The Trimble Telog Ru-32imA can store up to 125 events of variable duration that may occur over many months of on-site monitoring, recording up to a maximum of 20 minutes of pressure transient data at 30 samples/second. Impulse monitoring can be enabled on both pressure channels simultaneously, providing insight into impact and origins of such transient events.

Sensor Support

The Ru-32imA is a versatile eight channel RTU that can be supplied with one or two pressure sensors and can interface up to two digital inputs (pulse and/or event), one 4-20 mA current loop from a process instrument, one analog voltage or potentiometer input, and two additional inputs to capture the encoded register reading of single or dual water meters such as master meters and compound meters.

Wireless Communication

Using cellular technology enables unmanned monitoring of remote sites as well as instant updates and alarm notifications. The Ru-32imA uses a low power, LTE/Cat 1 cellular communication modem certified on multiple cellular systems. This ensures maximum coverage, reliability of service and alignment with cellular carriers technology roadmaps.

Collecting Data

The Telog Ru-32imA may be configured to call it's server application on a schedule (e.g. once per day; every four hours, etc.) and/or in response to site alarm conditions (e.g. transient event, high or low pressure or level exceedance). The recorder can sample the sensor up to four times/second and store the data statistics (minimum, average, maximum or totals) at user defined intervals. Additionally, the Telog Ru-32imA recorder can sample the pressure sensors up to 30 times/second for transient detection on both channels.

Packaging

The cellular modem, data recorder and battery are integrated into an IP68 rated, environmentally rugged enclosure weighing three pounds and measuring 8 x 8 x 4 inches (L x W x H). The unit is provided with a panel mount TNC coax connector and will support a variety of certified antennas. All connectors and fittings are watertight and the product is environmentally rated IP68 to 9.8 feet (three meters) of depth.

Battery Powered

The Telog Ru-32imA can be powered with internal battery or external DC power with internal battery backup. This is user selectable and the battery is a single, user replaceable battery pack, Telog BP-4, providing an operating life of up to five years depending on the user-defined call schedule. A five year battery life example would be sampling two pressure sensors every 10 seconds and water meter registers hourly and transferring data to a host server on a daily schedule.

Software Support

Trimble Telog wireless recorders are compatible with all Trimble software applications, including Trimble Unity, Telog Enterprise and Telogers for Windows application software. This ensures that utilities have a complete solution addressing all their remote monitoring requirements delivered in a manner that suits each individual utility's operations and IT needs.

Applications

+++++++++++++++++++

+++++++++++++++++++

- Water system pressure transient detection
- Water system pressure monitoring
- Underground water level monitoring
- Mag meter monitoring
- Pressure reducing valve (flow and pressure) monitoring
- Single or dual water meter monitoring
- Meter register input monitoring

Benefits

- Detection of potentially damaging pressure transients
- Insight into consumption for non-revenue water
- Optimized water and site operations and compliance
- Real-time situational awareness on pressure or bursts

Features

- Wireless communication via cellular (LTE)
- Alarm notification
- ► Time stamped events
- User programmable
- ► IP68 Rating



Telog Ru-32imA SPECIFICATIONS

RECORDER MODEL: Telog Ru-32imA

Eight channel, underground RTU with

embedded cellular modem

(Channels 1-2: 30 samples per second max - 33 ms, 1 second interval max): (Channels 3-4: 4 samples per second max - 250 ms, 1 second interval max): (Channels 5-6: 1 sample per second max - 1 s, 1 second interval max): (Channels 7-8: 1 sample per minute max - 1 min., 1 minute interval max):

I2C Pressure Sensors Channels 1 & 2 Resolution 12 bits (0.025%)

±0.075% of full scale at 73 °F [23 °C] Accuracy

±40 ppm/°F

40 °F to 149 °F [4 °C to 65 °C] Temperature range: For applications below this operating range please contact

your Trimble Telog support team. Current Loop (Channel 3) (4-20 mA) Input Resolution 12 bits (0.025%)

±0.075% of full scale at 70 °F [21 °C] Accuracy

±40 ppm/°F Analog Input (Channel 4) 0-5 VDC Resolution 12 bits (0.025%)

Accuracy ±0.075% of full scale at 70 °F [21 °C]

±40 ppm/°F

Digital Input 2 channels (5 and 6)

Selectable pulse counter or event recorder Туре

Contact closure or logic driven Input 3 volts at 20 µAmps maximum Excitation

Pulse Width 10 ms minimum Meter Register Inputs (Channels 7 and 8)

Reads absolute encoded register values;

4 thru 9 digits in length

3-wire synchronous interface, ASCII coded E.g. Sensus ECR, Neptune ProRead (3-wire),

Badger ADE & HR-E, etc.

Recording

Sample rate 4 per second to 1 per 8 hours; programmable

Clock accuracy

Memory size 128 kbytes; 80,000 data values Storage method Wrap around (first-in; first-out)

Communication

5 pin circular connector rated IP68 Local RS-232 Auto-selected baud rate to 19.2 K

Cellular IWM2/L1 cellular modem LTE Category 1

certified Verizon Wireless Local Bluetooth BLE 4.1

Bluetooth Power

> Factory installed, field replaceable Telog BP-4 Battery

lithium battery pack

Battery Life Up to 2800 data calls to host computer

Examples: Call Frequency Sampling Frequency Battery Life 1/day 5 years

5 second 1/day 4/second 2 years 1/day 30/second 3.5 months (2 sensors @ medium to excellent signal strength)

External Power 9-30 VDC @ 1 A optional via customer supplied DC or solar. Battery becomes backup if external

power is lost.

Enclosure

Size 8" L x 8" W x 4" H [204 mm x 102 mm x 204 mm]

Weight 3 lbs. [1.4 kg] Material Polycarbonate

Environmental

Temperature -40 °F to 158 °F Γ-40 °C to 70 °C1

Rating NEMA 6 (IP68) Support Software

Telogers for Windows®6.5 or later S-3PC S-3FP Telog® Enterprise 6.5 or later

TW-UNITY Trimble Unity

SENSOR MODEL: TELOG PT-DS SERIES

Strain gauge pressure sensor Type

Selectable 5, 10, 30, 100, 300, 1000 PSIG Range Accuracy over the calibrated temperature range including zero and span setting and the effects of non-linearity, hysteresis

and repeatability: 0.25% FS

Cable Vented Polyurethane 0.225" diameter [5.715 mm] Pressure Over Range 2x full scale with negligible calibration change 4x containment pressure up to 2900 psi max


Physical

Pressure fitting 1/4" NPT female

Environmental Submersible to NEMA 6P (IP68)

Sensor Length 4.5" [114 mm] Sensor Diameter (max) 1.0" [25.5 mm] Sensor Body Material 316 stainless steel 0.027 lbs./ft Cable Weight

ENCLOSURE DIMENSIONS



Specifications within this brochure are subject to change without notification This product covered by U.S. Pat. No. 7,219,553 and 7,357,034.

© 2020, Telog, A Trimble Company. All rights reserved. Telog is a registered trademark and Telogers is a trademark of Telog, A Trimble Company. Trimble and the Globe & Triangle logo are trademarks of Trimble Inc. registered in the United States and in other countries. Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Verizon Wireless is a trademark of Verizon Trademark Services. All other trademarks are the property of their respective owners. PN 022544-021 (10/2020)





18500 Von Karman Avenue, Suite 260, Irvine, CA 92612 +1 (949) 892-6120

CORK OFFICE, IRELAND

R.o.W: Trimble Navigation Limited NSC Campus, Mahon, Cork

+353 21 230 9328

TELOG (ROCHESTER OFFICE), NEW YORK, USA 830 Canning Parkway Victor, New York 14564 +1 (585) 742-3000

TrimbleWater_ContactUs@trimble.com www.trimblewater.com



