

3505-H321-V-CYL-B-TRM, 3505H321CYLBTRMTC Shower/Hand Shower Trim **Specification Submittal**



Feature Highlights	Options/Modifications
 Dia Shower/Hand Shower Trim Requires Temptrol® Pressure Balancing Shower Valve Requires Symmons Dual Outlet Diverter Valve Metal lever handles 30" slide bar for hand shower wand Dual checks for backflow protection 60" flexible metal hose 1 mode hand shower wand 1 mode showerhead 	□ -1.5
 2.5 gpm (9.5 L/min) flow restrictors Tub spout not included Components shall be metal and nonmetallic construction, plated in standard Polished Chrome finish Available with TA-10 flow control spindle and T-12A cap assembly for Temptrol valve bodies installed with Test Cap (order p/n 3505H321CYLBTRMTC) For optional in-line vacuum breaker order p/n EF-109 	☐ -L2 Less hand shower wand
Model Numbers 3505-H321-V-CYL-B-TRM Shower/Hand Shower Trim, Temptrol Pressure Balancing Shower Valve and Symmons Dual Outlet Diverter valve ordered separately	□ -R 60" white vinyl hose in place of 60" metal hose □ -VP Vandal resistant escutcheon screws in place of standard screws □ -BBZ Brushed Bronze finish □ -MB Matte Black finish
□ 3505H321CYLBTRMTC Shower/Hand Shower Trim with TA-10 flow control spindle and	□ -STN Satin Nickel finish

Note: Append appropriate -suffix to model number.

Compliance

- ASME A112.18.1/CSA B125.1
- WaterSense @ 1.5 gpm and 2.0 gpm (does not apply to L3 modification)



Warranty


Limited Lifetime - to the original end purchaser in consumer/residential installations.

5 Years - for industrial/commercial installations.


Refer to www.symmons.com/warranty for complete warranty information. Go to www.symmons.com/register to register your Symmons product.

T-12A cap assembly, must order Temptrol valve with Test Cap

Dimensions



Measurements		
Α	Ø 2-1/2", 64 mm	
В	6-3/4", 171 mm	
С	6", 152 mm	
D	Male 1/2-14 NPT thread must be recessed 1/4" (6 mm) from finished wall	
Е	Ref. 77", 1956 mm	
F	3-1/2", 89 mm	
G	Ø 5", 127 mm	
Н	Ø 7-1/2", 191 mm	
I	Ref. 10", 254 mm	
J	Ref. 42", 1067 mm	
K	3", 76 mm	
L	2-7/8", 73 mm	
М	Rough-in $2-3/8$ " $\pm 1/2$ ", 60 mm ± 13 mm	
N	6-3/4", 171 mm	
0	6", 152 mm	
Р	5-5/8", 143 mm	
Q	3", 76 mm	
R	2-7/8", 73 mm	
S	1-3/8", 35 mm	
Т	2-7/8", 73 mm	



Notes:

- 1) Valve body and piping not included and shown as reference only.
- 2) Plaster shield (p/n T-176) for dry wall, plaster or other type walls 1/2" or greater.
- 3) All dimensions measured from nominal rough-in (see M as reference).
- 4) Dimensions subject to change without notice.