

S59-4016 Series Navigator® Thermostatic Mixing Valves

- · Lead-free design†
- Glass-filled polysulfone valve body
- Thermoplastic polymer cartridge
- · Reliable wax-filled thermostat
- Adjustable set point within temperature range
- Easy installation and serviceability
- Universal mounting capability
- Integral check valves and strainers
- Factory assembled and tested
- · Optional mounting bracket

Valve Specifications

Maximum Operating Pressure

125 PSI (860 kPA)

Maximum Inlet Temperature

180° F (82° C)

Temperature Range

Std. 59° F (15° C) to 140° F (60° C)

Temperature Differential - Hot to Mix

10° F (5.6° C)

Flow Capacities — GPM (L/Min) \$59-4016D, \$59-4016N, \$59-4016S

Min.	Pressure Drop – PSI (Bar)						
Flow	5	10	15	20	30	45	60
	(.5)	(1.0)	(1.5)	(2.0)	(2.5)	(3.0)	(4.0)
0.5	5.0	7.0	8.5	10.0	12.5	15.0	16.5
(2.0)	(22.4)	(31.6)	(39.6)	(46.4)	(52.0)	(56.5)	(61.9)

\$59-4016X, \$59-4016Y, \$59-4016EX, \$59-4016EY

Min.	Pressure Drop – PSI (Bar)						
Flow	5	10	15	20	30	45	60
	(.5)	(1.0)	(1.5)	(2.0)	(2.5)	(3.0)	(4.0)
0.5	4.0	5.0	6.5	7.5	9.0	11.0	12.5
(2.0)	(17.3)	(23.5)	(29.0)	(33.8)	(38.0)	(41.5)	(46.5)

Product Compliance

Listed by IAPMO R&T to

- ASSE 1017, ASSE 1069, ASSE 1070/ASME A112.1070/CSA B125.70, CSA B125.3
- Uniform Plumbing Code (UPC)
- National Plumbing Code of Canada
- International Plumbing Code (IPC)

Listed by ASSE International to

ASSE 1017, ASSE 1069, ASSE 1070

Listed by NSF International to

NSF/ANSI 372








Consult local and national codes. Conformity and compliance to local and national codes is the responsibility of the installer.

Page 1 of 2 9/10/2020 This information is subject to change without notice. Bradley_TMV_PointOfUse_S59-4016Series




Models (Mus	et select one)
Model	Description
S59-4016D	Navigator $^{\! \otimes \! }$ Thermostatic Mixing Valve with 1/2" NPT/sweat connections
S59-4016N	Navigator Thermostatic Mixing Valve with 3/4" NPT connections
S59-4016S	Navigator Thermostatic Mixing Valve with 3/4" sweat connections
S59-4016X	Navigator Thermostatic Mixing Valve with 1/2" PEX connections
S59-4016Y	Navigator Thermostatic Mixing Valve with 3/4" PEX connections
S59-4016EX	Navigator Thermostatic Mixing Valve with 1/2" Expansion PEX connections
S59-4016EY	Navigator Thermostatic Mixing Valve with 3/4" Expansion PEX connections
\$45-2456	Optional Mounting Bracket (Not Shown)

Engineer's Approval_____

© 2020 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com



Dimensions (mm)



Model No	Connection Type	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E
S59-4016D	1/2" NPT/Sweat	3-5/8" (92)	4-1/4" (107)	7" (176)	4-1/8" (105)	4-1/8" (105)
S59-4016N	3/4" NPT	3-3/4" (95)	4-5/16" (110)	7" (176)	4-1/4" (107)	4-1/4" (107)
S59-4016S	3/4" Sweat	3-1/8" (79)	3-3/4" (95)	6-1/2" (164)	3-5/8" (92)	3-5/8" (92)
S59-4016X	1/2" PEX	3-1/8" (79)	3-3/4" (95)	6-1/2" (164)	3-5/8" (92)	3-5/8" (92)
S59-4016Y	3/4" PEX	3-1/8" (79)	3-3/4" (95)	6-1/2" (164)	3-5/8" (92)	3-5/8" (92)
S59-4016EX	1/2" Expansion PEX	3-1/4" (83)	3-7/8" (98)	6-5/8" (168)	3-3/4" (96)	3-3/4" (96)
S59-4016EY	3/4" Expansion PEX	3-1/2" (89)	4-1/8" (105)	6-7/8" (174)	4" (102)	4" (102)

Consult local and national codes. Conformity and compliance to local and national codes is the responsibility of the installer.

Page 2 of 2 9/10/2020 This information is subject to change without notice. Bradley_TMV_PointOfUse_S59-4016Series © 2020 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com