



G1691 Emergency Shower, Horizontally Mounted, All-Stainless Steel

Application: All-stainless steel emergency shower for horizontal mounting. Ideal for use in areas where highly corrosive materials are handled, as well as in laboratory and clean room applications.

Shower Head: 10" diameter stainless steel.

Valve: 1" IPS stainless steel stay-open ball valve. Valve has stainless steel ball and Teflon® seals. Furnished with stainless steel actuating arm and 29" stainless steel pull rod.

Pipe and Fittings: 1" IPS stainless steel.

Supply: 1" NPT female inlet.

Sign: ANSI-compliant identification sign.


Available Options

- PSH** Orange ABS plastic shower head.
- FC20** Regulates shower flow rate to 20 GPM.
- AP280-100 ELECTRIC LIGHT AND ALARM HORN**
Flashing light and horn serve to summon assistance when shower is activated.
- TMV** G3800LF thermostatic mixing valve precisely blends hot and cold water to deliver warm (tepid) water as required by ANSI Z358.1-2014. Refer to "Tempering Units" section for complete technical and product selection information.
- AP250-015 MODESTY CURTAIN**
Modesty curtain for horizontal shower installation.





□ G1691 Emergency Shower, Horizontally Mounted, All-Stainless Steel



THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Due to continuing product improvement, the information contained in this document is subject to change without notice. All dimensions are ± 1/4" (6mm). rev. 0115

Sign Included

