For Residential and Commercial Applications				
Job Name		Engineer / Architect		
Job Location		Wholesaler		
Submittal Date		Contractor		

40 Series Flare Caps

Use: For use with fuel, oil, liquefied petroleum (LP) and natural gas lines. Designed for use with aluminum, copper, brass and welded steel tubing that can be flared.

Design Features:


- Recommended for higher pressures than those covered by compression fittings
- Resist mechanical pull out
- Available in a broad range of sizes

Operating Specifications:

Temperature: -65°- 250° F at maximum operating pressures


Working Pressure: see chart below

Vibration: Good vibration resistance*





MAXIMUM WORKING PRESSURES											
Service Conditions	Tube O.D.	Type of Tubing and Wall Thickness (Inches)									
		Copper – Dead Soft (Seamless)				Copper – Half Hard (Seamless)					
		.030"	.032"	.035"	.049"	.065"	.032"	.035"	.042"	.049"	.065"
Safety Factor 4-1	1/8	4300		5000			5000				
	3/16	2850		3300			3400				
	1/4	2100	2250	2500			2500				
	5/16		1800	2000			2000				
	3/8		1500	1650			1700	1850			
	1/2		1100	1250		2000	1250	1400			2600
	5/8			1000	1400	1800	1000			1500	2000
	3/4			850	1150	1500			1100		1700
	7/8									1100	1500
	1/8	2800		3350			3400				
	3/16	1900		2200			2250				
Safety Factor 6-1	1/4	1430	1500	1650			1700				
	5/16		1200	1300			1350				
	3/8		100	1100			1100	1200			
	1/2		750	825		1550	850	925			1750
	5/8			650	930	1200	675			1000	1350
	3/4			550	775	1000			725		1100
	7/8									750	1000





^{*}Recommend long flare nuts when greater vibration resistance is required

40 Series Flare Caps

MATERIAL SPECIFICATIONS		
Flare Cap		C36000 brass

PART DIMENSIONS (Inches)				
Model	Straight Threads	DIM. A	НЕХ. В	
40-3	3/8-24	.47	1/2	
40-4	7/16-20	.56	9/16	
40-5	1/2-20	.62	5/8	
40-6	5/8-18	.58	3/4	
40-8	¾-16	.69	7/8	
40-10	7/8-14	.75	1-1/16	

Part Listing:

Ш	40-3	For 5/16" OD Tube
	40-4	For 1/4" OD Tube

