



## 4-9 PIPE CUTTERS

Manual & Ratchet Snap Cutters Hydraulic Pipe Cutters Replacement Cutter Chains Internal Cast Iron Pipe Cutter Steel Pipe Cutters Hinged Pipe Cutters The PipeMaster

Glass Tubing Cutters

# 10-23 PLASTIC PIPE & COPPER TUBE TOOLS

Professional & Economy Snippers Plastic Pipe Saws Hand And Powered Bevelers Pipe Hog Internal Plastic Pipe Cutters Chamfering/Depth Gauge Tool **Guillotine Pipe Cutters PEX Crimping Tools Utility Knives Tubing Cutters Close Quarters Cutter Auto-C Cutters** Ratch Cuts **Tube Brushes** Inner & Outer Reamer **Deburring Tool** Hammerhead Flaring Tool Rerounding Tools and Kit Replacement Cutter Wheels

# 24-25 GROOVING & FABRICATION

Portable Roll Groovers Hydraulic Grooving Machines Orbital Pipe Cutting Machine Mantis Blades

# 26-35 PIPE THREADING

Manual Ratchet Threader Sets Mini Power Drivers Hand Oiler 12R Style Dies – NPT, BSPT 12R Style Drop Head with Dies Sidekick III Pipe Threader Power Threading Machines Universal Replacement Dies Threader Cart & Stands Nipple Attachments Threadmaster Cutting Oil

# 36-40 HYDROSTATIC TEST PUMPS

Manual Operated Gas Operated Electric Operated Pneumatic Operated Fire Hose Testers

# 41 TRASH PUMP

2" and 3" Trash Pumps Mudsucker Pumps Vacuum Test Assembly

# 42-48 PIPE WORKING TOOLS

Tripod Vise Stands **Bench Vises Pipe Supports** Yoke Vises Floor Pipe Vises Pipe Puller Pipe Dolly **Pipe Wrenches** Spud Wrench Chain Wrench Strap Wrenches **Basin Wrench Coupling Torque Wrenches** Hydrant Wrench **Double-Up Wrenches** Heavy Duty Deep Sockets O.D. Tapes Pipe Descaler Pipe Freezing Kit

# 49 SHUTOFF TOOLS

Soft Copper Water Lines
Plastic Water and Gas Lines

# **50-53 DRILLING & TAPPING TOOLS**

Hot Tap System & Accessories Drill Taps Tapping Fluid Portable Hole Cutter Systems Hole Cutter System and Sheels Earthworm Hydro-Drill Pipe Slices & Accessories Mini Pipe Slice

# **54-55 VALVE EXERCISERS**

ValveMaster
Portable Valve Exercisers
Aluminum Valve Wheel Wrenches
Hydrant Nut
Rising Stem & Hand Wheel
Adapters
Telescoping Valve Key

# **56 MARKETING TOOLS**

# 58-63 PRODUCT LISTING



# **590 AND 591 MANUAL PIPE CUTTER**

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	No-Hub®	Tile / Clay	Shipping Weight
590-6	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-6" (100mm-150mm)	23 lbs. (10.5kg)
590-8	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-8" (100mm-200mm)	25 lbs. (11.5kg)
590-10	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-10" (100mm-250mm)	28 lbs. (13kg)
590-12	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-12" (100mm-300mm)	28 lbs. (12.7kg)
590-15	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-15" (100mm-375mm)	29 lbs. (13kg)
591-6	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-6" (100mm-150mm)	24 lbs. (11kg)
591-8	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-8" (100mm-200mm)	25 lbs. (11.5kg)



38

**Replacement Adjustment Screw Assembly** 



"captured screw"

# **490 AND 491 RATCHET PIPE CUTTER**

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	No-Hub®	Tile / Clay	Shipping Weight
490-6	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-6" (100mm-150mm)	18 lbs. (8.5kg)
490-8	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-8" (38mm-200mm)	4"-8" (100mm-200mm)	19 lbs. (8.6kg)
490-10	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-8" (38mm-200mm)	4"-10" (100mm-250mm)	20 lbs. (9.5kg)
490-12	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-8" (38mm-200mm)	4"-12" (100mm-300mm)	22 lbs. (10kg)
490-15	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-8" (38mm-200mm)	4"-15" (100mm-375mm)	23 lbs. (10.5kg)
491-6	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	4"-6" (100mm-150mm)	18 lbs. (8.5kg)
491-8	1 <sup>1</sup> / <sub>2</sub> "-6" (38mm-150mm)	1 <sup>1</sup> / <sub>2</sub> "-5" (38mm-125mm)	1 <sup>1</sup> / <sub>2</sub> "-8" (38mm-200mm)	4"-8" (100mm-200mm)	19 lbs. (9kg)

700669

6519 **Replacement Drive Screw Assembly** 275556 Replacement Pin for 700669



#### 3990 XH RATCHET PIPE CUTTER

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	Tile / Clay	Cast Iron Water Class 22	Shipping Weight
3990-6	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	21 lbs. (9.5kg)
3990-8	2"-8" (50mm-200mm)	2"-8" (50mm-200mm)	4"-8" (100mm-200mm)	2"-6" (50mm-150mm)	23 lbs. (10.5kg)

6520 700919 Replacement Drive Screw Assembly



# WHEELER-REX HYDRAULIC PIPE CUTTERS

WHEELER-REX Hydraulic Cutters are the solution to cutting larger diameter Cast Iron, Tile and Concrete Pipe. Like the hand operated "snap" cutters, hydraulic cutters are not rotated around pipe. Their remotely operated hydraulic pumps provide the required power. A 2"-3" minimum clearance is all that is needed to wrap cutter chain around pipe. They come complete with pump, hose and case.



#### 2990 HYDRAULIC PIPE CUTTER

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	Tile / Clay	Cast Iron Water Class 22	Cast Iron Water Class 26	Shipping Weight
2990-6	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	2"-6" (50mm-150mm)	NA	85 lbs. (39kg)
2990-8	2"-8" (50mm-200mm)	2"-8" (50mm-200mm)	2"-8" (50mm-200mm)	2"-6" (50mm-150mm)	NA	87 lbs. (40kg)
2990-10	2"-10" (50mm-250mm)	2"-8" (50mm-200mm)	2"-10" (50mm-250mm)	2"-6" (50mm-150mm)	NA	89 lbs. (41kg)
2990-12	2"-10" (50mm-250mm)	2"-8" (50mm-200mm)	2"-12" (50mm-300mm)	2"-6" (50mm-150mm)	NA	92 lbs. (42kg)
2990-15	2"-10" (50mm-250mm)	2"-8" (50mm-200mm)	2"-15" (50mm-375mm)	2"-6" (50mm-150mm)	NA	94 lbs. (43kg)

1630 Replacement Hydraulic Pump .......22 lbs. (48.5kg)



# 3890 HYDRAULIC PIPE CUTTER

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	Tile and Concrete	Cast Iron Water Class 22	Cast Iron Water Class 26	Shipping Weight
3890-12	4"-12" (100mm-300mm)	4"-12" (100mm-300mm)	4"-12" (100mm-300mm)	4"-12" (100mm-300mm)	4"-10" (100mm-250mm)	152 lbs. (69kg)
3890-15	4"-15" (100mm-375mm)	4"-15" (100mm-375mm)	4"-15" (100mm-375mm)	4"-12" (100mm-300mm)	4"-10" (100mm-250mm)	163 lbs. (74kg)
3890-18	4"-18" (100mm-450mm)	4"-18" (100mm-450mm)	4"-18" (100mm-450mm)	4"-12" (100mm-300mm)	4"-10" (100mm-250mm)	170 lbs. (77kg)
3890-24	4"-18" (100mm-450mm)	4"-18" (100mm-450mm)	4"-24" (100mm-600mm)	4"-12" (100mm-300mm)	4"-10" (100mm-250mm)	178 lbs. (88kg)

1830 



#### **5590 HYDRAULIC PIPE CUTTER**

Wheeler #	Service (Std) WT Soil Pipe	XH Soil Pipe	Tile and Concrete	Cast Iron Water Class 22	Cast Iron Water Class 26	Shipping Weight
5590-18	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	200 lbs. (91kg)
5590-20	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-20" (150mm-500mm)	6"-20" (150mm-500mm)	6"-18" (150mm-450mm)	213 lbs. (97kg)
5590-24	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-24" (150mm-600mm)	6"-20" (150mm-500mm)	6"-18" (150mm-450mm)	230 lbs. (105kg)
5590-36	6"-18" (150mm-450mm)	6"-18" (150mm-450mm)	6"-36" (150mm-900mm)	6"-20" (150mm-500mm)	6"-18" (150mm-450mm)	269 lbs. (122kg)

1930 



# HYDRAULIC PUMP FLUID

(WHEELER-REX Hydraulic Cutter guarantees valid only when Hydroyl fluid is used.)

3801	1 Ut	(1Kg)
3804	1 Gal	(4kg)

Gallons are available in cases of six.





# PIPE CUTTER CHAINS 490 RATCHET, 590 MANUAL & 1790 JR. HYDRAULIC

Part No.		Length	No. of pins	Weight
522	Chain for 6" Pipe	26 ¹/₄"	21	5 lbs. (2.3kg)
532	Chain for 6" Pipe with rollers for No-Hub®	26 <sup>1</sup> / <sub>4</sub> "	21	5 lbs. (2.3kg)
528	Chain for 8" Pipe	36"	29	6.5 lbs. (2.9kg)
533	Chain for 8" Pipe with rollers for No-Hub®	36"	29	6.5 lbs. (2.9kg)
5210	Chain for 10" Pipe	43 3/4"	35	8 lbs. (3.6kg)
5212	Chain for 12" Pipe	51"	41	10 lbs. (4.5kg)
5215	Chain for 15" Pipe	58 <sup>1</sup> / <sub>2</sub> "	47	11 lbs. (5kg)
	FOR CONVERTING YOUR PRESENT CHAIN	TO CUT L	ARGER SIZES	
5256	6" to 8", 8" to 10", 10" to 12", 12" to 15"	10"	8	2 lbs. (0.9kg)
5258	6" to 10", 8" to 12", 10" to 15"	17 ¹/₂"	14	3.5 lbs. (1.6kg)
52510	6" to 12", 8" to 15"	25"	20	8 lbs. (3.6kg)
52512	6" to 15"	32 <sup>1</sup> / <sub>2</sub> "	26	6 lbs. (2.7kg)
519	Kit to convert 590 Cutter to 591 No-Hub® Cutter or 490 Cutter to 491 No-Hub® Cutter			

#### **3990 RATCHET PIPE CUTTER**

Part No.		Length	No. of Pins	Weight
700987	Chain for 6" Pipe	26"	21	7 lbs. (3kg)
701077	Chain for 8" Pipe	36"	29	8.5 lbs. (3.8kg)

# **2990 HYDRAULIC CUTTER**

Part No.		Length	No. of pins	Weight			
1926	Chain for 6" Pipe	26 <sup>1</sup> / <sub>4</sub> "	21	7 lbs. (3kg)			
1924	Chain for 8" Pipe (replaces 2924)	36 <sup>1</sup> / <sub>4</sub> "	29	10 lbs. (4.5kg)			
192410	Chain for 10" Pipe (replaces 292410)	46 <sup>1</sup> / <sub>4</sub> "	37	12 lbs. (5.5kg)			
192412	Chain for 12" Pipe (replaces 292412)	53 ¹/₄''	43	14 lbs. (6.5kg)			
192415	Chain for 15" Pipe (replaces 292415)	61 <sup>1</sup> / <sub>4</sub> "	49	16 lbs. (7kg)			
	FOR CONVERTING YOUR PRESENT CHAIN TO CUT LARGER SIZES (Note – Old and new style chain extensions NOT interchangeable)						
19010	8" Cutter to 10"	10"	8	2.5 lbs. (1kg)			
19012	8" Cutter to 12"	17 ¹/₂"	14	4.5 lbs. (2kg)			
19015	8" Cutter to 15"	25"	20	6.5 lbs (2.9kg)			

# 3890 HEAVY DUTY HYDRAULIC CUTTER

Part No.		Length	No. of pins	Weight			
3824	Chain for 12" Pipe	50 <sup>3</sup> / <sub>4</sub> "	29	25 lbs. (11kg)			
382415	Chain for 15" Pipe	63"	37	32 lbs. (14.5kg)			
382418	Chain for 18" Pipe	76 <sup>1</sup> / <sub>2</sub> "	43	37 lbs. (16.8kg)			
382424	Chain for 24" Pipe	97 <sup>1</sup> / <sub>2</sub> "	55	47 lbs. (21.4kg)			
	FOR CONVERTING YOUR PRESENT CHAIN TO CUT LARGER SIZES						
382515	12" Cutter to 15"	14"	8	7 lbs. (3kg)			
382518	12" Cutter to 18"	24 <sup>1</sup> / <sub>2</sub> "	14	11 lbs. (5kg)			
382520	12" Cutter to 20"	35"	20	11 lbs. (5kg)			
382524	12" Cutter to 24"	46 <sup>1</sup> / <sub>2</sub> "	26	22 lbs. (10kg)			

#### **5590 SUPER HYDRAULIC CUTTER**

0000	OOI EITTI DIIAGEIG GO							
Part No.		Length	No. of pins	Weight				
5524	Chain for 18" Pipe	72 <sup>1</sup> / <sub>2</sub> "	29	71 lbs. (32kg)				
552420	Chain for 20" Pipe	82 <sup>1</sup> / <sub>2</sub> "	33	83 lbs. (37.8kg)				
552424	Chain for 24" Pipe	97"	39	98 lbs. (44.5kg)				
552436	Chain for 36" Pipe	142"	57	142 lbs. (64.5kg)				
	FOR CONVERTING YOUR PRESENT CHAIN TO CUT LARGER SIZES							
552520	18" Cutter to 20"	10"	4	10 lbs. (4.5kg)				
552524	18" Cutter to 24"	25"	10	25 lbs. (11.4kg)				
552536	18" Cutter to 36"	70"	28	64 lbs. (29.1kg)				

NOTE: Hydraulic cutter chain parts: individual pins, links and wheels are only available with factory installation. Hydraulic cutter chain extensions are available only through authorized service stations unless installed by the factory.



# **INTERNAL CAST IRON PIPE CUTTER** (CAPITOL STYLE CUTTER)

#### **Cuts Cast Iron from the inside out!!**

Designed to eliminate the difficulty plumbers have in setting toilet bowls, urinals and similar fixtures due to the shortness of the closet horn. Make cuts where nothing else can!

32900	3" Cast Iron10	lbs.	(4.5kg)
42900	4" Cast Iron	lbs.	(4.7kg)

#### **Replacement Cutter Wheels:**

700201 Cutter Wheel for CI for 32900/42900

276097 **Cutter Wheel Pin** 



# STEEL PIPE CUTTERS

Two models designed for fast, easy cutting of steel pipes. Both models come with an extra long shank which protects adjustment threads and an extra large handle for quick, easy adjustment.

2690	For <sup>1</sup> / <sub>8</sub> "–2" steel pipe (3.17mm-50.8mm)
8001 8082	Cutter Wheel for steel Cutter Wheel for stainless steel
4690 8004	For 2"-4" steel pipe (50.8mm-101.6mm)



# **HINGED PIPE CUTTER**

Four-wheel cutter, featuring a unique guide bar design that ensures both smooth operation and accurate precise pipe cutting. Needs only 90° to 110° handle swing, and only 4 inch clearance. Universal cutter wheels are ideal for cutting most metals and are interchangeable with many other makes of hinged pipe cutters.

5090	1/2"-2" pipe capacity (12.7mm-50.8mm) 6 lbs. (2	2.7kg)
95240	2"-4" pipe capacity (50.8mm-101.6mm)	8.2kg)
95460	4"-6" pipe capacity (101.6mm-152.4mm)21 lbs. (9	9.5kg)
95680	6"-8" pipe capacity (152.4mm-203.2mm)	(12kg)
95121	8"-12" pipe capacity (203.2mm-304.8mm)	(16kg)

#### **Replacement Cutter Wheels:**

8039	for 5090 for steel
8050	for 95041, 95240 for steel
8052	for 95061, 95460 for steel
8054	for 95081, 95680, 95121 for steel
8051	for 95041, 95240 for CI/DI
8053	for 95061, 95081, 95460, 95680, 95121 for CI/DI
8076	for 95061, 95081, 95460, 95680, 95121 / universal whee







#### **PIPEMASTER**

#### **General Information:**

Unit consists of a cutting head with internal gears which operate the drive wheels and blade shaft. Cutting blades (except for No. 4616) must be cooled with water during cutting and are fully enclosed for safety. The cutter is held onto the pipe by a wide roller chain which is tensioned with a threaded take-up mechanism. A chart is included which tells the operator how much chain is required for various sizes of pipe. PipeMaster comes standard with cutting head, roller chain, wedges and water supply tank in a wood case. Blades are chosen based on pipe material and are not included with the basic machine. Maximum wall thickness for cutting is 1". The unit has a hydraulic motor which requires an external hydraulic power source. See our Model 6500 Power Pak and 701185 Bypass Valve on the next page.

#### **PipeMaster Features:**

- Maximum hydraulic requirements 6 gpm/1500 psi
- Gearbox: Worm Drive with 80-90W gear oil required
- Cutting speed: 3" (150mm) of surface travel per minute 1" (25mm) of diameter per minute
- Cutting Clearance: Radial 8" (200mm); Axial 16" (400mm)
- Blade Speed: 1200 RPM
- Construction: Aluminum gearbox, side plated steel; bronze gears, steel roller chain, drive wheels are aluminum with urethane covering



#### PIPEMASTER ACCESSORIES

700821 20' Hydraulic Hose Assembly complete with male/female FF quick disconnects

276288 Flat Face Male Quick Disconnect 276289 Flat Face Female Quick Disconnect

#### Standard equipment (comes with 5624):

700970 Two Drive Wheels for 6" pipe \*These drive wheels are required to cut 6" pipes

276693 Water Supply Tank, 4 gallon
4685 Set of 6 steel wedges
4686 Roller Chain, one link section

#### **Number of Chain Links Required:**

Pipe Diameter 24" (600mm)
Number of Links 34 pieces



#### 6500 HYDRAULIC POWER PAK ......221 lbs. (100.5kg)

#### Features:

- Maximum hydraulic information: 6 gpm/1500 psi
- Adjustable pressure-relief valve
- Complete with 6.5 hp. Honda engine, on two-wheeled cart with pneumatic tires and cage
- Comes with two 700821 20' Hydraulic Hose Assemblies complete with male/female FF quick disconnects
- Can be used to power other hydraulic tools



#### 701185 BYPASS VALVE KIT

Bypass Valve 6 gpm/1500 psi ......13 lbs. (5.9kg)

Bypass Valve Kit is designed to be used with your truck, skid loader, backhoe or tractor's hydraulic system for use with the WHEELER-REX PipeMaster. The 701185 will adapt your current hydraulic system to the specs required to operate the PipeMaster (maximum 6 gpm/1500 psi). Weight is only 10 pounds and it is easy to connect. The PipeMaster's hydraulic lines will directly attach to the quick disconnects for both input and output points on the Bypass Valve. Hydraulic lines are required and are not included with the 701185 and are available as an additional accessory.\*

\*700821 20' Hydraulic Hose Assembly complete with male/female FF quick disconnects

#### **Features:**

4616

- Maximum input from alternative hydraulic power source: 0-30 gpm/0-3000psi
- Maximum output from Bypass valve: 0–6 qpm/0–1500psi



Blade No. 4706 6" Carbide-tipped Blade for Steel Pipe



Blade No. 4606 6" Diamond Blade for CI/DI Pipe



Blade No. 4616 6" Economy Diamond Blade for DI Pipe

#### PIPEMASTER BLADES

Three blades for Cast Iron, Ductile Iron and Steel Pipes. Available with diamond or carbide tipped. These blades will fit the WHEELER-REX PipeMaster as well as Universal and Utility Cutters from Reed Manufacturing, Keel and WACHS.

4706 6" Carbide Tipped Blade for steel pipes

4606 6" Diamond Blade for cast iron, ductile iron and clay pipes

6" Economy Diamond Blade for ductile iron pipes. Cut dry or wet. Low price and

excellent performance make this blade the best value on the market!

# PLASTIC PIPE & COPPER TUBE TOOLS

#### **GLASS TUBE CUTTERS**

For cutting glass tube and pipe as well as other brittle tubular materials. These tools are based on the original Wheeler "Squeeze and Pop" principle employing cutter wheels in the chain.

#### 69012

For 1/4" thru 3/4" (6–18mm) O.D. gauge glass, laboratory glass, and porcelain tube. Small enough to carry in your pocket and almost as simple to use as a pair of pliers. Just wrap the chain around the tube, and hook the nearest chain pin in the jaw. Then a quick twist of the wrist, a slight squeeze of the handles, and pop!







#### 79014

For 1/4" thru 1" (6–25mm) O.D. gauge glass, laboratory glass, and porcelain tube. Small enough to carry in your pocket and almost as simple to use as a pair of pliers. Just wrap the chain around the tube and insert it through the jaw. Then a quick twist of the wrist, a slight squeeze on the handles, and pop!







#### 79022

For  $^{1}/_{4}$ " thru  $^{1}/_{2}$ " (6–37mm) O.D. gauge glass, laboratory glass, and porcelain tube. Similar to the model 79014 except with a longer chain. Small enough to carry in your pocket and simple to use. Just wrap the chain around the tube and insert it through the jaw. Then a quick twist of the wrist, a slight squeeze on the handles, and pop!



#### REPLACEMENT GLASS CUTTER CHAIN

Part	Description	Length	No. of Pins
690012	Complete Chain for 69012 Glass Cutter	3" (75mm)	12
7914	Complete Chain for 79014 Glass Cutter	5 <sup>1</sup> / <sub>2</sub> " (137mm)	14
7922	Complete Chain for 79022 Glass Cutter	8" (200mm)	22

#### PROFESSIONAL SNIPPERS

WHEELER-REX Professional Snippers have been proven with years of professional use to be the snippers to have in your tool box. Durable and of high quality, with strong construction and long blade life, they are a must!



#### 5190 SNIPPER

For  $\frac{1}{8}$ " to  $\frac{1}{4}$ " (3–31mm) O.D. soft plastic tubing and hose. 5200 Replacement Blade

Blades are reversible for double life. Handles are die-cast aluminum — NOT plastic.

#### 5191 WITH COATED BLADE

For  $\frac{1}{8}$ " to  $\frac{1}{4}$ " (3–31mm) O.D. soft plastic tubing and hose, and 1/2" and 3/4" (12-19mm) 160 lb. and 200 lb. PVC.

5299 Replacement Blade

Blades are reversible for double life. Handles are die-cast aluminum — NOT plastic.



#### **5291 RATCHET ACTION**

For 1/8" to 15/8" (3-42mm) O.D. Schedule 40 Materials: PVC, ABS, vinyl, poly pipe and tubing. Ratchet style. Weight 

5300 Replacement Blade

#### 7291 RATCHET ACTION

For 1/8" to 27/16" (3-63mm) O.D. Schedule 40 Materials: Polyethylene, Polybutylene, Polypropylene, vinyl, PVC, and ABS pipe and tubing. Ratchet style. One hand operation.

Weight 

7324 Replacement Blade



#### PROFESSIONAL V-BLADE SNIPPERS

#### 5280 RATCHET ACTION

For 1/8" to 15/8" (3-42mm) O.D. Schedule 40 Materials: PVC, ABS, vinyl, poly pipe and tubing, and PEX.

Weight 5350 Replacement Blade

#### **7280 RATCHET ACTION**

For 1/8" to 27/16" (3-63mm) O.D. Schedule 40 Materials: PVC, ABS, vinyl, poly pipe and tubing, and PEX.

Weight 

7350 Replacement Blade

#### **ECONOMY SNIPPERS**

Need a snipper, but only for the occasional job? WHEELER-REX has an economical way for you to do just that and not spend a lot of money!



#### **4190 MICRO SNIPPER**

For  $\frac{1}{4}$ " to  $\frac{3}{8}$ " (6–9mm) O.D. soft plastic tubing and hose.

**Great for PVC supply lines!** 



#### **5195 ECONOMY SNIPPER**

For  $\frac{1}{8}$ " to  $\frac{1}{4}$ " (3–31mm) O.D. soft plastic tubing and hose.

Weight 

5196 Replacement Blade



#### **5295 ECONOMY RATCHET ACTION**

For 1/8" to 15/8" O.D. (3-41mm) Schedule 40 Materials: PVC, ABS, vinyl, poly pipe and tubing. Easy to use, anti-rust, anti-wear construction with a heat treated blade.

Weight 

5296 Replacement Blade





#### **HAND SAWS**

Two sizes with comfort fit handles: for plastic pipe and miscellaneous materials. CUTS ON PUSH AND PULL STROKE.

600 18" long blade (37mm).

Capacity: 1/2" to 6" (12-150mm) Sold in cartons of six or individually

601 With PTFE coated blade: 18" long (37mm).

Capacity: 1/2" to 6" (12-150mm) Sold in cartons of six or individually

602 13" long blade (25mm).

Capacity: 1/2" to 3" (12-75mm) Sold in cartons of six or individually

603 With PTFE coated blade: 13" long (25mm).

Capacity: 1/2" to 3" (12-75mm) Sold in cartons of six or individually

#### **Replacement Blades:**

610	Replacement Blade for 600 Hand Saw sold in cartons of twelve or individually	
	Weight for carton	2.7kg)
611	Replacement Blade for 601 Hand Saw sold in cartons of twelve or individually	σ,
	Weight for carton	2.7kg)
612	Replacement Blade for 600 Hand Saw sold in cartons of twelve or individually	٠,
	Weight for carton	1.8kg)
613	Replacement Blade for 603 Hand Saw sold in cartons of twelve or individually	0,
	Weight for carton	1.8ka)



# PVC AND ABS CABLE SAW

Cut PVC and ABS in tight places where other methods will not work. Simply slip the cable saw around the pipe and see-saw to quickly make a cut. Available in two lengths.

	-   -   -   -   -   -   -	
626	26" Cable Saw	0.05lb.
636	36" Cable Saw	0.05lb.



# 9015 HAND OPERATED PLASTIC PIPE BEVELER

The Universal Plastic Pipe Beveler makes a 15° bevel on SDR35 and Sch 40 thermoplastic pipe through 12" (300mm) capacity. It is lightweight and easy to adjust to different wall thicknesses for beveling and deburring. Wide saddle won't twist and dig into the pipe like others.

Capacity	: 1½" through 12" (38–300mm) Diameter	
Weight	5 lbs.	(2.3kg)
220083	Replacement Bevel Blade	



#### POWER OPERATED PLASTIC PIPE BEVELER

The power bevelers are designed for a wide variety of situations including high production applications. Our advanced HSS cutter design makes a smooth 15° bevel, which is adjustable for length and depth. Tools are easy to use and drastically reduces beveling time, especially on large pipe sizes or when doing production beveling.

9000 Capacity: 4" (100mm) and up. 115V, 13/4 hp., 11.0 amp motor, 24,500 RPM15 lbs. (6	(6.8ka)
,	(6.8kg)



# PLASTIC PIPE & COPPER TUBE TOOLS

CONTINUED



# PIPE HOG® PVC / ABS FITTING REAMER

Quickly and accurately bores out solvent welded fittings to make repairs. Fits  $^{1}/_{2}$ " drill chuck. Saves time and material. Pays for itself in one use.

16150	1 <sup>1</sup> / <sub>2</sub> " Pipe Hog for Schedule 40	0.73 lbs.
16200	2" Pipe Hog for Schedule 40	
16300	3" Pipe Hog for Schedule 40	
16400	4" Pipe Hog for Schedule 40	
16010	Pipe Hog Kit with extension shaft	

#### **Accessories:**

700588 Schedule 80 Guide for 16150
700589 Schedule 80 Guide for 16200
700590 Schedule 80 Guide for 16300
700591 Schedule 80 Guide for 16400
16050 12" Extension Shaft
1/2" Square Carbide Insert

Pat. No. 3,752,593





#### **FITTING SAVER**

Quickly and easily removes pipe from solvent welded fittings. Fits  $^{3}/_{8}$ " drill chuck. Saves time and money over replacing whole assemblies. Perfect for plumbing, irrigation and sprinkler contractors.

#### Fitting Savers for Schedule 40 19050 1/2" IPS Fitting Saver.....

19050	1/2" IPS Fitting Saver 0.45 lbs.
19075	<sup>3</sup> / <sub>4</sub> " IPS Fitting Saver 0.5 lbs.
19100	1" IPS Fitting Saver
19020	Sch 40 Fitting Saver Kit (contains 19050, 19075, 19100 Fitting Savers in case) 1.8 lbs.
Fitting	Savers for Schedule 80
19051	1/2" IPS Fitting Saver 0.45 lbs.
19076	<sup>3</sup> / <sub>4</sub> " IPS Fitting Saver
19101	1" IPS Fitting Saver
19025	Sch 80 Fitting Saver Kit (contains 19051, 19076, 19101 Fitting Savers in case) 1.8 lbs.
19030	1/2" CTS Fitting Saver 0.45 lbs.
19035	<sup>3</sup> / <sub>4</sub> " CTS Fitting Saver
277228	Carbide Cutting Insert
277227	Screw for Insert



#### **BEFORE**



Insert tool into broken or cut pipe



Begin cutting pipe





Continue until proper depth is obtained



**AFTER** 



#### **INTERNAL PLASTIC PIPE CUTTERS**

Make accurate, square cuts at floor level or in other blind locations. Cutters are easily preset for depth of cut and make their cuts in seconds. Recommended user supplied power source: 1/2" capacity, 350–450 RPM drill, rated at 4.6 to 6 amps.

For PVC and ABS plastic pipe. For individual pipe sizes from 11/2" to 6" Diameter.

1590	For 11/2" Schedule 40 pipe and DWV.	Weight 1 lbs.	
2290	For 2" Schedule 40 pipe and DWV.	Weight 1.5 lbs.	
2492	For 2" Schedule 80 pipe and DWV.	Weight 1.4 lbs.	
3290	For 3" Schedule 40 pipe and DWV.	Weight 1.9 lbs.	
3490	For 3" Schedule 80 pipe and DWV.	Weight 1.85 lbs.	
4290	For 4" Schedule 40 pipe and DWV.	Weight 2.6 lbs.	
4490	For 4" Schedule 80 pipe and DWV.	Weight 2.45 lbs.	
6000	For 6" Schedule 40 pipe and DWV.	Weight 4.2 lbs.	
6154	Kit for 1 <sup>1</sup> / <sub>2</sub> ", 2", 3", 4"	Weight 12 lbs.	
6156	Kit for 1 ½", 2", 3", 4", 6"	Weight 14 lbs.	

#### **Replacement Blades:**

1293 Replacement Blade for Models 1590, 2290 and 2492 3293 Replacement Blade for Models 3290 and 3490 4293 Replacement Blade for Models 4290, 4490 and 6000

32964 4' Drive Shaft for 11/2" – 2" models 700777 6' Drive Shaft for 11/2" – 2" models 700778 6' Drive Shaft for 3", 4" and 6" models

#### Replacement Blades:

Model	Adjustable Cutting Depth Range
1590 & 2290	1 <sup>5</sup> / <sub>8</sub> " - 8 <sup>1</sup> / <sub>4</sub> "
3290 & 3490	15/8" - 81/4"
4290 & 4490	15/8" - 115/8"
6000	23/8" - 123/4"



#### POLY PIPE CHAMFERING TOOL / DEPTH GAUGE

Lightly bevels the end of polyethylene pipe prior to socket fusion. The tool is sized to allow marking for the proper end distance for the cold ring per ASTM F1056.

10050	<sup>1</sup> / <sub>2</sub> " CTS	0.35 lbs.
10075	³/ <sub>4</sub> " CTS	0.40 lbs.
10100	1" CTS	
10125	11/4" CTS	
10150	1 <sup>1</sup> / <sub>2</sub> " CTS	0.60 lbs.
10200	2" CTS	
30050	¹/₂" IPS	
30075	³/₄" IPS	
30100	1" IPS	
30125	11/ <sub>4</sub> " IPS	0.60 lbs.
30150	1 <sup>1</sup> / <sub>2</sub> "IPS	0.55 lbs.
30200	2" IPS	0.70 lbs.

700155 Replacement Blade for All Models

# PLASTIC PIPE & COPPER TUBE TOOLS

CONTINUED











T-Handle (standard with 892, 1697, 1897 & 1698)

Power Driven (1894 only)



#### **GUILLOTINE PIPE CUTTERS**

#### 892

Designed to cut water/sewer plastic pipe up to 4.0" (125mm) O.D. Comes standard with removable T-Handle design, which can be removed to expose a 1" Hex nut. Wide saddle side-swing opening design simplifies positioning at any point on pipe. This nut can also be driven with a ratchet and 1" socket.

701149 Replacement V-Shaped Blade PTFE Coated 700692 Replacement Straight Blade PTFE Coated

6515 Ratchet 506032 Socket

#### 1697

Designed to cut thin-walled water/sewer plastic pipe up to 8.0" (225mm) O.D. Comes standard with removable T-Handle design, which can be removed to expose a 1" Hex nut. This nut can also be driven with a ratchet and 1" socket.

701358 Stainless Steel V-Blade

**6515** Ratchet **506032** Socket

#### 1698

701567 Low-profile Pointed Blade

#### 1894

A unique approach to cutting large diameter water/sewer plastic pipes. Can be used with a low speed power drive (300–500 RPM maximum), that delivers power to the blade through a right angle worm drive. Power cutting at 300 RPM is a fast 1 minute per inch of pipe diameter and gives better cuts and longer blade life due to reduced flexing. Maximum cutting capacity of 13.2" (335mm) O.D.

Power source is not included.

Weight ......95 lbs. (43kg)

701454 Stainless Steel V-Blade

#### 1897

A unique approach to cutting large diameter water/sewer plastic pipes. Comes standard with removable T-Handle design, which can be removed to expose a 1" Hex nut. This nut can also be driven with a ratchet and 1" socket. Maximum cutting capacity of 13.2" (335mm) O.D.

701454 Stainless Steel V-Blade

**6515** Ratchet **506032** Socket

#### **Guillotine Style Pipe Cutter Features:**

- HDPE/MDPE with low-profile pointed blade \* Thin-walled plastic pipe with v-shaped blade
- Coated steel cutter blade creates outstanding ease of cutting and corrosion protection
- Wide saddle side-swing opening design simplifies positioning at any point on pipe
- · Wide saddle base provides sturdy, positive pipe support
- Stainless steel fasteners and hardware
- $\bullet \ Structural \ members \ produced \ from \ aircraft-grade \ aluminum$
- Dry-lube coated drive screw

#### **CRIMPING TOOLS**

WHEELER-REX introduces a line of crimping tools specifically designed to help install better connections on PEX potable water or radiant heating systems. The full circle crimp eliminates the unsightly appearance of tool marks and distortion of crimped rings.

#### 89202 1/2" PEX RING CRIMPER

A PEX Ring Crimper for  $^1\!/_2$  ". Crimps conform to ASTM specifications and is supplied with a go/no-go gauge. Complete with a soft, comfortable grip. OAL 12"

Weight ......4 lbs. (1.8kg)

## 89203 3/4" PEX RING CRIMPER

A PEX Ring Crimper for  $^3/_4$ ". Crimps conform to ASTM specifications and is supplied with a go/no-go gauge. Complete with a soft, comfortable grip. OAL 12"

Weight ......4 lbs. (1.8kg)

#### 89204 1" PEX RING CRIMPER

#### 89206 1/2" AND 3/4" PEX COMBO CRIMPER

A Combination Pex Ring Crimper for  $\frac{1}{2}$ " and  $\frac{3}{4}$ ". Crimps conform to ASTM specifications and is supplied with a go / no-go gauge. Complete with a soft, comfortable grip and long handles for extra leverage. OAL 16"

#### STAINLESS CLAMP PINCHER RATCHET TOOL

The PEX Stainless Clamp Pincher Ratchet Tool with a full cycle mechanism assures consistent water tight crimps, eliminating the need for a crimp gauge. Made from heat treated steel for strength and durability. Its compact design and lightweight frame allow this tool to be extremely versatile when used in confined areas.

Our PEX Stainless Clamp Pincher ratchet tool can be used for  $^3\!/_8$  ",  $^1\!/_2$  ",  $^3\!/_4$  " and 1 ". Crimps conform to ASTM F2098 specifications. OAL 11 "

#### **PEX RING REMOVER**

This unique tool is designed for fitting recovery without damaging the fittings. The high mechanical advantage makes shearing of rings much easier and faster than sawing off a crimped ring. Just two cuts on the ring allow the user to reclaim the fitting. Saves time and money!



#### **CLOSE QUARTERS CRIMP TOOLS**

A unique tool designed for  $^{1}/_{2}$ " and  $^{3}/_{4}$ " pipe sizes. These tools provide a toggle action, which helps to assure a complete crimp cycle. Lightweight with a comfort fit handle, its high mechanical action allows one hand crimping to ASTM specifications. OAL 12"

89215	1/2" Close Quarters Crimp Tool	3.2 lbs. (1.45kg)
89216	3/4" Close Quarters Crimp Tool	



#### 89217 CLAMP CRIMPER

The Close Quarters Tool crimps rings to ASTM F-1087 on  $^3/_8$ ",  $^1/_2$ ",  $^3/_4$ ", and 1" pipe. A wrench is used to torque the bolts down until the gap is eliminated. Convenient 1" and  $^3/_4$ " on one side, flip over and  $^1/_2$ " and  $^3/_8$ " on the reverse. Complete with a gauge to assure crimps are to specifications. OAL  $^3/_2$ "



#### 89211 CLAMP REMOVAL TOOL

This unique tool allows fitting recovery with an effortless torquing action. Apply the socket to a "T" bar or socket wrench and place over the pinched clamp. By turning 90 degrees in a clockwise action and then counter-clockwise the clamp is sheared making fitting recovery quick and easy. Remove all clamps 3/8", 1/2", 5/8", 3/4" and 1" with ONE tool. Wrench nut supplied.

Weight.......1 lb. (0.5kg)



#### RETRACTABLE UTILITY KNIFE

Featuring a curved, comfort design, internal blade storage, interlock system and toolless blade changing.

5761 5 Pack of Replacement Blades



#### SELF-RETRACTING UTILITY KNIFE

Featuring a curved, comfort design, internal blade storage, interlock system and toolless blade changing.

5761 5 Pack of Replacement Blades



#### **MINI TUBING CUTTERS**

For accurate cutting of copper, brass and aluminum tubing.

90721	For 1/8" to 1" (3–25mm) O.D	0.3 lbs. (0.15 kg)
90727	For <sup>1</sup> / <sub>8</sub> " to 1 <sup>1</sup> / <sub>8</sub> " (3–30mm) 0.D	0.5 lbs. (0.22 kg)
8069	Replacement Cutter Wheel	



# **TELESCOPIC TUBING CUTTER**

For accurate cutting of copper, brass and aluminum tubing. Telescopic cutter wheel feeding system keeps turning radius constant. Includes spare wheel. Swivel deburring tool retracts conveniently into the body.

90734	For <sup>1</sup> / <sub>8</sub> " to 1 <sup>3</sup> / <sub>8</sub> " (3–35mm) 0.D	0.8 lbs. (0.35 kg)

8069 **Replacement Cutter Wheel** 80711 Replacement Deburring Blade



#### **TUBING CUTTER**

Cuts copper, aluminum and thin wall material. Grooved roller allows for close to the flare cut. No tool required for fast wheel change. Ergonomic knob.

8069 **Replacement Cutter Wheel** 



#### **QUICK RELEASE TUBING CUTTER**

Gives clean square cuts on copper, brass, aluminum tubing and thin walled conduit. Changing the cutter wheel allows plastic pipe to be cut. Tool includes two cutter wheels and swivel deburring tool which is stored conveniently in the body of the cutter.

90747	For 1/4" to 3" (6-76mn	n) O.D2 lb	s. (.9kg)
00	101 74 100 (0 1011111	, 0.5	0. (.0.19)

8069 **Replacement Cutter Wheel** 

8068 **Replacement Cutter Wheel for Plastic** 80711 **Replacement Deburring Blade** 

90749



#### **QUICK RELEASE TUBING CUTTER**

Gives clean, square cuts on plastic and non-ferrous metal pipe. Spring loaded cutter wheel feeding system allows slide-action size adjustment and quick release.

iccuirig	recalling system allows slide detion size adjustment and quiet release.		
90748	For 2" to 5" (50–127mm) 0.D		
8066	Replacement Cutter Wheel for plastic		
8067	Replacement Cutter Wheel for non-ferrous metals		

8066 Replacement Cutter Wheel for plastic

8067 Replacement Cutter Wheel for non-ferrous metals



#### STAINLESS STEEL TUBING CUTTERS

Specially designed for cutting stainless steel. All three models have a steel feed screw system and use specially designed cutter wheels with needle bearings for durability and longevity. No tools are required to change the cutter wheel and wheel pin.

90724	$^{1}/_{8}$ " to $1^{1}/_{8}$ " (3–30mm) O.D. Mini Tubing Cutter	0.5 lbs. (0.22kg)
90730	1/8" to 13/4" (3-44.5mm) O.D. Tubing Cutter	
90764	1/4" to 3" (6.35–76.2mm) O.D. Tubing Cutter	2 lbs. (0.9kg)
90799	Replacement Cutter Wheel	





#### **450 COPPER TUBE CLEANER**

Cleans inside and outside 1/2" and 3/4" copper tubing. Leaves copper surface polished and cleaned for optimum solder flow. Replaceable high carbon steel bristles extend tool life beyond that of disposable brushes.

Weight	1 lb.	(0.5kg)
452	Four Piece Replacement Brush Set	



#### 4506 6-IN-1 COPPER TUBE CLEANER

Cleans inside and out plus deburrs the inside diameter of 1/2" and 3/4" tubing with hardened steel reamer/deburrer.

Weight	1 lb.	(0.5kg)
452	Four Piece Replacement Brush Set	



#### **4992 CLOSE QUARTERS TUBING CUTTER**

Designed for plumbing remodeling, commercial boiler and air conditioning jobs, where standard cutters simply don't have the room. Cuts thin-wall material like traps and tailpieces with no distortion. Featuring a small swing radius of 3 - 5/8", it's perfect for under vanities, waste and overflows, and close to walls. Eliminates sawing which can loosen joints. Cutter comes with cutter wheel (No. 8038 for non-ferrous materials. Also available is cutter wheel (No. 8033 to cut plastic). For 1/4" to 23/8" (6-59mm) O.D. non-ferrous tube and plastic pipe and tube.

Weight ......1.5 lbs. (0.7kg) 8038 Replacement Cutter Wheel for Copper

8033 Replacement Cutter Wheel for Plastic







#### **AUTO-C TUBING CUTTERS**

With it's C-shape, these cutters are easy to grip and do not require any swing space. Just turn the cutter in the direction of the arrow and the cut will be complete in seconds. The spring loaded cutter wheel self-feeds with consistent pressure. Cuts type-K. L and M. copper and CTS CPVC.

5690	Auto-C Cutter 1/2" (15.9mm)	0.5 lb.	(0.23kg)
5691	Auto-C Cutter 3/4" (22.2mm)	0.5 lb.	(0.23kg)
5692	Auto-C Cutter 1" (28.6mm)	0.5 lb.	(0.23kg)
8046	Replacement Cutter Wheel		



# RATCH CUT TUBE AND PIPE CUTTERS 3590 RATCH CUT WITH METAL HANDLE

Uniquely designed for fast, accurate pipe cutting, especially in confined, nearly inaccessible locations. Suitable for use on mild or stainless steel, copper or thinwall PVC and CPVC tubing from 1/8" to 3/8" (3-9mm).

Weight		(0.23kg)
8040	Replacement Cutter Wheel	



#### 3790 RATCH CUT WITH METAL HANDLE

A larger version of our Model 3590 cutter described above. Use it for quick, precise cutting of mild or stainless steel, copper or thinwall PVC and CPVC tubing from 5/16" to 11/8" (8-27mm).

Weight		(0.68kg)
8041	Replacement Cutter Wheel	
8044	Cutter Wheel for thin walled stainless steel	

# PLASTIC PIPE & COPPER TUBE TOOLS

CONTINUED



#### **INNER & OUTER REAMER**

For fast, clean, inner and outer reaming and outer deburring/beveling of  $^3/_8$ "-2" copper and stainless steel tubing. Made of hardened steel construction.



#### **DEBURRING TOOL**

Ideal for removing internal burrs in copper, plastic, aluminum and steel tubing. Features long lasting replaceable high speed steel blade and plastic handle with built-in pocket clip.

919	5 Pack of Deburring Tools	0.15 lbs.	(0.06 kg)
921	10 Pack of Deburring Tools	0.6 oz.	(0.17 kg)
925	50 Pack of Deburring Tools	1.45 oz.	(0.65 kg)
80711	Replacement HSS Blade		



#### **4700 HAMMERHEAD FLARING TOOL**

Four interchangeable heads flare  $^3/_4$ "-2" type-K copper pipe. The 6 lb. slide hammer is easier and safer than regular hammers and the pressure-relieving heads allow flaring with water in the line. Complete with custom carrying case.



#### **4900 REROUNDING TOOL KIT**

WHEELER-REX Rerounding Tools quickly and easily reround soft type-K copper tubing for proper seal when using compression fittings. For safety, use only with brass hammers. For  $^{3}/_{4}$ " through 2" copper pipe, compact, divided kit makes transport easy.

Weight		12 lbs.	(5.4kg)
49075	3/4" Rerounding Tool*	1 lbs.	(0.45kg)
49100	1" Rerounding Tool*	1.6 lbs.	(0.7kg)
49150	11/2" Rerounding Tool*	2.7 lbs.	(1.2kg)
49200	2" Rerounding Tool*	5.5 lbs.	(2.5kg)
	* Included in 4900 Tool Kit		

# REPLACEMENT CUTTER WHEELS

WHEELER-REX		RIDGID°		REED®	
METAL TUBING C	UTTERS				
CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.	CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.	CUTTER WHEEL MODEL NO.	TUBING CUTTER MODEL NO.
8012	9290, 9291	E1240	10, 15, 20	OSS	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8015	9290, 9291	F158	10, 15, 20	0	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8021		E2191	30, 40, 106, 108, 109, 122, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8025	9490	E2558	30, 40, 106, 108, 109, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8034		E3469	101, 103, 104, 105, 117, 118, 131, 132, 150, 151, 152, 153, 205	345T	MC2
8038	4992, 4991, 4990				
8040	2590, 3590				
8041	3790				
8044 (SS)	3790				
8045	90722	E4546	105, 131, 132, 150 - 153, 205	R4546	MC2
8046	5690, 5691, 5692			SLRCW	TC50SL, TC75SL, TC1SL
8067	90748, 90749	E2558	30, 40, 106, 108, 109, 133, 134, 136, 154, 156	30-40	TC3Q, TC4Q, TC5Q, TC6Q, TC8Q
8069	90710, 90721, 90727, 90734, 90747	F158	10, 15, 20	0	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8071	90735, 90728, 90750			73505	TC14, TC166, MC3
90799 (SS)	90724, 90730, 90764				

PLASTIC TUBING CUTTERS					
8033	4992				
8037		E2156, E5299, E2157		3-6PVC	TC3Q, TC4Q, TC5Q, TC6Q
8066	90748, 90749		30P, 40P, 133P, 134P, 136P, 154P, 156P, 106, 109P	80P	TC6Q, TC8Q
8068	90747				
8073	90750			0P2	TC1Q, TC1.6Q, TC2Q, T10, T15, T20
8074	90751				
8075	90752				

PIPE CUTTERS					
8001	2690 (Steel)	F514, M-50, F3, F3S	1, 2, 42, 300, 50, 1A, 2A, 42A, 201, 202	2RBHD	2-1, 2-1Q, 2-4WG, 2-3, 2-3Q, 2-4
8003		E1032	300, 535, 1822-1, MACH	HX2, 1/2	
8004	4690 (Steel)	FS229S			
8006		F367	6S, 208, 209	R367	
8039	5090				
8082	2690 (SS)				
700201	32900, 42900				

HINGED CUTTERS					
8050	95041, 95240			HS4	H4
8051	95041, 95240			HS4	H4
8052	95061, 95460			HS6	H6
8053	95061, 95081, 95121, 95460, 95680			HI6	H6, H8, H12
8054	95081, 95121, 95680			HS8-12	H8, H12
8076	95061, 95081, 95121, 95460, 95680			H6PSE5	H6, H8, H12

THREADING MACHINES				
60322	WHEELER-REX MODELS 6990, 6991, 7991, 8991			
60324	WHEELER-REX MODELS 7890, 6090, 7090, 8090, 6190, 6290, 6390, 6490, 6790			
60390	CUTTER BLADE FOR 6794 & 6590			
60310	HSS CUTTER WHEEL FOR 6790, 6793			
60301	HSS CUT-0FF BLADE FOR 6794 & 6590			

# **GROOVING & FABRICATION**



#### **PORTABLE ROLL GROOVERS**

For 1"-6" Schedule 5 to Schedule 40 steel. T-handle feed design minimizes operator fatigue. No separate ratchet required. SAFER – short lengths of pipe stay on rollers without operator assistance. All models are lightweight, compact and easily mounted. Carriage does not need to be removed for installation.

8400	2"-6" Roll Groover with Base for 6090, 7090 & 8090	33 lbs.	(15kg)
8401	2"-6" Roll Groover with Base for Model 300	33 lbs.	(15kg)
8402	2"-6" Roll Groover with Base for Model 300 Compact	34 lbs.	(15.5kg)
8403	2"-6" Roll Groover with Base for 6790	35 lbs.	(15.9kg)

#### **Accessories:**

84000	Base Only for Models 6090, 7090 & 8090 Machines
84001	Base Only for Model 300 Machines
84002	Base Only for Model 300 Compact Machines
84003	Base Only for Model 6790 Machines
700628	2"-6" Roller & Shaft Set for Copper Pipe
700639	1" Roller & Shaft Set for Steel
700640	11/4"-11/2" Roller & Shaft Set for Steel



#### **HYDRAULIC ROLL GROOVER**

For use with a pipe threading machine. Makes grooves 1"–16" Schedule 10 and 1"–12" Schedule 40. Conveniently and easily attaches to your 2" or 4" pipe threading machine. The carriage, reamer or die heads do not need to be removed from the machine. A simple mounting bracket provides quick attachment to WHEELER-REX 6090, 7090, 8090 and 6790 Threading Machines as well as Model 300 Machines.

9700	Hydraulic Roll Groover with Base for WHEELER-REX 6090, 7090 & 8090 94 lbs.	(42.7kg)
9701	Hydraulic Roll Groover with Base for WHEELER-REX 679094 lbs.	(42.7kg)
9703	Hydraulic Roll Groover with Base for Model 300 Machines	(42.7kg)

#### Features:

- · Compact, light weight, powerful and large capacity
- Built-in hydraulic cylinder
- Easy operation with guide roller to prevent the pipe from slipping and helps to eliminate vibration
- Unit comes standard with 2"-6" Roller Set (341133) for Schedule 40
- Capacity: 1"-16" Schedule 10 Steel (341125 Spacer)
  - 1"-12" Schedule 40 Steel Pipe



9700 Hydraulic Roll Groover on Threader.

#### HYDRAULIC ROLL GROOVER ACCESSORIES

—	
341560	Machine Mounting Kit for WHEELER-REX 6090,7090 & 8090
341562	Machine Mounting Kit for WHEELER-REX 6790
341563	Machine Mounting Kit for Model 300 Machines
341118	Roller Set 1"- 11/2" Sch 5 and 10, Thin-Wall SS
341119	Roller Set 2"- 3" Sch 5 and 10, Thin-Wall SS
341120	Roller Set 4"-6" Sch 5 and 10, Thin-Wall SS
606460	Roller Set 1"- 11/2" Sch 10-40
606520•	Roller Set 2"- 6" Sch 10-40
606459	Roller Set 8"- 12", 8" Sch 40 / 8"-12" Sch 10-30
341137	Roller Set 10"- 12" Sch 40
341138	Roller Set 14"- 16" Sch 10
341141	Shaft 1"- 1 <sup>1</sup> / <sub>2</sub> "
341124	Guide/Gauge for 8" to 12"
<ul> <li>Incli</li> </ul>	ided with hasic machine



#### HYDRAULIC ROLL GROOVING MACHINES

Produces factory grooves on 1"–12" Schedule 10 and 1"–8" Schedule 40 steel pipe. Unique features include horizontal self-centering head, finished groove indicator light and optional electric power pump. Two (2) 220V outlets required; one (1) for the motor and one (1) for the hydraulic system. Standard rollers included for 2"–6".

#### Specifications: 220V 50-60Hz ONLY

Standard Accessories: 2"– 6" rollers, toolbox and tools.
7702 2"– 6" with manual pump 50-60Hz Only

7703 2"-6" with electric power pump 50Hz Only

#### **Optional Accessories:**

341118 Roller Set 1"- 11/2" Sch 5 & Sch 10, Thin Wall SS
341119 Roller Set 2"- 3" Sch 5 & Sch 10, Thin Wall SS
341120 Roller Set 4"- 6" Sch 5 & Sch 10, Thin Wall SS

**606460** • Roller Set 1"-11/2" Sch 10-40 **606520** • Roller Set 2"-6" Sch 10-40

606459 Roller Set 8"-12", 8" Sch 40 / 8"-12" Sch 10-30

341137 Roller Set 10"- 12" Sch 40 341136 Roller Set 14"- 16" Sch 10 606461•• Shaft 1"-11/2"

Included with basic machine.

Both items are required to groove 1" - 11/2" pipe



Support stand not included.

#### **ORBITAL PIPE CUTTER**

For 4"-12" (100-300mm) steel and ductile iron pipe. The clamshell frame and modular design make this machine fast and easy to set up and operate. A single frame and gear plate make the orbital the most economical unit for its size range. Standard 115V electric power. Complete with all necessary accessories and packed in a storage case.

6412 Cut & Bevel, DI & CI pipe 4"-12" (100-300mm)
8412 Cut & Bevel, steel pipe 4"-12" (100-300mm)
5412 Cut & Groove, steel pipe 4"-12" (100-300mm)

#### Spares and Accessories:

 220267
 Cut-Off Blade, DI

 220808
 RH Cut-Off Blade, steel

 220809
 LH Cut-Off Blade, steel

 220705
 30° Steel Bevel Blade

 220706
 37 ½° Steel Bevel Blade

 220770
 45° Steel Bevel Blade

 220707
 45° DI Bevel Blade

220855 Support Stand (not included with orbital as standard feature-purchased separately)

#### MANTIS™ REPLACEMENT BLADES

Blade Number	Material	Number of Teeth
475200		8
475201		10
475202	Alloy	14
475203		18
475204		24
475210		10
475211	High-Speed	14
475212	Steel Bimetal	18
475213		24





WHEELER-REX Drop Heads and Dies are ideal for in-place threading from 1/2" – 2" and are designed to fit Wheeler Ratchet Handle 43310 as well as the Ridge Tool Company Models 12R, OO-R, 111-R, O-R, 30A & 31A, 600 & 700 Power Drives, Reed Mfg. DHR12 Series Drop Heads and Berkley Tool BT40000 Series Drop Heads.

4200	Complete with Tool Box for 1/2"-2"52 lbs.	(23.6kg)
4202	Complete with Tool Box for 1/2"-1"27 lbs.	(12kg)
4207	Complete with Tool Box for 1/2"-11/4"39 lbs.	(18kg)
4211	Complete with Tool Box for 1"-2"42 lbs.	(19kg)
4213	Complete without Tool Box for 1/2"-2"35 lbs.	(16kg)
4215	Complete with Tool Box for 1/2"-2" BSPT49 lbs.	(22kg)
43310	Ratchet Handle5.5 lbs.	(2.5kg)
43300	Replacement Carrying Case14 lbs.	(6kg)



#### HAND OPERATED OILER

The WHEELER-REX hand operated oiler features a metal reservoir bucket, removable plastic scrap/chip tray and 56" hose with trigger nozzle. Includes one gallon of ThreadMaster Oil.

5900	Weight19 lbs.	(8.6kg)
59050	Renlacement Hand Pumn	



#### **MINI POWER DRIVES**

Lightweight and portable, the WHEELER-REX Mini Power Drive can thread up to 11/4" diameter pipe or conduit and 1" bolt or rod in just seconds. Accepts 12R style die heads. Requires only 13/4" clearance for working in trenches, overhead and in tight quarters and can tighten nuts, drive cable pullers, turn hoists and jacks, open and close valves. Mechanical high speed reverse speeds removal after threading.

640	Power Drive, 12R Adapter & Safety Vise with Case	38 lbs.	(17ka)
UTU	I UWGI DIIVG. IZII AUGDIGI X JAIGIV VISG WIIII GASG		11/10

#### **Accessories:**

6402 12R Adapter for 640

#### Safety Vise:

80115 Absorbs torque from Power Drives to reduce fatigue and protect the operator 6 lbs. (3kg)

#### 12R STYLE DIES - NPT

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
837825	37825	1/2"	NPT	Alloy
837830	37830	3/4"	NPT	Alloy
837835	37835	1"	NPT	Allov
837840	37840	11/4"	NPT	Allov
837845	37845	11/2"	NPT	Allov
837850	37850	2"	NPT	Alloy

#### 12R STYLE DROP HEAD WITH DIES - NPT

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
837390	37390	1/2"	NPT	Alloy
837395	37395	3/4"	NPT	Allov
837400	37400	1"	NPT	Allov
837405	37405	11/4"	NPT	Allov
837410	37410	11/2"	NPT	Allov
837415	37415	2"	NPT	Allov

#### 12R STYLE DIES - BSPT

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
866125	66125	1/2"	BSPT	Alloy
866130	66130	3/4"	BSPT	Alloý
866135	66135	1"	BSPT	Alloy
866140	66140	11/4"	BSPT	Alloý
866145	66145	11/2"	BSPT	Alloý
866150	66150	2"	BSPT	Alloy

#### 12R STYLE DROP HEAD WITH DIES - BSPT

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
865965	65965	1/2"	BSPT	Alloy
865970	65970	3/4"	BSPT	Allov
865975	65975	1"	BSPT	Allov
865980	65980	11/4"	BSPT	Allov
865985	65985	11/2"	BSPT	Allov
865990	65990	2"	BSPT	Alloy



#### 8991 SIDEKICK III PIPE THREADER

The WHEELER-REX Model 8991 is a full-featured threading machine for 1/2" to 1" pipe. Featuring front and rear chucks, an auto-open auto-oiling notch-type die head, safety auto shut off, larger carriage & cutter handles and a unique one blade reamer.

#### Model 8991 Features:

- Auto open notch die head
- Front and rear chucks
- Auto-oiling die head
- Large scrap tray
- Weighs only 58 pounds
- 1/2"-1" die head Includes:
  - Two sets of dies: 1/2"-3/4" and 1"
- One blade reamer • 1" pipe threading time
  - 16 seconds

· Safety auto shut off

- Built-in carrying handle
- · Foot switch
- · Spare cutter wheel





Standard Capacity: 1/2"-1"

Dimensions: 15" x 11" x 12"


Voltage: 115 Volt

Motor: 400 Watt series, single phase

Free Speed: 55 RPM Net Weight: 58 lbs.

Optional:

- 1/4"-3/8" NPT dies
- 1/4"-1" NPT Die Head
- 841 Stand





8992 Same as 8991 except comes complete with 60131 manual opening die head for  $\frac{1}{4}$ "-1". Along with  $\frac{1}{4}$ "- $\frac{3}{8}$ ",  $\frac{1}{2}$ "- $\frac{3}{4}$ " and 1" NPT dies.

> Net weight...... 58 lbs. (26kg)

8993 Same as 8991 except comes complete with two 1/2"-1" quick opening 70131 die heads and one each 1/2"-3/4" and 1" NPT dies.

8998 Same as 8991 except comes complete with 220V motor.

> Net weight...... 58 lbs. (26kg)

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS









#### 8090

Features complete **interchangeability** with the Model 300 dies and die heads. This portable and compact, high-performance threading machine has a self-opening die head and through the die head oiling. Completely equipped to cut, thread and ream.

**Features:** For  $\frac{1}{2}$ " to 2" pipe, 110/120V, single phase 700W series motor, average noise

level: 85db, maximum amperage under load: 15.3, no load RPM: 39

Includes:  $^{1}/_{2}$ "-2" die head, two sets of NPT dies:  $^{1}/_{2}$ "- $^{3}/_{4}$ " and 1"-2", spare cutter wheel,

foot switch, 4 leas.

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.

8096 Same as 8090 except comes with two 80118 Die Heads.

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.

8097 Same as 8090 except comes with 897065 Universal Die Head for 1/8"-2".

 Weight, packed
 186 lbs. (84.5kg)

 Net weight
 140 lbs. (64kg)

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.

8098 Same as 8090 except comes with 220V motor.

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.



BALL DETENTS ARE STANDARD ON ALL WHEELER-REX DIE HEADS



## **UNIVERSAL REPLACEMENT DIES**

WHEELER-REX Dies are manufactured from Tool Steel and are designed to fit Wheeler Die Head 897065 as well as the following Ridge Tool Models 504A, 711, 713, 811A, 815A, 816, 817, and 842.

#### **UNIVERSAL DIE HEAD**

Wheeler # Ridge #

#### PIPE DIES FOR UNIVERSAL DIE HEADS - NPT

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
847745	47745	1/2"-3/4"	NPT	Tool Steel
847750	47750	1"-2"	NPT	Tool Steel

# PIPE DIES FOR UNIVERSAL DIE HEADS - NPT FOR STAINLESS STEEL

Wheeler #	Ridge #	Nominal Pipe Size	Type Thread	Die Material
847785	47785	1/2"-3/4"	NPT	HSS
847790	47790	1"-2"	NPT	HSS



#### 6790

The 6790 features a self-opening die head, with through die head oiling. Ultimate accuracy with quick changes between pipe sizes, producing quality threads. The 6790 offers adjustable thread length, three-stage oil filtration system, and a sturdy three flute reamer that covers the entire 1/2"-4" range. The 6790 is a three speed machine that is powered by a durable condenser motor, with an extremely low noise level. Completely equipped to cut,

Features: For 1/2" to 4" pipe, 110V/120V or 220V/230V, single phase 1KW condenser motor, average noise level: 72db, maximum amperage under load: 18.5

no load RPM: 15/27/48, 1Hp, 50/60HZ

Includes: Two die heads:  $\frac{1}{2}$ " – 2" and  $\frac{2^{1}}{2}$ " – 4", three sets of NPT dies:  $\frac{1}{2}$ " –  $\frac{3}{4}$ ", 1" – 2" and

21/2"-4", spare cutter wheel, foot switch, 4 legs and built-in tool tray.

**Optional:**  $\frac{1}{4}$ "- $\frac{3}{8}$ " NPT,  $\frac{3}{4}$ "-4" beveling and grooving,  $\frac{5}{16}$ "-2" UNC bolt, and  $\frac{1}{2}$ "-4" NPSM Weight 





6793 Same as 6790 except with THREE (3) self-opening NOTCH-TYPE DIE HEADS. This offers accuracy, quick changes between pipe sizes and eliminates switching dies when changing pipe sizes. Completely equipped to cut, thread,









6794 Same as 6790 except with a BLADE-TYPE CUTTER, which is designed for plastic lined pipe, as well as standard steel pipe. Completely equipped to cut, thread, and ream.

Features: For 1/2" to 4" pipe, 110V/120V or 220V/230V, single phase 1KW condenser motor, average noise level: 72db, maximum amperage under load: 18.5 no

load RPM: 15/27/48

**Includes:** Two die heads:  $\frac{1}{2}$ " – 2" and  $\frac{2^{1}}{2}$ " – 4", three sets of NPT dies:  $\frac{1}{2}$ " –  $\frac{3}{4}$ ", 1" – 2" and

2<sup>1</sup>/<sub>2</sub>"-4", spare cutter wheel, foot switch, 4 leas and built-in tool tray.

**Optional:**  $\frac{1}{4} - \frac{3}{8}$  NPT,  $\frac{3}{4} - 4$  beveling and grooving,  $\frac{5}{16} - 2$  UNC bolt, and  $\frac{1}{2} - 4$  NPSM 

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.







#### 6590

This machine has self opening notch type die heads with through die head oiling. These die heads offer accuracy and quick changes between pipe sizes, while providing quality threads. The 6590 is totally gear driven and powered by a condenser motor, producing extremely low noise levels. Quiet operation permits use in hospitals, factories, and in other locations where noise can be a problem. Completely equipped to cut, thread, and ream.

Features: For 2<sup>1</sup>/<sub>2</sub>" - 6" pipe, 110/120V or 220V/230V, single phase .75KW condenser motor, average noise level: 76db, maximum amperage under load: 14.5, no load RPM: 6.1/20.2, 1Hp, 50/60HZ

**Includes:** Two die heads:  $2^{1}/_{2}$ "-4" and 5"-6", two sets of NPT dies:  $2^{1}/_{2}$ "-4", and 5"-6", foot switch, 4 legs and Blade-Type Cutter.

Optional: 2<sup>1</sup>/<sub>2</sub>"-6" beveling and grooving

THREE YEAR WARRANTY, INCLUDING ELECTRIC MOTORS.







#### **THREADER CARTS**

60513 60518	Collapsible Cart for WHEELER-REX 8090 Pipe Threader	, 0,
60506	Threader Cart w/out Toolbox for 6390/6790/6794/6793135 lbs.	(61.4kg)
60507	Threader Cart with Toolbox for 6390/6790/6794/6793178 lbs.	(81kg)
60514	Threader Cart w/out Toolbox for 6590135 lbs.	(61.4kg)
60515	Threader Cart with Toolbox for 6590178 lbs.	(81kg)



#### **NIPPLE ATTACHMENTS**

62000	1/2" NPT Nipple Chuck	(1.4kg)
62001	3/4" NPT Nipple Chuck	(1.4kg)
62002	1" NPT Nipple Chuck3 lbs.	(1.4kg)
62003	11/4" NPT Nipple Chuck5 lbs.	(2.3kg)
62004	1½" NPT Nipple Chuck5 lbs.	(2.3kg)
62005	2" NPT Nipple Chuck5.5 lbs.	(2.5kg)
62006	2 ½" NPT Nipple Chuck8 lbs.	(3.6kg)
62007	3" NPT Nipple Chuck8.5 lbs.	(3.8kg)
62009	4" NPT Nipple Chuck12 lbs.	(5.5kg)



#### **841 PORTABLE THREADER STAND**

Light weight folding stand. Designed to fit model 7991/8991......30 lbs. (14kg)



# WHEELER-REX PIPE THREADING OIL

WHEELER-REX Pipe Threading Oil gives you premium performance at a reasonable price. Blended to thread Stainless Steel, Galvanized as well as Carbon Steel means you only need one oil for all your needs. Low odor and transparent appearance make this fluid pleasant to use in addition to creating quality threads and long die life.



60601	1 Gallon ThreadMaster Oil	8 lbs.	(3.5kg)
60604	1 Quart ThreadMaster Oil	2.5 lbs.	(1kg)
60603	2 Quart ThreadMaster Oil	4.5 lbs.	(2kg)
60602	5 Gallon Pail of ThreadMaster Oil	41 lbs.	(19kg)
60655	55 Gallon Drum of ThreadMaster Oil	434 lbs.	(197kg)
60607	1 Gallon ThreadMaster Oil for Stainless Steel	12 lbs.	(5.4kg)
60608	5 Gallon Pail of ThreadMaster Oil for Stainless Steel	42 lbs. (	19.05kg)



# 6990 PONY 1/4"-3/4" MAXIMUM PIPE RANGE

PART NO.	DIES
60210	1/4" – 3/8" NPT (60131 Die Head)
60211•	1/2"-3/4" NPT (60130 Die Head)
	DIE HEADS
60130•	1/2"-3/4" NPT/Self Opening Notch Style
	SPARE PARTS
60322•	Cutter Wheel
600979	Chuck Jaw Insert Set
602005	Motor Brush Set
602029	Reamer Cone

Included with basic machine.



# 6991 SIDEKICK 1/4"-1" MAXIMUM PIPE RANGE

PART NO.	DIES
60210	1/4"-3/8" NPT (60131 Die Head)
60211•	1/2"-3/4" NPT (60130 & 60131 Die Heads)
60212•	1" NPT (60131 Die Head)
60256	1/2"-3/4" NPSM (60131 Die Head)
60257	1" NPSM (60131 Die Head)
DIE HEADS	
60131•	1/4"-1" NPT/Manual Opening
SPARE PARTS	
60322•	Cutter Wheel
602103	Chuck Jaw Insert Set
602005	Motor Brush Set
602125	Reamer Cone

Included with basic machine.



# 7991 SIDEKICK II AND 8991 SIDEKICK III 1/4"-1" MAXIMUM PIPE RANGE

PART	DIES
60210	1/4"-3/8" NPT Dies (60131 Die Head)
60211•	1/2"-3/4" NPT Dies (60130, 60131 & 70131 Die Heads)
60212•	1" NPT Dies (60131 & 70131 Die Heads)
60213	1/4"-3/8" NPT Dies for S.S. (60131 Die Head)
60214	1/2"-3/4" NPT Dies for S.S. (60131 & 70131 Die Heads)
60215	1" NPT Dies for S.S. (60131 & 70131 Die Heads)
60256	1/2"-3/4" NPSM Dies (60131 & 70131 Die Heads)
60257	1" NPSM Dies (60131 & 70131 Die Heads)
	DIE HEADS
70131•	1/2"-1" NPT/Auto-Open, Notch Type Die Head
60131	1/4"-1" NPT/Manual Opening Die Head
60136	1/4"-3/8" NPT/Auto-Open Die Head
	SPARE PARTS
60322•	Cutter Wheel
62322	Cutter Wheel for Stainless Steel
602103	Chuck Jaw Insert Set
606665	Motor Brush Set
606705	Reamer Blade
	·

Model 6890 was discontinued 11/1/06 and these parts are interchangeable with Model 7890.

# 7890 1/4"-1 1/2" MAXIMUM PIPE RANGE



, 000	
PART NO.	DIES
60200	1/4"-3/8" NPT (60120 Die Head)
60201 •	<sup>1</sup> / <sub>2</sub> "- <sup>3</sup> / <sub>4</sub> " NPT (60120 Die Head)
60202 •	1"-1 <sup>1</sup> / <sub>2</sub> " NPT (60120 Die Head)
60220	1/4"-3/8" HSS NPT (60120 Die Head)
60346	5/16"-18 UNC Bolt (60125 Die Head)
60347	<sup>3</sup> / <sub>8</sub> "-16 UNC Bolt (60125 Die Head)
60348	<sup>7</sup> / <sub>16</sub> "-14 UNC Bolt (60125 Die Head)
60340	1/2"-13 UNC Bolt (60125 Die Head)
60341	<sup>5</sup> / <sub>8</sub> "-11 UNC Bolt (60125 Die Head)
60342	3/4"-10 UNC Bolt (60125 Die Head)
60343	<sup>7</sup> / <sub>8</sub> "–9 UNC Bolt (60125 Die Head)
60344	1"-8 UNC Bolt (60125 Die Head)
60345	1 <sup>1</sup> / <sub>8</sub> "-1 <sup>1</sup> / <sub>4</sub> " 7 UNC Bolt (60125 Die Head)
60349	1 <sup>1</sup> / <sub>2</sub> "-6 UNC Bolt (60125 Die Head)
	DIE HEADS
60120 •	1/4"-11/2" NPT/Manual Opening
60125	<sup>5</sup> / <sub>16</sub> "-1 <sup>1</sup> / <sub>2</sub> " UNC Bolt/Manual Opening
	SPARE PARTS
60324 •	Cutter Wheel
60323	Chuck Jaw Insert Set
	الماريط ملائني الماريط

Included with basic machine.

# 7090 & 8090 1/8"-2" MAXIMUM PIPE RANGE



PART NO.	DIES
70201 •	1/2"-3/4" NPT (70118, 80118 & 897065 Die Heads)
70209 •	1"-2" NPT (70118, 80118 & 897065 Die Heads)
847745	1/2"-3/4" NPT (70118, 80118 & 897065 Die Heads)
847750	1"-2" NPT (70118, 80118 & 897065 Die Heads)
847785	1/2"-3/4" S.S. (70118, 80118 & 897065 Die Heads)
847790	1"-2" S.S. (70118, 80118 & 897065 Die Heads)
	DIE HEADS
80118#	1/2"-2" NPT/Automatic Opening Die Head for 8090
897065	1/8"-2" NPT/Quick Opening Die Head
	SPARE PARTS
60324 •	Cutter Wheel
70235	Chuck Jaw Insert Set
60513	Collapsible Threader Cart for 8090

Included with 8090 basic machine.

# 6090 1/4"-2" MAXIMUM PIPE RANGE



PART NO.	DIES
60200	1/4"-3/8" NPT (60115 Die Head)
60201 •	1/2"-3/4" NPT (60118 Die Head)
60209 •	1"-2" NPT (60118 Die Head)
60220	1/4"-3/8" HSS NPT (60115 Die Head)
60233	1/2"-3/4" S.S. (60118 Die Head)
60238	1"-2" S.S. (60118 Die Head)
60250	1/2"-3/4" NPT for PVC (60118 Die Head)
60251	1"-2" NPT for PVC (60118 Die Head)
60353	3/4" Beveling 37.5° (60117 Die Head)
60354	1"-2" Beveling 37.5° (60117 Die Head)
60338	3/4" Grooving (60117 Die Head)
60339	1"-2" Grooving (60117 Die Head)
60230	1/2"-3/4" Conduit (60116 Die Head)
60231	1"–11/4" Conduit (60116 Die Head)
60232	1 <sup>1</sup> / <sub>2</sub> "-2" Conduit (60116 Die Head)
60346	<sup>5</sup> / <sub>16</sub> "–18 UNC Bolt (60114 Die Head)
60347	3/8"-16 UNC Bolt (60114 Die Head)
60348	<sup>7</sup> / <sub>16</sub> "–14 UNC Bolt (60114 Die Head)
60340	1/2"-13 UNC Bolt (60114 Die Head)
60341	<sup>5</sup> / <sub>8</sub> "–11 UNC Bolt (60114 Die Head)

# Eastern Time 1-800-321-7950 | Fax 440-992-2925 | wheeler@wheelerrex.com



# 6090 1/4"-2" MAXIMUM PIPE RANGE CONTINUED

60342	3/4"-10 UNC Bolt (60114 Die Head)
60343	7/8"-9 UNC Bolt (60114 Die Head)
60344	1"-8 UNC Bolt (60114 Die Head)
60345	1 <sup>1</sup> / <sub>8</sub> " & 1 <sup>1</sup> / <sub>4</sub> " – 7 UNC Bolt (60114 Die Head)
60349	1 <sup>1</sup> / <sub>2</sub> "-6 UNC Bolt (60114 Die Head)
60352	2"-41/2" UNC Bolt (60114 Die Head)
60360	3/4" Beveling Dies for SS (60117 Die Head)
60361	1"-2" Beveling Dies for SS (60117 Die Head)
60362	3/4" Grooving Dies for SS (60117 Die Head)
60363	1"-2" Grooving Dies for SS (60117 Die Head)
	DIE HEADS
60115	1/4"-2" NPT/Manual Opening
60118•	1/2"-2" NPT/Automatic Opening
60114	5/16"-2" UNC Bolt/Manual Opening
60117	3/4"-2" Beveling & Grooving
60112	1/2"-3/4" NPT/Automatic Opening,/Notch type
60113	1"-2" NPT/Automatic Opening,/Notch type
60116	1/2"-2" Conduit/Manual Opening
	SPARE PARTS AND CART
60324•	Cutter Wheel
60318	Chuck Jaw Insert Set
60328	Chuck Jaw Insert Set for Plastic Coated Pipe
60509	Collapsible Threader Cart

• Included with basic machine.

# 6390 1/4"-2" MAXIMUM PIPE RANGE



PART NO.	DIES
60200	1/4"-3/8" NPT (60115 Die Head.)
60201 •	1/2"-3/4" NPT (60112 & 60115 Die Heads)
60220	1/4"-3/8" HSS NPT (60115 Die Head)
60233	1/2"-3/4" S.S. (60112 & 60115 Die Heads)
60208•	1"-2" NPT (60113 Die Head)
60234	1"-2" S.S. (60113 Die Head)
60250	<sup>1</sup> / <sub>2</sub> "- <sup>3</sup> / <sub>4</sub> " NPT for PVC (60112 & 60115 Die Heads)
60252	1"-2" NPT for PVC (60113 Die Head)
60353	3/4" Beveling 37.5° (60117 Die Head)
60354	1"-2" Beveling 37.5° (60117 Die Head)
60338	3/4" Grooving (60117 Die Head)
60339	1"-2" Grooving (60117 Die Head)
60230	1/2"-3/4" Conduit (60116 Die Head)
60231	1"-11/4" Conduit (60116 Die Head)
60232	11/2"-2" Conduit (60116 Die Head)
60346	5/ <sub>16</sub> "–18 UNC Bolt (60114 Die Head)
60347	3/8"-16 UNC Bolt (60114 Die Head)
60348 60340	7/ <sub>16</sub> "–14 UNC Bolt (60114 Die Head)
60341	1/ <sub>2</sub> "-13 UNC Bolt (60114 Die Head) 5/ <sub>8</sub> "-11 UNC Bolt (60114 Die Head)
60342	<sup>3</sup> / <sub>4</sub> "-10 UNC Bolt (60114 Die Head)
60343	7/8"-9 UNC Bolt (60114 Die Head)
60344	1"-8 UNC Bolt (60114 Die Head)
60345	1 <sup>1</sup> / <sub>8</sub> " & 1 <sup>1</sup> / <sub>4</sub> "–7 UNC Bolt (60114 Die Head)
60349	1 <sup>1</sup> / <sub>2</sub> "-6 UNC Bolt (60114 Die Head)
60352	2"-4 <sup>1</sup> / <sub>2</sub> UNC Bolt (60114 Die Head)
	DIE HEADS
60112•	1/2"-3/4" NPT/Automatic Opening/Notch type
60113•	1"–2" NPT/Automatic Opening/Notch type
60114	5/ <sub>16</sub> "-2" UNC Bolt/Manual Open
60115	1/4"–2" NPT/Manual Opening
60117	3/4"–2" Beveling & Grooving
60116	1/2"-2" Conduit/Manual Opening
	SPARE PARTS AND CART
60324•	Cutter Wheel
60306	Chuck Jaw Insert Set for black iron and PVC pipes
60506	Threader Cart NO Toolbox
60507	Threader Cart with Toolbox
	Included with basic machine

## 6790, 6793 & 6794 1/4"-4" MAXIMUM PIPE RANGE





- Included with basic machine.
- Included with 6794 machine.
- ••• Included with 6793 machine.

# 6590 2 1/2"-6" MAXIMUM PIPE RANGE



PART NO.	DIES
60206•	2 <sup>1</sup> / <sub>2</sub> "-4" Tapered or Straight (60127 Die Head)
60235	2 <sup>1</sup> / <sub>2</sub> "-4" NPT S.S. (60127 Die Head)
60253	2 1/2"-4" NPT for PVC (60127 Die Head)
60207•	5"-6" Tapered or Straight (60128 Die Head)
60236	5"-6" NPT S.S. (60128 Die Head)
60255	5"-6" NPT for PVC (60128 Die Head)
60330	2 <sup>1</sup> / <sub>2</sub> "-4" Beveling 37.5° (60121 Die Head)
60332	2 <sup>1</sup> / <sub>2</sub> "-4" S.S. Beveling 37.5° (60121 Die Head)
60331	5"-6" Beveling 37.5° (60122 Die Head)
60333	5"-6" S.S. Beveling 37.5° (60122 Die Head)
60227	2 <sup>1</sup> / <sub>2</sub> "-3 <sup>1</sup> / <sub>2</sub> " Grooving (60121 Die Head)
60228	4" Grooving (60121 Die Head)
60357	2 <sup>1</sup> / <sub>2</sub> "-3 <sup>1</sup> / <sub>2</sub> " Grooving Dies for S.S. (60121 Die Head)
60358	4" Grooving Dies for S.S. (60121 Die Head)
60359	5"-6" Grooving Dies for S.S. (60122 Die Head)
60229	5"-6" Grooving (60122 Die Head)
	DIE HEADS
60121	2 <sup>1</sup> / <sub>2</sub> "-4" Beveling & Grooving
60122	5"-6" Beveling & Grooving
60127•	2 <sup>1</sup> / <sub>2</sub> "-4" NPT Notch Style Tapered or Straight Automatic Opening
60128•	5"-6" NPT Notch Style Tapered or Straight Automatic Opening
	ACCESSORIES
60390•	Cut-Off Blade
60301	HSS Cut-Off Blade
220204	HSS 10° Bevel Blade
60310	Cutter Wheel
600280	Straight Profile Block Assembly
60514	Threader Cart NO Toolbox
60515	Threader Cart with Toolbox
60307	Chuck Jaw Insert Set
60327	Chuck Jaw Insert Set for Plastic Coated Pipe



6790 mounted on 60507 cart.

# HYDROSTATIC TEST PUMPS



#### MANUAL HYDROSTATIC TEST PUMPS

Ideal for testing residential water lines. Also for pressure testing small pressure tanks, sprinkler, boiler and solar systems. Lightweight and easy to use.  $^3/_4$ " garden hose female inlet and  $^9/_{16}$ "–18 JICF male outlet. Equipped with shut off valve, gauge, and adjustable internal relief valve. 10 foot output hose included.

Features: 300psi (20 bar)

• **29200**......12 lbs. (5.5kg)

#### **Accessories:**

- 3917 10' High-Pressure Output Hose (1/4" NPT male outlet connection)
- 29250 Pump Rebuild Kit
- 34550 10' Long Suction Hose with strainer (3/4" male garden hose connection)



Features: 1000psi (68 bar)

#### **Accessories:**

- $\bullet$  3917 10' High-Pressure Output Hose (½" NPT male output connection)
- 29250 Pump Rebuild Kit
- 34550 10' Long Suction Hose with strainer (3/4" male garden hose connection)



Features: 870 psi/60 bar, 1/2" connections

#### **Accessories:**

- 3917 10' High-Pressure Output Hose (1/4" NPT male outlet connection)
- 29950 Pump Repair Kit

Designed especially for use in heating, compressed air, refrigeration systems, oil installations and sprinkler systems. Complete with 2.6 gallon stainless steel integral tank and 10 ft. output hose.

## **GAS POWERED HYDROSTATIC TEST PUMPS**

Ideal for certifying the integrity of newly installed or repaired water lines, sewer lines, commercial sprinkler systems, and pressure vessels. All gasoline driven models come with Briggs & Stratton™ Intek Pro or Honda engines and are backed by their warranties. Recirculating systems provide pump protection and water conservation. Carts are wheeled for ease of movement. All units come standard with 10 ft. high-pressure output hose and 10 ft. suction hose with strainer.



### **ROLLER PUMPS**

Features: 5.4 gpm/300 psi (20.5 lpm/21 bar)

- 46301 with 6.5 hp. B&S engine, Cart w/wheels ......151 lbs. (69kg)
- **463010** with 5.5 hp Honda engine, Cart w/wheels ......150 lbs. (68kg)

## **Accessories:**

- 36352 Pump Repair Kit
- 34550 10' Suction Hose
- 221065 10' High-Pressure Output Hose



## **TWIN PISTON PUMPS**

Features: 10 gpm/400 psi (38 lpm/28 bar)

• <b>46453</b> with 6.5 hp. B&S engine, Cart w/wheels	(74kg)
• 464530 with 5.5 hp Honda engine, Cart w/wheels	(72kg)
• <b>36454</b> with 6.5 hp. B&S engine, Roll-cage	(61kg)
• 364540 with 5.5 hn Honda engine Roll-cage 136 lbs	(61ka)

### **Accessories:**

- 36351 Pump Repair Kit
- 34550 10' Suction Hose
- 221065 10' High-Pressure Output Hose



### TRIPLEX PLUNGER PUMP

Features: 3.5 gpm/3000 psi (13 lpm/206 bar)

## **Accessories:**

- 36395 Valve Kit
- 36396 Pump Seal Kit
- 34550 10' Suction Hose
- 220577 10' High-Pressure Output Hose



## TRIPLEX PLUNGER PUMPS

Features: 3.5 gpm/1200 psi (13 lpm/82bar)

• <b>46200</b> with 6.5 hp. B&S engine, Cart w/wheels	(59kg)
• <b>462000</b> with 5.5 hp Honda engine, Cart w/wheels130 lbs.	(59kg)
• <b>36200</b> with 6.5 hp. B&S engine, Roll-cage	(40kg)
• <b>362000</b> with 5.5 hp Honda engine, Roll-cage	(40kg)

### Accessories:

- 34052 Pump Repair Kit
- 34053 Pump Seal Kit
- 34550 10' Suction Hose
- 220577 10' High-Pressure Output Hose

## DROSTATIC TEST PUMPS



## TRIPLE DIAPHRAGM PUMPS ....CAPABLE OF HANDLING 10% CHLORINE SOLUTIONS

Features: 10 gpm/500 psi (37.8 lpm/35 bar)

**Udor Pump Models** 

• 46501 with 6.5 hp. B&S engine, Cart w/wheels	161 lbs.	(73kg)
• 465010 with 5.5 hp Honda engine, Cart w/wheels	162 lbs.	(73kg)
• 46503 with 6.5hp B&S engine, Roll-cage	155 lbs.	(70kg)
• 465030 with 5.5hp Honda engine, Roll-cage	155 lbs.	(70kg)
• 46506 with 6.5 hp B&S engine, caged with handles and 4 wheels	181 lbs.	(82kg)
• 465060 with 5.5 hp Honda engine, caged with handles and 4 wheels	181 lbs.	(82kg)
Comet Pump Models		
46521 with 6.5 B&S engine, Cart w/wheels	155 lbs.	(70kg)
• 465210 with 5.5 Honda engine, Cart w/wheels	155 lbs.	(70kg)
46523 with 6.5 B&S engine, Roll-cage	150 lbs.	(68kg)
• 465230 with 5.5 Honda engine, Roll-cage	150 lbs.	(68kg)
• 46526 with 6.5 hp B&S engine, caged with handles and 4 wheels	181 lbs.	(82kg)



### **Accessories:**

- 36345 Pump Repair Kit for 46501, 465010, 46701, 467010
- 36349 Pump Repair Kit for models 46500 and 465000
- 36391 Pump Repair Kit for 46521, 4645210, 46523, 465230, 46526, 465260

• 465260 with 5.5 hp Honda engine, caged with handles and 4 wheels....... 181 lbs.

- 36345 Pump Repair Kit for 46503, 465030, 46506, 465060
- 34550 10' Suction Hose
- 221065 10' High-Pressure Output Hose for Udor pumps
- 220577 High Pressure Output Hose for Comet pumps
- 34562 Two Wheel & Handle Kit
- 34563 25 Gallon Tank Kit
- 34564 Four Wheel & Handle Kit



## TRIPLE DIAPHRAGM PUMPS ....CAPABLE OF HANDLING 10% CHLORINE SOLUTIONS

(82kg)

Features: 15 gpm/300 psi (57 lpm/21 bar)

• 46600 with 6.5 hp. B&S engine, Cart w/wheels	173 lbs.	(79kg)
466000 with 5.5 hp Honda engine, Cart w/wheels	167 lbs.	(76kg)
eatures: 32 gpm/300 psi (121 lpm / 21 bar)		

## Fea

(103kg)

- 36347 Pump Repair Kit for models 46600 and 466000
- 36390 Pump Repair Kit for models 46800 and 468000
- 36392 Pump Repair Kit for model 468260
- 34551 10' Intake Hose for models 46600 and 466000
- 700685 10' Intake Hose for model 468260



## ELECTRIC POWERED HYDROSTATIC TEST PUMPS PORTABLE

Features: 4 gpm / 300 psi (15 lpm / 20 bar), 1/2hp, 115/230V, 60Hz motor

 39300 Ideal for certifying fire sprinkler lines, commercial plumbing and industrial testing. Compact, lightweight for portability, but yet powerful and rugged for the professional. Built in adjustable pressure regulator.

#### Accessories:

- 39350 Pump Repair Kit
- 34550 10' Suction Hose



## TWIN PISTON PUMPS

Features: 3 gpm / 500 psi (11 lpm / 35 bar) 1hp capacitor start motor

#### **Accessories:**

- 36361 Pump Repair Kit
- 34550 10' Suction Hose



## **DUPLEX PLUNGER PUMPS**

Features: 1 gpm / 1000 psi (3.7 lpm / 68 bar) 1hp capacitor start motor

- **33100** 115/230V, single phase, 60Hz, Roll-cage .......110 lbs. (50kg)

### **Comet Pump Models**

## Accessories:

- 36389 Pump Repair Kit
- 34550 10' Suction Hose



## TRIPLEX PLUNGER PUMPS

Features: Single phase, 1.5hp, 15amp capacitor start motor, Cart w/wheels

•	<b>47100</b> 2.2gpm / 1000psi (8.3 lpm / 68 bar), 115V, 60Hz	127 lbs.	(57kg)
•	<b>47101</b> 2.2gpm / 1000psi (8.3 lpm / 68 bar), 220V, 59Hz	143 lbs.	(65kg)
•	<b>47102</b> 1.1gpm / 2000psi (4.1 lpm / 138 bar), 115V, 60Hz	127 lbs.	(57kg)
•	<b>47103</b> 1.1gpm / 2000psi (4.1 lpm / 138 bar), 220V, 50Hz	127 lbs.	(57kg)
•	<b>47105</b> 2.2gpm / 2000psi (8.3 lpm / 138 bar), 115V, 60Hz,	127 lbs.	(57ka)

### **Accessories:**

- 34052 Valve Kit
- 34053 Pump Seal Kit
- 34550 10' Suction Hose



## TRIPLEX PLUNGER PUMP

Features: 3.5 gpm / 3000psi (13.25 lpm / 206 bar), 7.5hp 208/230V 3-phase, 60Hz motor

## **Accessories:**

- 34056 Pump Seal Kit
- 34057 Valve Kit
- 34550 10' Suction Hose



## PNEUMATIC POWERED HYDROSTATIC TEST PUMPS

Features: 1 gpm / 1500psi (3.7 lpm / 103 bar) 40-100psi @ 75 cfm required

Features: 0.5 gpm/ 3,000psi (1.8 lpm / 206 bar) 40-100 psi @ 75 cfm required

Features: 0.088gpm / 10,000psi (0.3 lpm / 689 bar) 100 psi @ 28 cfm required

#### **Accessories:**

- 32151 Fluid Section Repair Kit for 32150
- 32152 Air Section Repair Kit for 32150 and 32300
- 32301 Fluid Section Repair Kit for 32300
- 32451 Air Section Repair Kit for 32450
- 32452 Fluid Section Repair Kit for 32450



## **FIRE HOSE TESTERS**



Features: 3 gpm/500 psi, (11 lpm/35 bar), 115V, single-phase, 1 hp. capacitor motor, one (1) 2  $^{1}/_{2}$ " NST swivel female quick fill inlet and two (2) 2  $^{1}/_{2}$ " NST male outlets with individual ball valves. Cage mounted on swivel casters. Inlet and outlet hoses not provided.

Features: 3 gpm/500 psi, (11 lpm/35 bar), 115V, single-phase, 1 hp. capacitor motor, one (1) 2  $^{1}/_{2}$ " NST swivel female quick fill inlet and four (4) 2  $^{1}/_{2}$ " NST male outlets with individual ball valves. Cage mounted on swivel casters. Inlet and outlet hoses not provided

Features: 10 gpm/400 psi, (37.8 lpm/27 bar), 5.5hp Honda engine, one (1) 2  $^{1}/_{2}$ " NST swivel female quick fill inlet and four (4) 2  $^{1}/_{2}$ " NST male outlets with individual ball valves. Cage mounted on two-wheeled cart with solid tires.






## TRASH PUMPS







## 2" TRASH PUMPS

Features: 2" Suction / Discharge ports, 180gpm / 681 lpm, max solids up to 1"

• <b>56200</b> With 6.5hp B&S Engine (Caged)100 lbs.	(45.5kg)
• <b>56201</b> With 6.5hp B&S Engine on wheeled cart140 lbs.	(63.6kg)
• <b>562000</b> With 5.5hp Honda Engine (Caged)100 lbs.	(45.5kg)
• <b>562001</b> With 5.5hp Honda Engine on wheeled cart140 lbs.	(63.6kg)

#### Accessories:

- 56250 2" x 20' Suction Hose
- 56251 2" x 25' Discharge Hose
- 276270 Pump Repair Kit



## 3" TRASH PUMPS

Features: 3" Suction/ Discharge ports, 300gpm / 1135 lpm, max solids up to 1.25"

• 56300 With 6.5hp B&S Engine (Caged)	132 lbs.	(60kg)
• 56301 With 6.5hp B&S Engine on wheeled cart	150 lbs.	(68kg)
• 563000 With 5.5hp Honda Engine (Caged)	134 lbs.	(61kg)
• 563001 With 5.5hp Honda Engine on wheeled cart	150 lbs.	(68kg)

#### Accessories:

- 56350 3" x 15' Suction Hose
- 56351 3" x 25' Discharge Hose
- 276271 Pump Repair Kit



## **MUDSUCKER DIAPHRAGM STYLE TRASH PUMPS**

Features: 3" Suction/Discharge ports, 90gpm / 340 lpm; for sewage, slurry, mud, thick liquids, max solids up to 1-5/8"

• 56310 With 6.5hp B&S Engine	179 lbs.	(81kg)
• 563100 With 5 5hn Honda Engine	181 lhe	(82ka)

## **Accessories:**

- 56350 3" x 15' Suction Hose
- 56351 3" x 25' Discharge Hose



## **VACUUM TEST ASSEMBLY**

700536	1 lb.	(0.45kg)
--------	-------	----------

An easy way to check a trash pump for proper suction. Verify proper operation before putting a pump into service. Simply prime pump, place flat face over suction port and start pump.



## 4160 TRIPOD VISE STAND

For  $^{1}/_{8}$ " – 6" pipe capacity. Lightweight and portable with a large top working area. It features a built-in chain vise, pipe bending slots, pipe rest, ceiling brace screw and hardened replaceable jaws. The lower tray folds for extra convenience.

Weight .......50 lbs. (22kg)

606738 Replacement Chain 606739 Replacement Jaws



## 4180 BENCH VISE

This new heavy duty bench vise is ideal for a wide range of pipe working from <sup>1</sup>/<sub>8</sub>" OD to 6" OD and features a reinforced steel chain and replaceable hardened jaws. Mounting bolts are included. It is ideal for a multitude of applications.

**600015** Replacement Chain **600016** Replacement Jaws



850 Shown Collapsed

## **FOLDING TRIPOD PIPE SUPPORTS**

Tripod Pipe Supports are designed to hold stock for threading machines, chop saws, and other equipment. Sturdy, all steel construction supports hold up to one ton (2000 lbs.) of materials: pipe, tubing, conduit, bar, rod, or structural steel. Quick-release locking ring allows for fast height adjustments, while  $1^{1}/_{2}$ " diameter Acme threads on the adjusting column provide fine height adjustments. Heavy duty lockscrew maintains height safely.

Height range is 27" - 50" (675-1250mm). Capacity: 1/2" - 16" (12-400mm) Diameter.

850	With standard V-head, Weight28 lbs	s. (13kg)
851	With heavy duty ball transfer head, Weight32 lbs	s. (14.5kg)
854	Ball Transfer Head only for use on standard V-head	







## **YOKE VISES**

These vises firmly hold pipe and round bar stock for cutting, drilling, and threading operations. Vises are reversible for left or right opening. All jaws are made of hardened steel and can easily be replaced in the field. The yoke and base are constructed of high-grade malleable iron. Meets all Federal Specifications: GGG-V-415a Type 1, Class II.

Product	O.D. Capacity	Weight
13020	<sup>3</sup> / <sub>8</sub> " - 2 <sup>3</sup> / <sub>8</sub> " (60mm)	10 lbs. (4.5kg)
13040	<sup>3</sup> / <sub>8</sub> " - 3 <sup>1</sup> / <sub>2</sub> " (89mm)	18 lbs. (8kg)
13060	<sup>3</sup> / <sub>8</sub> " - 4 <sup>1</sup> / <sub>2</sub> " (114mm)	28 lbs. (12.7kg)
13080	³/ <sub>8</sub> " – 5" (127mm)	27 lbs. (12kg)



## **FLOOR MODEL PIPE VISES**

WHEELER-REX Pipe Vises are designed to be portable and quickly assembled for field use, yet strong and tough enough for the shop. All models have a 2000 lb. (900kg) capacity. The quick releasing chain provides positive gripping power evenly around the pipe and prevents damage to pipe surfaces. Adjustments are fast to accommodate different pipe sizes.

401500	Capacity: 3/4" to 15" (18–375mm) Weight	54 lbs.	(24.6kg)
402000	Capacity: 3/4" to 20" (18–500mm)		(=3)
	Weight	55 lbs.	(25kg)
402800	Capacity: 3/4" to 28" (18-700mm)		
	Weight	56 lbs.	(25.5kg)



## PIPE PULLER

For joining all types of gasketed pipe: plastic, cast iron, clay, and concrete. Comes with two 12 ft. long anchor chains. Also pulls fittings, valves, and couplings into place. Lightweight yet rugged, this tool operates on a basic lever action and is used easily by one person.

4012	Pipe Capacity: 4" - 14" (100–350mm) Diameter		
	Wainht	33 lhe	(15ka)





## **PIPE DOLLY**

These dollies are used to support, rotate and align pipes. They are extremely heavy duty with 1" (25mm) diameter axle shafts. All steel construction. Normally used in pairs.

880	Capacity: 3" - 30" (75–750mm) pipe, 2500 lb. load rating each	
	Weight23 lbs.	(10.5kg)

Heavy Duty Iron Pipe Wrenches have I-Beam handles for proven strength and durability without excess weight. Full floating jaws have spring suspension for fast grip and release. Replaceable jaws are made of tough heat-treated alloy steel. Aluminum Wrenches are nearly 50% less weight compared to Iron Wrenches. The End Wrenches and the Off-Set Wrenches allow for usage in areas with space restrictions. All Pipe Wrenches are made to U.S. Federal Specifications. Parts are interchangeable with most major brands and carry a limited lifetime warranty.

## **HEAVY DUTY STRAIGHT IRON PIPE WRENCHES**

Manufactured to U.S. Specifications GGG-W-651e Type II Class A

Model		Pipe (	Capacity	Weig	jht	Std
Number	Description	Inches	mm	lbs	Kg	Pack
4508	8" (200mm) Straight Pipe Wrench	1	25	3/4	0.3	6
4510	10" (250mm) Straight Pipe Wrench	1 1/2	40	1 3/4	0.8	6
4512	12" (300mm) Straight Pipe Wrench	2	50	23/4	1.2	6
4514	14" (350mm) Straight Pipe Wrench	2	50	31/2	1.6	6
4518	18" (450mm) Straight Pipe Wrench	21/2	65	5 <sup>3</sup> / <sub>4</sub>	2.6	6
4524	24" (600mm) Straight Pipe Wrench	3	80	93/4	4.4	4
4536	36" (900mm) Straight Pipe Wrench	5	125	19	8.7	1
4548	48" (1200mm) Straight Pipe Wrench	6	150	34	15.5	1
4560	60" (1524mm) Straight Pipe Wrench	8	200	51 <sup>1</sup> / <sub>4</sub>	23.3	1

## **HEAVY DUTY END IRON PIPE WRENCHES**


Manufactured to U.S. Specifications GGG-W-651e Type VI



Model		Pipe (	Capacity	Weig	jht	Std
Number	Description	Inches	mm	lbs	Kg	Pack
4710	10" (250mm) End Pipe Wrench	1 1/2	40	1 <sup>3</sup> / <sub>4</sub>	0.8	6
4714	14" (350mm) End Pipe Wrench	2	50	31/2	1.6	6
4718	18" (450mm) End Pipe Wrench	21/2	65	53/4	2.6	3

## **ALUMINUM STRAIGHT PIPE WRENCHES**

Manufactured to U.S. Specifications GGG-W-651e Type II Class C



## **ALUMINUM OFF-SET PIPE WRENCHES**

Manufactured to U.S. Specifications GGG-W-651 Type II Class C

Model		Pipe C	Capacity	Weig	jht	Std
Number	Description	Inches	mm	lbs	Kg	Pack
4814	14" (350mm) Aluminum Off-Set	2	50	2	0.9	6
4818	18" (450mm) Aluminum Off-Set	21/2	65	31/2	1.6	6
4824	24" (600mm) Aluminum Off-Set	3	80	5	2.3	6





## **GRIPMASTER**

The GripMaster is a one-handed operation wrench which provides a fast, secure grip. Spring-loaded jaws for fast placement on pipe and secure ratchet action.

Model		Pipe C	apacity	Weig	jht	Std
Number	Description	inches	mm	lbs	kg	Pack
4310	10" GripMaster	1 1/2	37.5	2	0.9	6
4314	14" GripMaster	2	50	4	1.8	6

## SPUD WRENCH

The 4612 Spud Wrench is for  $^3/_8$ " –  $2^5/_8$ " pipes and is designed with narrow jaws to fit into small spaces. The smooth jaws are the perfect tool when toothed jaws may not be the right choice for the job.

	Model		Pipe C	Capacity	Weig	ht	Std
ı	Number	Description	inches	mm	lbs	kg	Pack
ſ	4612	12" Spud Wrench	2 <sup>5</sup> / <sub>8</sub>	67	2.7	1.2	6

## **5400 LIGHT DUTY CHAIN WRENCH**

With forged alloy steel handles, the 5400 is ideal for use in small locations. The 5400 is designed for pipes up to 4" O.D. Chain length is  $15^{3}/_{4}$ "; handle length is 12".

Weight	2.5 lbs.	(1.2ka)

## **STRAP WRENCHES**

Provides quick gripping to plastic or chrome plated objects without scratching or damaging the surface. Neoprene Coated Strap. Ductile iron handles for high strength.

Model No.	Pipe capacity	O.D. Capacity	Handle Length
8312	1/8"-2" (10-63mm)	1/8"-31/2" (10-90	mm) 12" (305mm) weight 2.0 lbs.
8318	1"-5" (33-127mm)	1"-6" (33-150n	nm) 18" (458mm) weight 3.3 lbs.
8324	2"-12" (60-324mm)	2"-14" (60-350)	mm) 24" (610mm) weight 5.7 lbs.
83120	Replacement Strap for	8312 <b>83121</b>	Replacement Wedge for 8312
83180	Replacement Strap for	8318 <b>83181</b>	Replacement Wedge for 8318
83240	Replacement Strap for	8324 <b>83241</b>	Replacement Wedge for 8324



## **BASIN WRENCH**

Quickly & easily tightens or loosens faucet shank nuts in close quarters. Complete with spring loaded jaws and a friction plug that helps hold the head in position.  $^3/_8$ " to  $1^1/_4$ " capacity.

9401	Basin Wrench	2 lbs (0.9kg)
340 I	Dasiii wiciicii	. Z 105. (U.3KU)



## SOIL PIPE COUPLING TORQUE WRENCH

This durable "T-Handle" type torque tool with a contoured comfort-fit handle features a removable socket and a unique locking collar, which allows the tool to be used as an untorqued snug-up or back-off, as well as a conventional torque tool. With the locking collar retracted, the tool torques to the right (tightening), while ratcheting to the left. When proper torque value has been achieved, the mechanism slips internally and over-tightening is impossible.

1977 T-Torque for tightening 5/16" coupling nuts to 60 in. lbs	Weight 1 lb.	(0.5kg)
1980 T-Torque for tightening 5/16" coupling nuts to 80 in. lbs	Weight 1 lb.	(0.5kg)
1981 T-Torque for tightening 3/8" coupling nuts to 80 in. lbs	Weight 1 lb.	(0.5kg)
<b>1982 T-Torque</b> for tightening ${}^{5}/_{16}$ " & ${}^{3}/_{8}$ " coupling nuts to 80 in. lbs	Weight 1 lb.	(0.5kg)

275410 5/<sub>16</sub>" Replacement Socket 275818 3/<sub>8</sub>" Replacement Socket



## **NO-HUB® COUPLING WRENCHES**

WHEELER-REX powered No-Hub® Coupling Wrenches tighten or loosen couplings in just a few seconds. The tools can be used with most  $^3/_8$ " reversible electric drills. They can be installed and removed as quickly as a drill bit. Automatic clutch in torque heads prevent over and under tightening. Recalibration is easy with a torque wrench.

1964 "Fastite" for tightening 5/16" coupling nuts to 60 in. lbs	. Weight 0.8 lb.	(0.36kg)
1965 "Fastite Plus" for tightening 3/8" coupling nuts to 80 in. lbs	. Weight 0.8 lb.	(0.36kg)
1966 "Fastite Plus 2" for tightening 5/16" coupling nuts to 80 in. lbs	. Weight 0.8 lb.	(0.36kg)





## **HYDRANT WRENCH**

For removing hydrant caps and operating hydrants. Made of sturdy forged construction; will fit pentagon nuts up to  $1^{3}/_{4}$ " or square nuts up to  $1^{1}/_{4}$ " with spanners for either pin or lug style host couplings.

8700	Hydrant Wrench5 lbs.	(2.5kg)
------	----------------------	---------



## **DOUBLE-UP WRENCH**

One through-bolt wrench with two sockets makes for fast, easy tightening of your repair clamp and service saddle nuts. Easy reversing with a single lever. Strong, all steel construction with a vinyl grip.

9600	1 1/4" x 1 1/16" Double-Up Wrench	2.75 lbs.
9601	<sup>15</sup> / <sub>16</sub> " x 1 <sup>1</sup> / <sub>8</sub> " Double-Up Wrench	2.75 lbs.



## **HEAVY DUTY DEEP SOCKETS**

Designed for tightening hex nuts on repair clamps, mechanical joint fittings, and saddles. Large diameter barrels make fast hand tightening easy. Operates with any 1/2" drive manual or impact wrench. Twelve individual kits are available.

Indiv	<i>i</i> dual	<b>Six Point Deep Sockets</b>
978	3/4"	Deep Socket 6 pt

9/8	3/4"	Deep Socket 6 pt1 lbs.	(U.5Kg)
979	<sup>7</sup> / <sub>8</sub> "	Deep Socket 6 pt1 lbs.	(0.5kg)
980	<sup>15</sup> / <sub>16</sub> "	Deep Socket 6 pt1.2 lbs.	(0.5kg)
981	1 1/ <sub>16</sub> "	Deep Socket 6 pt1.4 lbs.	(0.6kg)
982	1 1/ <sub>4</sub> "	Deep Socket 6 pt1.5 lbs.	(0.7kg)
983	1 1/8"	Deep Socket 6 pt1.5 lbs.	(0.7kg)
984	1 <sup>5</sup> / <sub>16</sub> "	Deep Socket 6 pt1.85 lbs.	(0.8kg)
985	1 <sup>7</sup> / <sub>16</sub> "	Deep Socket 6 pt2.15 lbs.	(1kg)
986	1"	Deep Socket 6 pt1.2 lbs.	(0.5kg)
987	1 1/2"	Deep Socket 6 pt2.3 lbs.	(1kg)
947	17mm	Deep Socket 6 pt	(0.4kg)
943	19mm	Deep Socket 6 pt	(0.4kg)
944	22mm	Deep Socket 6 pt	(0.5kg)
945	24mm	Deep Socket 6 pt	(0.5kg)
948	27mm	Deep Socket 6 pt1.4 lbs.	(0.6kg)
946	30mm	Deep Socket 6 pt	(0.7kg)

## Kits Available with Deep Sockets in Tool Box with 6515 Ratchet as Follows:

960	Includes $980 - \frac{15}{16}$ , $981 - \frac{11}{16}$ , $982 - \frac{11}{4}$	7.75 lbs.	(3.5kg)
961	Includes $980 - \frac{15}{16}$ , $981 - \frac{11}{16}$ , $982 - \frac{11}{4}$ , $983 - \frac{11}{8}$	9 lbs.	(4kg)
962	Includes 980 – 15/16", 982 – 11/4", 983 – 11/8"	7.75 lbs.	(3.5kg)
963	Includes $981 - 1^{1}/_{16}^{"}$ , $982 - 1^{1}/_{4}^{"}$ , $984 - 1^{5}/_{16}^{"}$ , $985 - 1^{7}/_{16}^{"}$	13 lbs.	(5.9kg)
964	Includes 981 – 1 <sup>1</sup> / <sub>16</sub> ", 982 – 1 <sup>1</sup> / <sub>4</sub> ", 983 – 1 <sup>1</sup> / <sub>8</sub> "	8 lbs.	(3.6kg)
965	Includes 979 – 7/8", 981 – 11/16", 982 – 11/4"	7.6 lbs.	(3.45kg)
966	Includes $978 - \frac{3}{4}$ , $979 - \frac{7}{8}$ , $980 - \frac{15}{16}$ , $981 - \frac{11}{16}$	8 lbs.	(3.6kg)
967	Includes $978 - \frac{3}{4}$ , $979 - \frac{7}{8}$ , $980 - \frac{15}{16}$ , $981 - \frac{11}{16}$ , $982 - \frac{11}{4}$ , $982 - \frac{11}{4}$	83 – 1 ¹/ <sub>8</sub> ",	
	$984 - 1^{5}/_{16}$ ", $985 - 1^{7}/_{16}$ ", $986 - 1$ ", $987 - 1^{1}/_{2}$ "	20 lbs.	(9kg)
968	Includes $978 - \frac{3}{4}$ ", $979 - \frac{7}{8}$ ", $980 - \frac{15}{16}$ ", $981 - \frac{11}{16}$ ", $982 \frac{11}{4}$ ", $983$	1 <sup>1</sup> / <sub>8</sub> " 16 lbs.	(7.26 kg)

## Kits with Deep Sockets in Metric Sizes:

940	Includes 943– 19mm, 944– 22mm, 945– 24mm7 lbs.	(3kg)
941	Includes 943–19mm, 944–22mm, 945–24mm, 946–30mm8 lbs.	(3.6kg)
942	Includes 947– 17mm, 943– 19mm, 945– 24mm, 946– 30mm20 lbs.	(9kg)
950	Includes 947- 17mm, 943- 19mm, 944- 22mm, 945- 24mm,	
	948– 27mm, 946– 30mm13 lbs.	(5.9kg)



## **DIAMETER TAPE**

For measuring diameter or circumference of pipes and cylindrical objects.

Pocket size 6' (1.82m) linear / 22" (.56m) Diameter Tape. 71 English/Metric Scales. ..... Weight 0.35 lbs (0.16kg)



## **PIPE CLEANER (Descaler)**

A versatile scraper for removing mud and scale from pipe surfaces. Makes for faster cutting and better repairs and joints. Belt material is light, strong and non-corroding. Angled blades promote self-cleaning. Belt is replaceable, longer length reduces back strain.

1300	For 3-12" diameter, 45" OAL 4 I	bs.	(2kg)
1301	Replacement Belt, 45"3 I	bs.	(1.5kg)
1350	For 12-36" diameter, 72" OAL 5 I	bs.	(2.5kg)
1351	Replacement Belt, 72" 4 I	bs.	(2kg)



## ARCTIC POLAR SYSTEM® PIPE FREEZING KIT


Designed specifically for the professional, WHEELER-REX Pipe Freezing Kits will rapidly form an ice plug in static water lines eliminating the need to drain down a system to make a repair. Ice plugs will last 15 to 20 minutes and can be easily renewed.

Kit comes complete with jackets for double freezes. No tools are required to set up and complete a freeze. An easy-to-use scale is included to ensure economical operation. Packaged in a convenient carrying case.

Polar Spray is non-toxic, non-flammable and ozone friendly. (Tetrafloraethane)

## TWO CAN PIPE FREEZING KIT

1755	<sup>3</sup> / <sub>8</sub> "-2 <sup>3</sup> / <sub>8</sub> " O.D. Kit includes the following:	
	2 jackets each – 17550 for $\frac{3}{8}$ " – $\frac{1}{2}$ ", 17551 for $\frac{5}{8}$ " – $\frac{7}{8}$ ", 17552 for 1" – $\frac{1}{8}$ ",	
	17553 for 1 <sup>5</sup> / <sub>8</sub> ", 17554 for 2"–2 <sup>3</sup> / <sub>8</sub> ", valve, scale, t-fitting and 5' tubing.	
	Weight11.5 lbs.	(5.3kg)





REPLACEMENT CANISTERS



WHEELER-REX's Pipe Freeze Kits install in seconds on pipes up to  $2\sqrt[3]{8}$ " O.D. and require no special tools. Ice plugs last 15-20 minutes and can be easily renewed.

## SHUTOFF TOOLS

## SHUT OFF TOOLS FOR SOFT COPPER PIPE

Our shut off tools are invaluable for maintenance and installation of soft copper service lines where they can shut off, hold, and restore flow quickly and easily. They are handy for quick repairs with their swing-out design. Complete with socket, ratchet, holding clamp, and carrying case.

## New & Improved — with Grease Fitting

85	Capacity: 3/4" (20mm) through 1" (25mm) soft copper tubing	
	Includes: ratchet, carrying case and #62 clamp.	
	Weight12 lbs.	(5.5kg)





Capacity: 1/2" (12mm) through 1" (25mm) soft copper tubing 86 Includes: ratchet, carrying case and #62 clamp. (5.9kg)

70 Capacity: 11/4" (31mm) through 2" (50mm) soft copper tubing Includes: ratchet, carrying case and #72 clamp. (8.6kg) 





8570 Combination of Models 85 and 70 Includes: ratchet, carrying case and clamps. 8670 Combination of Models 86 and 70 Includes: ratchet, carrying case and clamps.



(5.4kg)

#### **Accessories:**


1/2" (12mm) through 1" (25mm) Clamp for soft copper pipe 62 72 11/4" (31mm) through 2" (50mm) Clamp for soft copper pipe 6515 1/2" Square Male Drive Ratchet 221220 Conversion Kit from 85 to 86

506032 1"x 1/2" Square Drive Socket



## SHUT OFF TOOLS FOR PLASTIC PIPE

These unique portable valves shut off the flow of either water or gas in Polyethylene or Polybutylene plastic pipe. They are especially handy for fast on-the-spot repairs. Complete with socket, ratchet, and carrying case.





77 With adjustable stops to prevent damage to pipe. Capacity: 3/8" to 2" (10-50mm) Plastic gas pipe. Includes: ratchet and carrying case. 

## **DRILLING AND TAPPING TOOLS**







**Cutaway View** 

## **HOT TAPPING SYSTEM**

Capacity: from  $^3/_4$ " to 2" (19–50mm) in Steel, Cast Iron, Ductile, and Plastic Pipe. The WHEELER-REX Hot Tapping System is hand operated and designed for drilling holes in active water lines up to 250 psi. It is lightweight and easy for one person to set up and use. Complete with 6515 ratchet, tool box, adapters and cutter shells for making  $^3/_4$ " (19mm) and 2" (50mm) holes.

Built-in bleed-off valve allows chips to be flushed away.

Model	Pipe Size	Description	Use
8100	³/ <sub>4</sub> " - 1"	Complete with 3/4" & 1" NPT Adapters and HSS Cutter Shells for Steel and Copper Pipe.	STEEL & COPPER
8102	³/ <sub>4</sub> " - 2"	Complete with $34$ ", $1$ ", $114$ ", $112$ ", & 2" NPT Adapters and HSS Cutter Shells for Steel and Copper Pipe, Includes Large Arbor Assembly.	STEEL & COPPER
8200	³/ <sub>4</sub> " - 1"	Complete with $34^{\circ}$ & 1" CTS Flare Adapters and HSS Cutter Shells for Steel and Copper Pipe.	STEEL & COPPER
8201	³/ <sub>4</sub> " - 1"	Complete with ¾" & 1" CTS Flare Adapters and Cutter Shells for Plastic Pipe.	PLASTIC
8202	³/ <sub>4</sub> " - 2"	Complete with ¾", 1", 1½", & 2" CTS Flare Adapters and Cutter Shells for Plastic Pipe, Includes Large Arbor Assembly.	PLASTIC
8203	³/ <sub>4</sub> " - 1"	Complete with ¾" & 1" CTS Flare Adapters and Cutter Shells for Ductile & Cast Iron Pipe.	DUCTILE/CAST IRON
8204	³/ <sub>4</sub> " - 2"	Complete with ¾", 1", 1½", & 2" CTS Flare Adapters and Cutter Shells for Ductile and Cast Iron Pipe, Includes Large Arbor Assembly.	DUCTILE/CAST IRON
8205	³/ <sub>4</sub> " - 1"	Complete with ¾" & 1" CTS Flare Adapters and Cutter Shells for Plastic, Ductile and Cast Iron Pipe.	PLASTIC, DUCTILE & CAST IRON
8206	³/ <sub>4</sub> " - 2"	Complete with ¾", 1", 1½", & 2" CTS Flare Adapters and Cutter Shells for Plastic, Ductile and Cast Iron Pipe, Includes Large Arbor Assembly.	PLASTIC, DUCTILE & CAST IRON
8209	³/ <sub>4</sub> " - 2"	Complete with ¾", 1", 1½", & 2" CTS Flare Adapters, 1½" & 2" Compression Style Adapters, and Cutter Shells for Plastic, Ductile and Cast Iron Pipe, Includes Large Arbor Assembly.	PLASTIC, DUCTILE & CAST IRON
8300	³/ <sub>4</sub> " - 1"	Complete with ¾" & 1" BSPT Adapters and HSS Cutter Shells for Steel and Copper Pipe.	STEEL & COPPER

ADAPTERS FOR NPT THREAD	ADAPTERS FOR CTS FLARE	ADAPTERS FOR BSPT THREAD	COMPRESSION STYLE CORP STOP MUELLER 110	CUTTER SHELLS FOR STEEL AND COPPER	CUTTER SHELLS FOR DUCTILE IRON & CAST IRON	CUTTER SHELLS FOR PLASTIC C-900	OTHER ACCESSORIES
802051 <sup>3</sup> / <sub>4</sub> "	802050 3/ <sub>4</sub> "	802071 <sup>3</sup> / <sub>4</sub> "	802060 1- <sup>1</sup> / <sub>2</sub> " ADAPTER	903071 <sup>3</sup> / <sub>4</sub> "	904065 ³/ <sub>4</sub> "	5800 ³/₄"	6515 RATCHET
802053 1"	802052 1"	802072 1"	802061 2" ADAPTER	903072 1"	904066 1"	5801 1"	908097 THREADED BUSHING
802055 1-¹/₄"	802054 1-¹/₄"	802073 1- <sup>1</sup> / <sub>4</sub> "		903073 1-¹/₄"	904067 1- <sup>1</sup> / <sub>4</sub> "	5803 1-¹/₄"	908094 CENTER DRILL
802057 1- <sup>1</sup> / <sub>2</sub> "	802056 1- <sup>1</sup> / <sub>2</sub> "	802074 1- <sup>1</sup> / <sub>2</sub> "		903074 1- <sup>1</sup> / <sub>2</sub> "	904068 1- <sup>1</sup> / <sub>2</sub> "	802084 1- <sup>1</sup> / <sub>2</sub> "	908098 Center Drill W/ Coupon Retainer
802059 2"	802058 2"	802075 2"		903075 2"	904069 2"	802085 2"	



## 701440 1-1/2" & 2" ARBOR ASSEMBLY -HOT TAP SYSTEM ADAPTER

Reinforced Arbor for cutting larger holes in difficult materials. To be used with  $1-\frac{1}{2}$ " and 2" cutter shells for all three WHEELER-REX hot tap systems. The new arbor design has drive pins that align with holes in the large cutter shells for a stronger assembly.

Weight......2 lbs. (0.9kg)



## **COMBINED DRILL TAPS**

WHEELER-REX's combined drill taps bring you premium performance at a reasonable price. Designed and manufactured to produce a quality thread and ensure a pressure tight fit. Made from high speed steel, they are tough and durable and fit all popular tapping machines.

WHEELER-REX Drill Taps will fit all popular tapping machines including:

Mueller B100 • Mueller B101 • Mueller A2 • Mueller A3 • Hays Transmate B1 • All Reed

89075	3/4" CC Thread Drill Tap1.1 lbs.	(0.49kg)
89150	1-1/2" CC Thread Drill Tap	(1.24kg)
89100	1" CC Thread Drill Tap	(0.6kg)
89200	2" CC Thread Drill Tap	(1.74kg)
86075	3/4" CC PVC Drill Tap	(0.45kg)
86100	1" CC PVC Drill Tap	

Resharpening service only available for WHEELER-REX CC Thread Drill Taps (not available for PVC Drill Taps).



## **TAPPING FLUID**

A completely new concept in a lubricant for drill taps and other related uses where a non-toxic food grade lubricant is required. Slik-tap is easy to apply, yet thick enough to hang onto the cutting tool, providing the lubrication to reduce tapping effort and produce clean threads.

·				•	•	
8900	1 pint of Tappi	ng Fluid Slik-Tap				1.5 lbs. (0.68kg)
8901	12 pack of 890	00 Tapping Fluid Slik	-Tap			14 lbs. (6.35kg)



A compact, light-weight hole cutter system that utilizes a drill to cut a hole in pipes. Designed to cut most materials, including steel.



### Without drill - provide your own:

3090	with adapter only for Milwaukee® Drill (less drill)46 ids.	(21Kg)
3091	With adapter only for DeWalt® DW130V Drill (less drill)46 lbs.	(21kg)
With drill	! <del>:</del>	
3092	Hole Cutter System with Milwaukee® Model 1660-6 Drill57 lbs.	(26kg)
3093	Hole Cutter System with DeWalt® DW130V Drill57 lbs.	(26kg)
701173	Drill Adapter Kit for DeWalt® 131 Drill for all models	(0.5kg)

#### Accessories:

908094 Center Drill

#### Features:

- Cuts holes up to 4<sup>3</sup>/<sub>4</sub>" (120mm)
- For use with standard off-the-shelf hole saw (not included)
- Comes standard with metal carrying case
- Comes standard with enough chain for 10" pipes, extra chain available
- Handle can be changed for right or left feed
- Rack & pinion feed gear
- Fast, easy, secure mounting to pipe
- Spring loaded pin holds drill in position
- Comes complete and ready to use with either: DeWalt® DW130V Drill or Milwaukee® 1660-6 Drill




## DRILLING AND TAPPING TOOLS

CONTINUED







1660	Complete with gasoline power pack and water valve assembly Shipping weight (less cutter shells)108 lbs. (49kg)
1661	Complete with air power pack and water valve assembly, $70-80$ psi (4.6–5.5 bar), $50-60$ cfm ( $1400-1700$ lpm) Shipping weight (less cutter shells)123 lbs. (55.9kg)
276582	Air Motor Repair Kit
1662	Complete with 115V electric motor and water valve assembly Shipping weight (less cutter shells)102 lbs. (46kg)
1663	Complete with hydraulic motor and water valve assembly, 8 gpm, 2000 psi (30 lpm @ 130 bar) Shipping weight (less cutter shells)
1664	Hole Cutter System less drive
tractor for your curre (8 gpm and hydraulic l	Bypass Valve for 1663 Hole Cutter System 8 gpm, 2000 psi

## **HOLE CUTTER SHELLS**

Coupon Retainer

Carbide-Tipped Center Drill for Clay and Concrete

Nominal Hole Size	Clay Concrete	Reinforced Concrete, Clay, Ductile & Cast Iron	Plastic
4" (100mm)	3395*	6395*	4395
4 <sup>1</sup> / <sub>2</sub> " (112mm)	3450*	6450*	4450
6" (150mm)	3595*	6595*	4595
6 <sup>1</sup> / <sub>2</sub> " (172mm)	3650*	6650*	4650
8" (200mm)		6800*	4800

<sup>\*</sup> Water coolant required

Larger sizes available upon request



Bores holes underground without trenching or disturbing surface materials. Ideal for installing water, gas, drain, and electrical lines. Comes standard with a combination drive/water valve assembly, and a 2" (50mm) diameter auger. User supplies 3/4" pipe for drill shaft.



## **Additional Augers**

211

220025

**7801** 1" (25mm) Auger **7802** 2" (50mm) Auger

**7810** 3" (75mm) Auger

**7808** 4" (100mm) Reversing Auger **7809** 6" (150mm) Reversing Auger



## PIPE SLICES 8600 PIPE SL

 Kits:

 8631
 Includes 8600 Pipe Slice, 8610 Cable Grip, 8625 & 8626 Poly/Copper Pipe Pulling Attachments
 18 lbs.
 (8kg)

 8632
 Includes 8600 Pipe Slice, 8611 Cable Grip, 8625 & 8626 Poly/Copper Pipe Pulling Attachments
 18 lbs.
 (8kg)

 Accessories:
 8605
 3/8" x 50' Cable with Ferrule
 16 lbs.
 (7.2kg)

(7.2kq)8606 (10kg) 8607 (12.7kg) 8608 (16.8kg) 8610 Cable Grip – Double V ......7 lbs. (3kg) 8611 Cable Grip – Flat .......7 lbs. (3kg) 8625 (.25kg) 8626 (.25kg)

**8601 PIPE SLICE** with 1-1/2" – 12 Straight Threads, Single Blade..................3 lbs. (1.4kg)

Recommended for replacing existing poly service lines.



Poly/Copper Pipe

Kits:		
8633	Includes 8601 Pipe Slice, 8610 Cable Grip, 8645 & 8646 Poly Pipe	
	Pulling Attachments18 lbs.	(8kg)
8634	Includes 8601 Pipe Slice, 8611 Cable Grip, 8645 & 8646 Poly Pipe	
	Pulling Attachments	(8kg)
8635	Includes 8601 Pipe Slice, 8610 Cable Grip, 8647 Flare Tool,	, 0,
	8648 & 8649 Copper Flare Locknuts	(8kg)
8636	Includes 8601 Pipe Slice, 8611 Cable Grip, 8647 Flare Tool,	, 0,
	8648 & 8649 Copper Flare Locknuts	(8kg)
8637	Includes 8601 Pipe Slice, 8610 Cable Grip, 8645 & 8646 Poly Pipe	, 0,
	Pulling Attachments, 8647 Flare Tool, 8648 & 8649 Copper Flare Locknuts20 lbs.	(9kg)
8638	Includes 8601 Pipe Slice, 8611 Cable Grip, 8645 & 8646 Poly Pipe	, ,,
	Pulling Attachments, 8647 Flare Tool, 8648 & 8649 Copper Flare Locknuts 20 lbs.	(9kg)
Acces	ssories:	
8605	<sup>3</sup> / <sub>8</sub> " x 50' Cable with Ferrule16 lbs.	(7.2kg)
8606	<sup>3</sup> / <sub>8</sub> " x 75' Cable with Ferrule22 lbs.	(10kg)



ACCESS	oures.		
8605	<sup>3</sup> / <sub>8</sub> " x 50' Cable with Ferrule	16 lbs.	(7.2kg)
8606	<sup>3</sup> / <sub>8</sub> " x 75' Cable with Ferrule	22 lbs.	(10kg)
8607	3/8" x 100' Cable with Ferrule	28 lbs.	(12.7kg)
8608	3/8" x 150' Cable with Ferrule	37 lbs.	(16.8kg)
8610	Cable Grip - Double V	7 lbs.	(3kg)
8611	Cable Grip – Flat	7 lbs.	(3kg)
8645	3/4" Poly Pipe Pulling Attachment	1 lb.	(.25kg)
8646	1" Poly Pipe Pulling Attachment	1 lb.	(.25kg)
8647	34" & 1" Double Flare Tool	1 lb.	(.5kg)
8648	34" Copper Flare Locknut	1 lb.	(.25kg)
8649	1" Copper Flare Locknut	1 lb.	(.25kg)
	••		` 0,



<b>850</b> ( Kits:	O MINI PIPE SLICE with ½" NPT Male Threads1 lb.	(0.5kg)
8520	Includes 8500 Mini Pipe Slice, 8506 50' Cable, 8525 Pulling Attachment, 8611 Cable Grip18 lbs.	(8kg)
8521	Includes 8500 Mini Pipe Slice, 8507 75' Cable, 8525 Pulling Attachment,	(- 3)
	8611 Cable Grip21 lbs.	(9.5kg)
8522	Includes 8500 Mini Pipe Slice, 8508 100' Cable, 8525 Pulling Attachment,	
	8611 Cable Grip23 lbs.	(10.5kg)
Acces	sories:	
8506	1/4" x 50' Cable with Ferrule	(3.6kg)
8507	14" x 75' Cable with Ferrule11 lbs.	(5kg)
8508	13 lbs. 1/4" x 100' Cable with Ferrule	(6 kg)
8525	1 lb. ½" – ¾" Pipe Pulling Attachment	(.25kg)



## **VALVEMASTER PORTABLE VALVE EXERCISER**

ValveMaster portable valve exerciser delivers 0–600 ft. lbs. of torque with finger tip control. All torque absorbed by frame to protect the operator. Standard features include digital counter, 2" ball hitch coupling, 4.80 x 12" wheels and auxiliary connections for use as hydraulic power source for other tools.

(Type II 8 gpm, 2000 psi) 8 ft telescoping key included

<b>98001</b> With Honda engine	2 lbs. (233kg)
98003 With Honda engine and reversible counter	0 lbs. (232kg)

Note: 8 foot is the maximum key length recommended for optimal performance.



681155

## **VALVE EXERCISER / POWER DRIVE**

The 68 series valve exerciser offers high performance in a compact, lightweight package. A wide variety of adapters are available for multiple uses. 115V,  $^{1}/_{2}$  hp., 6 amps, 250 ft. lbs., 22 RPM.

68115	Power Drive only – For use with adapters below 22 rpm35 lbs. (**Other voltages may be available upon request.	15.90kg)
681150	Power Drive with 13964, 22 rpm45 lbs. (2	20.45kg)
681155	Rising Stem Valve Operator with counter, clutch and hand wheel adapter Weight	(28.1kg)
68315	Power Drive Only, 66 rpm	
683155	Power Drive with 13968 and 13970, 66 rpm	
13964	Torque Limiting Adapter with counter and 1" square drive. 0-250 ft. lbs.  Weight8 lbs.	(3.6kg)
10709	1" Square Female Adapter Weight	(1.4kg)
10696	Adapter for 12R drop head dies Weight	(0.9kg)
701061	Electric Counter Assembly Weight	(.65kg)
21389	Torque Limiting Adapter with 1" Square Drive, 2-250 ft. lbs.	



681150 in use



## **ALUMINUM VALVE WHEEL WRENCHES**

Designed to provide leverage to turn a valve wheel without slipping. Made from aluminum to be light weight and non-sparking. Three convenient sizes for added leverage.

8708	8" Length (3/4" Mouth Opening) Weight	(0.13kg)
8714	14" Length (1" Mouth Opening) Weight	
8718	18" Length (13/8" Mouth Opening) Weight	(1.1kg)


10696



## 13968 RISING STEM TORQUE ADAPTER

#### Features:

- · Clutch "slips" to keep operator and valve safe while exercising.
- Torque Specs: adjustable 0 200 ft.lbs.
- Unique clutch system allows you to set the torque accordingly, to exercise valves without exceeding their limit.
- Clutch can be easily adjusted with any 3/4" wrench. (Not included)
- Control Rods have graduations for approximate ft.lbs. of torque.
- To be used with the 13970 on rising stem valves.
- The 701061 counter assembly can be added to the 68115 and the 13970 for ease
  of valve revolution counting.
- Clutch is allowed to "slip" and keep correct count when using the 701061 counter assembly.



## 13970 HAND WHEEL ADAPTER

#### Features:

- Adapts to valves with hand wheels with or without rising stems up to 3" in diameter.
- Series of bolt holes to adapt to many different spoke patterns and styles available.
- Allows you to exercise the valve with ease by using the 68115 with the addition of a 13968 Rising Stem Torque Adapter.
- The 701061 counter assembly can be added to the 68115 and the 13968 for ease of valve revolution counting.



## **10700 HYDRANT NUT**

A convenient 1" square drive adapter designed for most hydrants. Use it with a portable power drive or with a T-Handle Key. It reduces worker fatigue when used with the WHEELER-REX 68115 Power Drive. Can also use the WHEELER-REX 8806 or 8808 Telescoping Valve Keys.

Machined and fabricated steel construction, adjustable to a variety of pentagon nut up to a  $1^{-3}/_4$ ". A  $^3/_4$ " jam bolt is included.

Weight .......6 lbs. (2.7kg)



### **VALVE KEYS**

### 8806 6 FT. TELESCOPING VALVE KEY

#### 8808 8 FT. TELESCOPING VALVE KEY

#### 88024 2 FT. EXTENSION

## **MARKETING TOOLS**

## WHEELER-REX 2'X2' GRID WALL DISPLAY



998042, 998043

998042 Wall Display Kit 2'x2' 1 Black and 1 Red Panel, 18 hooks per kit

998043 Wall Display Literature Holder Accessory

998037 Counter Mat998022 Product Catalog

998027 Price List

998039 Threading Machine Mini Catalog

998040 Test Pump Mini Catalog998041 Tubing Cutter Mini Catalog



998037





998027 998041

## **WHEELER-REX HISTORY**





Wheeler Manufacturing was established in 1957 on the shores of Lake Erie, with the invention of the chain-type snap cutter for cast iron and clay tile pipes. A product that would become the first of many industry changing inventions.

In 1988, Wheeler became part of the Rex Industries family. Rex Industries is known for the highest quality and most innovative pipe threading machines in the world. Rex set the bar for threading machine standards on a global scale with features such as through the die head oiling, auto open die heads, notch-style adjustment, and ball detent die location.

Thus, WHEELER-REX was born. Blending the best of American and Japanese culture to create a company focused on product perfection, work ethic, employee pride, and customer success. Today, WHEELER-REX maintains its presence as one of the industry leaders in the Hydrostatic Test Pump and Threading Machine markets. As well as continuting to focus on expanding our line of pipe tools, accessories, and exemplary customer service staff.



## **VISIT THE WHEELER-REX WEBSITE**

WHEELER-REX products are sold exclusively through an extensive network of distributors. To find your nearest location, use the "Where to Buy" feature located on our website, or give us a call! Also available are online catalogs, product information, parts diagrams, operation manuals, and other useful information.



# PRODUCT LISTING

Part No	Description	Page	Part No	Description	Page
70	SHUT OFF TOOL 1-1/4"-2" SOFT COPPER	49	982	1-1/4 HD DEEP SOCKET	47
71	ENGLISH/METRIC 6 FOOT DIAMETER TAPE	47	983	1-1/8 HD DEEP SOCKET	47
75	SHUT OFF TOOL 3/8"-2" PLASTIC WATER LINES	49	984	1-5/16 HD DEEP SOCKET	47
77	SHUT OFF TOOL 3/8"-2" PLASTIC GAS LINES	49	985	1-7/16 HD DEEP SOCKET	47
85	SHUT OFF TOOL 3/4"- 1" COPPER LINES	49	986	1 HD DEEP SOCKET	47
86	SHUT OFF TOOL 1/2"- 1" COPPER LINES	49	987	1-1/2 HD DEEP SOCKET	47
450	TUBE CLEANING BRUSH 1/2" & 3/4" COPPER	20	1293	REPLACEMENT BLADAE FOR MODELS 1590, 2290, 2492	15
452	REPLACEMENT BRUSH SET (453 AND 454)	20	1300	PIPE SCRAPER, 3"-12"	47
522	COMPLETE CHAIN FOR 6" 490/590	6	1350	PIPE SCRAPER, 12"-36"	47
528	COMPLETE CHAIN FOR 8" 590/490	6	1590	INTERNAL PIPE CUTTER 1-1/2"	15
532	COMPLETE CHAIN FOR 6" 590/490 W/ROLLERS	6	1660	HOLE CUTTER, GAS	52
533	COMPLETE CHAIN FOR 8" 590/490 W/ROLLERS	6	1661	HOLE CUTTER, PNEUMATIC	52
600	PLASTIC PIPE HAND SAW 18"	13	1662	HOLE CUTTER, ELECTRIC	52
601	PLASTIC PIPE HAND SAW 18", PTFE BLADE	13	1663	HOLE CUTTER, HYDRAULIC	52
602	PLASTIC PIPE HAND SAW 13"	13	1664	HOLE CUTTER, LESS DRIVE	52
603	PLASTIC PIPE HAND SAW 13", PTFE BLADE	13	1697	T-HANDLE GUILLOTINE CUTTER 8", SS BLADE	16
610	REPLACEMENT 18" BLADE FOR 600 SAW	13	1755	3/8"- 2-3/8" FREEZE KIT W/ 2CANS SPRAY	48
611	REPLACEMENT 18" BLADE FOR 601 SAW	13	1894	GUILLOTINE CUTTER/POWER DRIVEN	16
612	REPLACEMENT 13" BLADE FOR 602 SAW	13	1897	GUILLOTINE CUTTER, 14.2", V BLADE, T-HANDLE	16
613	REPLACEMENT 13" BLADE FOR 603 SAW	13	1924	COMPLETE CHAIN FOR 8" 2990	6
626	26" CABLE SAW	13	1924	COMPLETE CHAIN FOR 6" 2990	6
636	36" CABLE SAW	13	1964	FASTITE 5/16" SOCKET 60IN LB	46
	POWER DRIVE W/CASE, ADAPTER&TORQUE VISE	26	1965	FASTITE 3/10 SOCKET BOIN LB	46
640 841	STAND FOR 7991				
		30	1966	FASTITE 5/16" SOCKET 80IN LB	46
850	FOLDING PIPE STAND W/PT USAD	42	1977	SOIL PIPE TORQUE WRENCH,60in/lb 5/16"	46
851	FOLDING PIPE STAND W/BT HEAD	42	1980	SOIL PIPE TORQUE WRENCH,80IN/LB 5/16"	46
854	BALL TRANSFER SET PAIR	42	1981	SOIL PIPE TORQUE WRENCH,80IN/LB 3/8"	46
880	PIPE DOLLIE 3"-30"	43	1982	SOIL PIPE TORQUE WRENCH,80IN/LB 5/16"& 3/8"	46
892	T-HANDLE GUILLOTINE CUTTER, POINTED	16	2290	INTERNAL PIPE CUTTER 2"	15
919	5 PACK OF DEBURRING TOOLS	22	2492	INTERNAL PIPE CUTTER 2" SCH 80	15
921	10 PACK OF DEBURRING TOOLS	22	2690	1/8"-2" STEEL PIPE CUTTER	7
925	50 PACK OF DEBURRING TOOLS	25	3090	HOLE CUTTER W/MILW ADAPTER/NO DRILL	51
940	HD METRIC DS KIT-19,22,24MM	47	3091	HOLE CUTTER W/DEWALT ADAPTER/NO DRILL	51
941	HD METRIC DS KIT-19,22,24,30MM	47	3092	3090 HOLE CUTTER W/MILW DRILL	51
942	HD METRIC DS KIT-17,19,24,30MM	47	3093	3091 HOLE CUTTER W/DWLT DRILL	51
943	HD 19MM DEEP SOCKET	47	3290	INTERNAL PIPE CUTTER 3"	15
944	HD 22MM DEEP SOCKET	47	3293	REPLACEMENT BLADE FOR MODELS 3290 AND 3490	15
945	HD 24MM DEEP SOCKET	47	3490	INTERNAL PIPE CUTTER 3" SCH 80	15
946	HD 30MM DEEP SOCKET	47	3590	1/8"-3/8" RATCH-CUT	21
947	HD 17MM DEEP SOCKET	47	3790	5/16"-1-1/8" RATCH CUT	21
948	HD 27MM DEEP SOCKET	47	3801	WHEELER HYDROYL ONE QUART	5
950	HD METRIC DS KIT-17,19,22,24,27,30	47	3804	WHEELER HYDROYL ONE GALLON	5
960	HD DEEP SOCKET KIT-980,981,982	47	3824	COMPLETE CHAIN 12" FOR 389012	6
961	HD DEEP SOCKET KIT-980,981,982,983	47	4012	PIPE PULLER 4" - 14"	43
962	HD DEEP SOCKET KIT-980,982,983	47	4160	TRIPOD CHAIN VISE 1/8"-6"	42
963	HD DEEP SOCKET KIT-981,982,984,985	47	4180	BENCH CHAIN VISE	42
964	HD DEEP SOCKET KIT-981,982,983	47	4190	MICRO SNIPPER 1/4" TO 3/8"	12
965	HD DEEP SOCKET KIT-979,981,982	47	4200	1/2"-2" MANUAL THREADER SET, NPT	26
966	HD DEEP SOCKET KIT-978,979,980,981	47	4202	1/2"- 1" RATCHET THREADER SET, NPT	26
967	HD DEEP SOCKET KIT (10 SOCKETS)978 THRU 987	47	4207	1/2-1-1/4" MANUAL THREADER SET, NPT	26
968	HD DEEP SOCKET KIT-978, 979,980,981,982,983	47	4211	1"-2" MANUAL THREADER SET, NPT	26
978	3/4 HD DEEP SOCKET	47	4213	1/2"-2" MANUAL THREADER SET, NPT, NO CASE	26
979	7/8 HD DEEP SOCKET	47	4215	1/2-2"BSPT MANUAL THREADER SET, BSPT	26
980	15/16 HD DEEP SOCKET	47	4290	INTERNAL PIPE CUTTER 4"	15

Part No	Description	Page	Part No	Description	Page
4310	10" GRIPMASTER PIPE WRENCH	45	5300	REPLACEMENT BLADE FOR 5291	11
4314	14" GRIPMASTER PIPE WRENCH	45	5400	CHAIN WRENCH	45
4410	10" ALUMINUM STRAIGHT PIPE WRENCH	44	5412	OPC,4-12" CUT & GRV STL & ALU	25
4414	14" ALUMINUM STRAIGHT PIPE WRENCH	44	5524	COMPLETE CHAIN 18" FOR 559018	6
4418	18" ALUMINUM STRAIGHT PIPE WRENCH	44	5350	REPLACEMENT BLADE 5280	11
4424	24" ALUMINUM STRAIGHT PIPE WRENCH	44	5624	PIPEMASTER II, 6" - 24"	8
4436	36" ALUMINUM STRAIGHT PIPE WRENCH	44	5690	AUTO C CUTTER 1/2" (15.9MM)	21
4448	48" ALUMINUM STRAIGHT PIPE WRENCH	44	5691	AUTO C CUTTER 1/2 (13.58MM)  AUTO C CUTTER 3/4" (22.2MM)	21
4490	INTERNAL PIPE CUTTER 4" SCH 80	15	5692	AUTO C CUTTER 3/4 (22.2MM)	21
4506	COPPER TUBE CLEANER (6-IN-1) 1/2"&3/4"	20	5741	RETRACTABLE UTILITY KNIFE	18
4508	8"HD STRAIGHT IRON PIPE WRENCH	44	5751	SELF-RETRACTING SAFETY KNIFE	18
4510	10" HD STRAIGHT IRON PIPE WRENCH	44	5761	5 PACK OF REPLACEMENT KNIFE BLADES	18
4512	12" HD STRAIGHT IRON PIPE WRENCH	44	5800	3/4" CUTTER SHELL PLASTIC C-900	50
4514	14" HD STRAIGHT IRON PIPE WRENCH	44	5801	1" CUTTER SHELL PLASTIC C-900	50
4518	18" HD STRAIGHT IRON PIPE WRENCH	44	5803	1 1/4" CUTTER SHELL PLASTIC C-900	50
4524	24" HD STRAIGHT IRON PIPE WRENCH	44	5900	OIL BUCKET W/PUMP	26
4536	36" HD STRAIGHT IRON PIPE WRENCH	44	5906	MANUAL PIPE CTR 1-1/2" to 6"	4
4548	48" HD STRAIGHT IRON PIPE WRENCH	44	5908	MANUAL PIPE CTR 1-1/2 to 8	4
4560	60" HD STRAIGHT IRON PIPE WRENCH	44	5916	MANUAL CUTTER 1-1/2"-6", W/519	4
4606	6" DIAMOND BLADE FOR DI & CI	9	5918	MANUAL PIPE CUTTER 1-1/2"-8", W/519	4
4612	12" SPUD WRENCH	45	6000	INTERNAL PIPE CUTTER 6"	15
4616	6" DIAMOND ECONOMY BLADE	9	6154	IPC KIT FOR 1 1/2", 2", 3", 4"	15
4685	SET OF 6 STEEL WEDGES	8	6156	IPC KIT FOR 1 1/2", 2", 3", 4", 6"	15
4686	ROLLER CHAIN, ONE LINK SECTION	8	6412	OPMT CUT & BEVEL DIP 4"-12"	25
4690	2"-4" STEEL PIPE CUTTER	o 7	6500	HYDRAULIC POWER PACK	9
4700	HAMMERHEAD FLARING KIT, 3/4"-2" COPPER	22	6515	RATCHET	16,49
4706	6.5" TCT BLADE FOR STEEL	9	6590	THREADING MACHINE 2-1/2"-6"	29
4700	10" HD END IRON PIPE WRENCH	44	6598	THREADING MACHINE 2-1/2 -0 THREADING MACHINE 2-1/2-6"220V	29
4710	14" HD END IRON PIPE WRENCH	44	6790	THREADING MACHINE 1/2"-4"	29
4714	18" END IRON PIPE WRENCH	44	6793	6790 THREADING MACHINE 1/2"-4"(NOTCH DH)	29
4814	14" ALUMINUM OFF-SET PIPE WRENCH	44	6794	6790 THREADING MACHINE 1/2"-4"(NOTOTI DIT)	29
4818	18" ALUMINUM OFF-SET PIPE WRENCH	44	6798	THREADING MACHINE 1/2"-4" (BLADE CTR)	29
4824	24" ALUMINUM OFF-SET PIPE WRENCH	44	7280	V-BLADE RATCHET SNIPPER 1/8"-2 7/16"	11
4900	REROUNDING TOOL KIT 3/4"-2" COPPER	22	7200	PROFESSIONAL SNIPPER 7291 1/8"- 2-7/16"	11
4906	RATCHET PIPE CTR 1-1/2 to 6	4	7324	REPLACEMENT BLADE FOR 7291	11
4908	RATCHET PIPE CTR 1-1/2 to 8	4	7350	REPLACEMENT BLADE FOR 7280	11
4906	RATCHET PIPE CUTTER 1-1/2"-6" W/519	4	7702	ROLL GROOVING MACHINE W/MANUAL PUMP	25
4918	RATCHET PIPE CUTTER 1-1/2"-8" W/519	4	7702	ROLL GROOVING MACHINE W/POWER PUMP	25
4992	CLOSE QUARTER CUTTER, COPPER&PLASTIC	21	7800	EARTHWORM HYDRO DRILL	52
5090	PIPE CUTTER 1/2"- 2"	7	7801	1 INCH AUGER	52
5190	MINI SNIPPER 1/8" TO 1-1/4"	11	7802	2 INCH AUGER	52
5190	MINI SNIPPER 1/8" TO 1-1/4", PTFE BLADE	11	7808	4 INCH REVERSE AUGER	52
5195	ECONOMY SNIPPER 1/8" - 1-1/4"	12	7809	6 INCH REVERSE AUGER	52
5196	REPLACEMENT BLADE FOR 5195	12	7810	3 INCH AUGER	52
5200	REPLACEMENT BLADE 5190	11	7914	3/8 PITCH CUTTER CHAIN	10
5210	COMPLETE CHAIN, 10" 490/590	6	7914	1-1/2" GLASS CUTTER CHAIN, 3/8 PITCH	10
5210	COMPLETE CHAIN, 10 490/390	6	8001	CUTTER WHEEL	7
5215	COMPLETE CHAIN, 12 490/390	6	8003	CUTTER WHEEL	23
5256	CHAIN EXTENSION 490/590 8 PINS	6	8004	CUTTER WHEEL - 4690 (8016)	7
5258	CHAIN EXTENSION 490/590 14PINS	6	8006	CUTTER WHEEL	23
5280	V-BLADE RATCHET SNIPPER 1/8"-1 5/8"	11	8012	CUTTER WHEEL	23
5291	PROFESSIONAL SNIPPER 5291, 1/8"- 1-5/8"	11	8015	CUTTER WHEEL	23
5295	ECONOMY SNIPPER 1/8" - 1-5/8"	12	8021	CUTTER WHEEL	23
5296	REPLACEMENT BLADE FOR 5296	12	8025	CUTTER WHEEL	23
5299	REPLACEMENT BLADE FOR 5290	11	8033	CUTTER WHEEL FOR PLASTIC 4992	21
0200	THE ENGLINEET BEABLY ON OTO	• •	0000	OUT EN WILLE FORT ENOUGH TOUR	

# PRODUCT LISTING

Part No	Description	Page	Part No	Description	Page
8034	CUTTER WHEEL	23	8522	MINISLICE 100'-8508,8500,8611	53
8037	CUTTER WHEEL	23	8525	1/2-3/4 POLY PULLER	53
8038	CUTTER WHEEL, 4990/ 4991/4992	21	8570	SHUT OFF TOOL COMBO 85 & 70, 3/4"-2"	49
8039	CUTTER WHEEL, 5090	7	8600	PIPE SLICE	53
8040	CUTTER WHEEL FOR 2590/3590, RC375	21	8601	PIPESLICE II-PIPELINE REPLACEMENT TOOL	53
8041	CUTTER WHEEL FOR 2790/3790, RC1125	23	8605	3/8 x 50' CABLE WITH FERRULE	53
8042	CUTTER WHEEL FOR 4590	23	8606	3/8 x 75' CABLE WITH FERRULE	53
8043	CUTTER WHEEL FOR 4790	23	8607	3/8 x 100' CABLE WITH FERRULE	53
8044	CUTTER WHEEL FOR 2790 & 3790 HSS/SS	21	8608	3/8 x 150' CABLE WITH FERRULE	53
8045	CUTTER WHEEL	23	8610	CABLE GRIP - DOUBLE V	53
8046	CUTTER WHEEL FOR 5690/1/2,COPPER/CTS/CPVC	21	8611	CABLE GRIP - FLAT	53
8050	CUTTER WHEEL FOR 95041 STEEL, STYLE HS4	7	8625	3/4 POLY/COPPER PIPE PULLING FOR 8600	53
8051	CUTTER WHEEL FOR 95041 CI/DI, STYLE H14	7	8626	1" POLY/COPPER PIPE PULLING FOR 8600	53
8052	CUTTER WHEEL FOR 95061 STEEL, STYLE HS6	7	0020	PIPE SLICE KIT 8600 SLICE, 8610 GRIP, 8625 & 8626	
8053	·	7	8631	POLY/COPPER PULLING	53
8054	CUTTER WHEEL FOR 95061/81/121, CI/DI CUTTER WHEEL FOR 95081/121 STL	7		PIPE SLICE KIT 8600 SLICE, 86110 GRIP, 8625 & 8626	
			8632	POLY/COPPER PULLING	53
8066	CUTTER WHEEL FOR 90748,90749, PLASTIC	20		PIPE SLICE KIT 8601 SLICE, 8610 GRIP, 8645 & 8646	
8067	CUTTER WHEEL FOR 90748,90749, COPPER,AL	20	8633	POLY PULLING ATTACHMENT	53
8068	CUTTER WHEEL FOR 90747, PLASTIC	19		PIPE SLICE KIT 8601 SLICE, 8611 GRIP, 8645 & 8646	
8069	CUTTER WHEEL (90710/721/727/734/747)	19	8634	POLY PULLING ATTACHMENT	53
8071	CUTTER WHEEL FOR 90735/90728/90750 METAL	23		PIPE SLICE KIT 8601 SLICE, 8610 GRIP, 8647 FLARE,	
8073	CUTTER WHEEL FOR 90750 PLASTIC	23	8635	8648 & 8649 LOCKNUT	53
8074	CUTTER WHEEL FOR 90737,90751 PLASTIC	23		PIPE SLICE KIT 8601 SLICE, 8611 GRIP, 8645 & 8646	
8075	CUTTER WHEEL FOR 90738, 90752 PLASTIC	23	8636	POLY PULLING ATTACHMENT	53
8076	CUTTER WHEEL FOR 95061/81/121,UNIVERSAL	7	0007	PIPE SLICE KIT 8601, 8610, 8645, 8646, 8647, 8648,	50
8082	CUTTER WHEEL FOR 2690 SS	7	8637	8649	53
8090	THREADING MACHINE 1/2"-2"	28	8638	PIPE SLICE KIT 8601, 8611, 8645, 8646, 8647, 8648,	E2
8096	THREADER 8090 W/2 DIE HEADS	28	0030	8649	53
8097	THREADER 8090 W/897065 DH	28	8645	3/4 PE PIPE PULLING ATTACHMENT FOR 8601	53
8098	THREADING MACHINE 1/2"-2" 220V	28	8646	1" PE PULLER ATTACHMENT FOR 8601	53
8100	HOT TAPPING SYSTEM 3/4"-1" NPT, STEEL/COPPER	50	8647	3/4"+ 1" DOUBLE FLARE TOOL FOR 8601	53
8102	HOT TAPPING SYSTEM 3/4"-2" NPT, STEEL/COPPER	50	8648	3/4" COPPER FLARE LOCKNUT FOR 8601	53
8200	HOT TAPPING SYSTEM 3/4"-1" CTS, STEEL/COPPER	50	8649	1" COPPER FLARE LOCKNUT FOR 8601	53
8201	HOT TAPPING SYSTEM 3/4"-1" CTS, PLASTIC	50	8670	SHUT OFF TOOL COMBO 86 & 70 1/2"-2"	49
8202	HOT TAPPING SYSTEM 3/4"-2" CTS, PLASTIC	50	8700	FORGED HYDRANT WRENCH	46
8203	HOT TAPPING SYSTEM 3/4"-1" CTS, DI & CI	50	8708	8" ALUMINUM VALVE WHEEL WRENCH	54
8204	HOT TAPPING SYSTEM 3/4"-2" CTS, DI & CI	50	8714	14" ALUMINUM VALVE WHEEL WRENCH	54
	HOT TAPPING SYSTEM 3/4"-1" CTS, PLASTIC, DI, CI			18" ALUMINUM VALVE WHEEL WRENCH	54
8205 8206	HOT TAPPING SYSTEM 3/4"-2" CTS, PLASTIC, DI, CI	50 50	8718 8806	6 FT ADJUST-A-KEY	55
8209	• • •		8808		55
	HOT TAPPING SYSTEM 3/4"-2" CTS, PLASTIC, DI, CI	50		8 FT ADJUST-A-KEY	
8300	HOT TAPPING SYSTEM 3/4"-1"BSPT, STEEL, COPPER	50	8900	SLIK-TAP DIRECT TAP LUBRICANT	51
8312	12" STRAP WRENCH, 1/2-2" PIPE	45	8901	SLIK-TAP, 12 PACK CASE	51
8318	18" STRAP WRENCH, 1-5" PIPE	45	8991	THREADING MACHINE 1/2"-1"	27
8324	24" STRAP WRENCH, 2-12" PIPE	45	8992	THREADER 8991 W/60131 DH	27
8400	ROLL GROOVER-6090,7090,8090	24	8993	THREADER 8991 W/2 DIE HEADS	27
8401	ROLL GROOVER-300	24	8998	THREADING MACHINE 1/2"-1" 220V	27
8402	ROLL GROOVER FOR 300 COMPACT	24	9000	POWER PLASTIC BEVELER	13
8403	ROLL GROOVER 6790	24	9001	MODEL 9000 WITH CARBIDE BIT	13
8412	OPMT CUT BEVEL STEEL 4"-12"	25	9015	PLASTIC PIPE BEVEL TOOL	13
8500	MINI PIPE SLICE-PIPELINEREPLACEMENT TOOL	53	9400	TELESCOPING BASIN WRENCH	45
8506	1/4 X 50' CABLE FOR MINI SLICE	53	9401	STANDARD BASIN WRENCH	45
8507	1/4 X 75' CABLE FOR MINI SLICE	53	9600	1-1/4 X 1-1/16 DOUBLE-UP WRENCH	46
8508	1/4 X 100' CABLE FOR MINI SLICE	53	9601	15/16 X 1 1/8 DOUBLE-UP WRENCH	46
8520	MINISLICE 50'-8506,8500,8611	53	9700	HYDRAULIC ROLL GROOVER W/BASE FOR 60/70/8090	24
8521	MINISLICE 75'-8507,8500,8611	53	9701	HYDRAULIC ROLL GROOVER W/BASE FOR 6790	24
	, ,				

Part No	Description	Page	Part No	Description	Page
9703	HYDRAULIC ROLL GROOVER W/BASE FOR 300	24	32964	4' DRIVE SHAFT FOR 1 1/2" - 2" MODELS	15
10050	1/2" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	33100	ELECTRIC TEST PUMP 1000PSI, 1GPM	39
10075	3/4" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	33101	ELECTRIC TEST PUMP (33100) 220V, 50HZ	39
10100	1" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	33110	ELECTRICT TEST PUMP 1000 PSI, 1 GPM (COMET PUMP)	39
10125	1-1/4" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	35100	ELECTRIC TEST PUMP 500PSI 3GPM	39
10150	1-1/2" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	35101	ELECTRIC TEST PUMP 220V 50HZ	39
10200	2" CTS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	36200	TEST PUMP,3.5GPM, 1200PSI, B&S ENGINE	37
10696	ADAPTER FOR 12R DROP HEAD DIES	54	36454	HYDROSTATIC TEST PUMP 400PSI, 10GPM	37
10700	HYDRANT NUT DRIVER	55	37210	ELECTRIC TEST PUMP 3000 PSI3.5 GPM,208/230V	39
10709	1" SQUARE FEMALE ADAPTER	54	3/210	3-PHASE	39
13020	2" HINGED PIPE VISE	43	39300	TEST PUMP 300PSI 4GPM 1/2HP	39
13040	2-1/2" HINGED PIPE VISE	43	39301	39300 TEST PUMP,220V,60HZ	39
13060	4" HINGED PIPE VISE	43	39906	HD RATCHET PIPE CUTTER 6"	4
13080	5" HINGED PIPE VISE	43	39908	HD RATCHET PIPE CUTTER 8"	4
13964	TORQUE LIMITING ADAPTER W/CTR/1" SQ DRIVE	54	42900	4" CAPITOL STYLE CI CUTTER	7
13968	RISING STEM TORQUE ADAPTER	55	46200	HYDROSTATIC TEST PUMP 1200PSI 3.5GPM B&S	37
13970	RISING STEM HAND WHEEL ADAPTER, 681155	55	46301	HYDROSTATIC TEST PUMP 300PSI 5.4GPM B&S	37
16010	1.5"-4" PIPE HOG KIT Sch 40	14	46453	HYDROSTATIC TEST PUMP 400PSI 10GPM	37
16150	1-1/2" PIPE HOG	14	46501	HYDROSTATIC TEST PUMP 500PSI, 10GPM UDOR/B&S/	38
16200	2" PIPE HOG	14	10001	CART	
16300	3" PIPE HOG	14	46503	HYDROSTATIC TEST PUMP 500PSI, 10GPM UDOR/B&S/	38
16400	4" PIPE HOG	14		ROLL CAGE	
16050	12" EXTENSION SHAFT	14	46521	HYDROSTATIC TEST PUMP 500PSI, 10GPM COMET/B&S/	38
16055	1/2" SQUARE CARBIDE INSERT	14		CART HYDROSTATIC TEST PUMP 500PSI 10GPM COMET/B&S/	
17500	REPLACEMENT POLAR GAS CANISTER	48	46523	ROLL CAGE	38
19010	CHAIN EXTENSION 8 PINS 2990	6	46600	HYDROSTATIC TEST PUMP 300PSI, 15GPM B&S	38
19012	CHAIN EXTENSION 14 PINS 2990	6	40000	HYDROSTATIC TEST PUMP 1000PSI, ELECTRIC 115V 60HZ	30
19015	CHAIN EXTENSION 20 PINS 2990	6	47100	2.2GPM	39
19020	FITTING SAVER KIT IPS SCH 40	14		HYDROSTATIC TEST PUMP 1000PSI, ELECTRIC 220V	
19025	FITTING SAVER KIT IPS SCH 80	14	47101	50HZ 2.2GPM	39
19030	1/2" CTS FITTING SAVER	14	47102	HYDROSTATIC TEST PUMP 2000PSI, ELECTRIC 115V 60HZ	39
19035	3/4" CTS FITTING SAVER	14	4/102	1.1GPM	39
19050	1/2" SCH 40 FITTING SAVER	14	47103	HYDROSTATIC TEST PUMP 2000PSI, ELECTRIC 220V	39
19051	1/2" SCH 80 FITTING SAVER	14	47100	50HZ 1.1GPM	00
19075	3/4" SCH 40 FITTING SAVER	14	47105	HYDROSTATIC TEST PUMP 2000PSI, ELECTRIC 115V 60HZ	39
19076	3/4" SCH 80 FITTING SAVER	14		2.2GPM	
19100	1" SCH 40 FITTING SAVER	14	49010	RATCHET PIPE CTR 1-1/2" to 10"	4
19101	1" SCH 80 FITTING SAVER	14	49012	RATCHET PIPE CTR 1-1/2" to 12"	4
21389	TORQUE LIMITING ADAPTER W/ 1" SQ DRIVE	54	49015	RATCHET PIPE CUTTER 2"-15"	4
29200	MANUAL TEST PUMP 300PSI	36	49075	REROUNDING TOOL 3/4"	22
29201	MANUAL TEST PUMP 1000PSI	36	49100	REROUNDING TOOL 1"	22
29900	MANUAL TEST PUMP W/TANK 870PSI	36	49150	REROUNDING TOOL 1-1/2"	22
29906	2-6" HYDRAULIC PIPE CUTTER	5	49200	REROUNDING TOOL 2"	22
29908	2-8" HYDRAULIC PIPE CUTTER	5	50100	INNER-OUTER REAMER 3/8"-2" 10MM-54MM	22
30050	1/2" IPS CHAMFER/BEVELTOOL/DEPTH GAUGE	15	52510	CHAIN EXTENSION 490/590 20 PINS 6"	6
30075	3/4" IPS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	52512		6
30100	1" IPS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	56200	2 INCH TRASH PUMP	41
30125	1-1/4" IPS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	56201	56200 WITH WHEELED CART	41
30150	1-1/2" IPS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	56300	3 INCH TRASH PUMP	41
30200	2" IPS CHAMFER/BEVEL TOOL/DEPTH GAUGE	15	56301	56300 WITH WHEELED CART	41
32150	PNEUMATIC TEST PUMP, 1GPM/1500PSI	40	56310	3" MUDSUCKER DIAPHRAGM PUMP	41
32300	PNEUMATIC TEST PUMP, .5GPM / 3000PSI	40	59010		4
32301	FLUID SECTION REPAIR KIT FOR 32300	40		MANUAL PIPE CUTTER 1-1/2"-12"	4
32450	PNEUMATIC TEST PUMP, 1GPM, 10,000PSI	40	59015	MANUAL PIPE CUTTER 2"-15"	4
32900	3" CAPITOL STYLE CI CUTTER	7	60506	WHEELED CART FOR 6390/6790	30

# PRODUCT LISTING

	WHEELED CART W/TOOL BOX, 6390/6790				Page
60513 (		30	90799	REPLACEMENT CUTTER WHEEL FOR SS TUBING CUTTERS	20
	COLLAPSIBLE CART FOR 8090	30	95121	HINGED PIPE CUTTER 8"-12"	7
60514 \	WHEELED CART FOR 6590	30	95240	HINGED PIPE CUTTER 2"-4"	7
60515 \	WHEEL CART W/TOOLBOX FOR 6590	30	95460	HINGED PIPE CUTTER 4"-6"	7
60518	ANTI-TIP BRACKET FOR COLLAPSIBLE CART	30	95680	HINGED PIPE CUTTER 6"-8"	7
60601	THREADMASTER OIL GALLON JUG	30	98001	ValveMaster Frwd Ctr Honda	54
60602	THREADMASTER OIL 5 GALLON PAIL	30	98003	ValveMaster 2 way Ctr Honda	54
60603	THREADMASTER OIL 2 QUART BOTTLE	30	192410	COMPLETE CHAIN 10" FOR 299010	6
60604	THREADMASTER OIL 1 QUART BOTTLE	30	192412	COMPLETE CHAIN 12" FOR 299012	6
60607	THREADMASTER SS OIL 1 GALLON	30	192415	COMPLETE CHAIN 15" FOR 299015	6
60608	THREADMASTER SS OIL 5 GALLON	30	220220	BEVELER UNIT LESS ROUTER	13
60655	THREADMASTER OIL 55 GALLON DRUM	30	220234	REPLACEMENT HSS 15 DEGREE ROUTER BIT ASSEMBLY	13
62000 I	NIPPLE ATTACHMENT NPT 1/2"	30	000044	REPLACEMENT CARBIDE 15 DEGREE ROUTER BIT AS-	10
62001 I	NIPPLE ATTACHMENT NPT 3/4"	30	220041	SEMBLY	13
62002	NIPPLE ATTACHMENT NPT 1"	30	220083	REPLACEMENT BLADE BEVEL FOR 9015	12
62003	NIPPLE ATTACHMENT NPT 1-1/4"	30	276288	FLAT FACE MALE QUICK DISCONNECT	8
62004	NIPPLE ATTACHMENT NPT 1-1/2"	30	276289	FLAT FACE FEMALE QUICK DISCONNECT	8
62005	NIPPLE ATTACHMENT NPT 2"	30	276693	WATER SUPPLY TANK, 4 GALLON	8
62006	NIPPLE ATTACHMENT NPT 2-1/2"	30	277227	SCREW FOR CARBIDE CUTTING INSERT	14
	NIPPLE ATTACHMENT NPT 3"	30	277228	CARBIDE CUTTING INSERT	14
	NIPPLE ATTACHMENT NPT 4"	30	299010	2-10" HYDRAULIC PIPE CUTTER	5
	POWER DRIVE 22rpm, 115v, 50/60HZ, 1/2HP	54	299012	2-12" HYDRAULIC PIPE CUTTER	5
	POWER DRIVE 66rpm, 115v, 50/60HZ, 1/2HP	54	299015	2-15" HYDRAULIC PIPE CUTTER	5
	GLASS TUBE CUTTER 1/4"-3/4"	10	362000	HYDROSTATIC TEST PUMP, 3.5GPM 1200PSI HONDA	37
	GLASS TUBE CUTTER 1/4"-1"	10	363020	FIRE HOSE TEST PUMP - 2 HOSE	40
	GLASS TUBE CUTTER 1/4"-1-1/2"	10	363040	FIRE HOSE TEST PUMP - 4 HOSE	40
	REPLACEMENT DEBURRING BLADE	19,22	363060	GAS FIRE HOSE TEST PUMP 10GPM, 400PSI	40
	3/4 CC PVC DRILL TAP	51	364540	HYDROSTATIC TEST PUMP WITH HONDA ENGINE	37
	1 CC PVC DRILL TAP	51	373080	HYDROSTATIC TEST PUMP HONDA, 3.5GPM/3000PSI	37
	2 FOOT KEY EXTENSION	55	382415	COMPLETE CHAIN 15" FOR 389015	6
	3/4" DRILL TAP	51	382418	COMPLETE CHAIN 18" FOR 389018	6
	1" DRILL TAP	51	382424	COMPLETE CHAIN 24" FOR 389024	6
	1-1/2" DRILL TAP	51	382515	CHAIN EXTENSION 8 PINS 3890	6
	2" DRILL TAP	51	382518	CHAIN EXTENSION 14 PINS 3890	6
	1/2" PEX RING CRIMPER	17	382520	CHAIN EXTENSION 20 PINS 3890	6
	3/4" PEX RING CRIMPER	17	382524	CHAIN EXTENSION 26 PINS 3890	6
	1" PEX RING CRIMPER	17	389012	4"-12" HYDRAULIC PIPE CUTTER	5
	1/2" & 3/4" PEX COMBO CRIMPER	17	389015	4"-15" HYDRAULIC PIPE CUTTER	5
	1/2"- 1" RING REMOVER	17	389018	4"-18" HYDRAULIC PIPE CUTTER	5
	CLAMP REMOVAL TOOL	18	389024	4"-24" HYDRAULIC PIPE CUTTER	5
	1/2" CLOSE QTRS CRIMP TOOL	18	401500	PIPE VISE W/LEGS 3/4"-15"	43
	3/4" CLOSE QTRS CRIMP TOOL	18	402000	PIPE VISE W/LEGS 3/4"-20"	43
	COMBO CLAMP STYLE CRIMPER	18	402800	PIPE VISE W/LEGS 3/4"-28"	43
	SS CLAMP PINCHER	17	462000	HYDROSTATIC TEST PUMP 1200PSI, 3.5GPM HONDA ENGINE	37
	TUBING CUTTER 1/8"-1-1/8", CU/AL	19	463010	HYDROSTATIC TEST PUMP 300PSI, 5.4GPM HONDA ENGINE	37
	MINI TUBING CUTTER 1/8"-1", CU/AL	19	464530	HYDROSTATIC TEST PUMP 400PSI, 10GPM HONDA ENGINE	37
	MINI TUBING CUTTER 1/8 -1 , CU/AL MINI TUBING CUTTER 1/8"-1-1/8", SS	20		HYDROSTATIC TEST PUMP 500PSI, 10GPM UDOR/HONDA/	
	MINI TUBING CUTTER 1/8 -1-1/8 , 55 MINI TUBING CUTTER 1/8"-1-1/8", CU/AL	19	465010	CART	38
	TUBING CUTTER 1/8"-1-1/8", CU/AL TUBING CUTTER 1/8"-1-3/4" SS	20		HYDROSTATIC TEST PUMP 500PSI, 10GPM UDOR/HONDA/	
			465030	ROLL CAGE	38
	TUBING CUTTER 1/8"-1-3/8", TELESCOPIC	19	ACE040	HYDROSTATIC TEST PUMP 500PSI, 10GPM COMET/HONDA/	20
	TUBING CUTTER 1/4"-3" QUICK RELEASE	19	465210	CART	38
	TUBING CUTTER 4" 6 F/9" QUICK RELEASE	20	465330	HYDROSTATIC TEST PUMP 500PSI, 10GPM COMET/HONDA/	20
	TUBING CUTTER 4"-6-5/8" QUICK RELEASE	20	465230	CAGE	38

Part No	Description	Page
466000	HYDROSTATIC TEST PUMP 300PSI, 15GPM HONDA ENGINE	38
468260	HYDROSTATIC TEST PUMP 300PSI, 32GPM HONDA ENGINE	38
475200	BAND SAW BLADE-ALLOY 8 TEETH	25
475201	BAND SAW BLADE- ALLOY 10 TEETH	25
475202	BAND SAW BLADE- ALLOY 14 TEETH	25
475203	BAND SAW BLADE- ALLOY 18 TEETH	25
475204	BAND SAW BLADE- ALLOY 24 TEETH	25
475210	BAND SAW BLADE - BI METAL 10 TEETH	25
475211	BAND SAW BLADE - BI METAL 14 TEETH	25
475212	BAND SAW BLADE - BI METAL 18 TEETH	25
475213	BAND SAW BLADE - BI METAL 24 TEETH	25
506032	SOCKET	16
552420	COMPLETE CHAIN 20" FOR 559020	6
552424	COMPLETE CHAIN 24" FOR 559024	6
552436	COMPLETE CHAIN 36" FOR 559036	6
552520	CHAIN EXTENSION 4 PINS 5590	6
552524	CHAIN EXTENSION 10 PINS 5590	6
552536	CHAIN EXTENSION 28 PINS 5590	6
559018	6"-18" HYDRAULIC PIPE CUTTER	5
559020	6"-20" HYDRAULIC PIPE CUTTER	5
559024	6"-24" HYDRAULIC PIPE CUTTER	5
559036	6"-36" HYDRAULIC PIPE CUTTER	5
562000	2" TRASH PUMP W/HONDA ENGINE	41
562001	SAME AS 562000 WITH WHEELED CART	41
563000	3" TRASH PUMP W/HONDA ENGINE	41
563001	SAME AS 563000 WITH WHEELED CART	41
563100	3" MUDSUCKER DIAPHRAGM PUMP/HONDA	41
681150	POWER DRIVE W/CLUTCH & COUNTER, 250FT LBS 22RPM 115V 6 AMPS	54
681155	HAND WHEEL VALVE EXERCISER W/COUNTER & TORQUE ADAPTER, 22RPM	54
683155	HAND WHEEL VALVE EXERCISER W/COUNTER & TORUQE ADAPTER, 66RPM	54
690012	COMPLETE CHAIN FOR 69012 GLASS CUTTER	10
700155	REPLACEMENT BLADE FOR ALL CHAMFERING TOOLS	15
700536	VACUUM TEST ASSEMBLY	41
700588	SCHEDULE 80 GUIDE FOR 16150	14
700589	SCHEDULE 80 GUIDE FOR 16200	14
700590	SCHEDULE 80 GUIDE FOR 16300	14
700591	SCHEDULE 80 GUIDE FOR 16400	14
700692	REPLACEMENT STRAIGHT BLADE PFTE COATED	16
700777	6' DRIVE SHAFT FOR 1 1/2" - 2" MODELS	15
700778	6' DRIVE SHAFT FOR 3", 4" AND 6" MODELS	15
700821	20' HYDRAULIC HOSE ASSESMBLY	8
700970	TWO DRIVE WHEELS FOR 6" PIPE	8
701061	ELECTRIC COUNTER ASSEMBLY	54
701358	STAINLESS STEEL V-BLAD FOR 1697	16
701149	REPLACEMENT V-SHAPED BLADE PFTE COATED	16
701440	1 1/2" & 2" ARBOR ASSEMBLY	50
701454	STAINLESS STEEL V-BLAD FOR 1894, 1897	16
701567	LOW-PROFILE POINTED BLADE FOR 1698	16
701185	BYPASS VALVE KIT	9
802050	3/4" CTS ADAPTER	50
802051	3/4" NPT ADAPTER	50
802052	1" CTS ADAPTER	50

Part No	Description	Page
802053	1" NPT ADAPTER	50
802054	1-1/4" CTS ADAPTER	50
802055	1-1/4" NPT ADAPTER	50
802056	1-1/2" CTS ADAPTER	50
802057	1-1/2" NPT ADAPTER	50
802058	2" CTS ADAPTER	50
802059	2" NPT ADAPTER	50
802060	1-1/2" ADAPTER FOR MUELLER 110	50
802061	2" ADAPTER FOR MUELLER 110	50
802071	3/4" BSPT ADAPTER	50
802072	1" BSPT ADAPTER	50
802073	1-1/4" BSPT ADAPTER	50
802074	1-1/2" BSPT ADAPTER	50
802075	2" BSPT ADAPTER	50
802084	1-3/8 PVC CUTTER SHELL	50
802085	1-7/8 PVC CUTTER	50
892100	REPLACEMENT CUTTING BLADE FOR 89210	17
897065	DIE HEAD UNIVERSAL MANUAL OPEN 1/8"-2" NPT/NPSM/ UNC/8090	28
903071	11/16HSS CUTTER SHELL (502723)	50
903072	1" HSS CUTTER SHELL 506542	50
903073	1-1/4" CUTTER SHELL 506547	50
903074	1-1/2" CUTTER SHELL WITH 908097 BUSHING	50
903075	2" HSS CUTTER SHELL WITH908097 BUSHING	50
904065	11/16 CUTTER FOR 3/4 DI TAP	50
904066	7/8 CUTTER FOR 1" DI TAP	50
904067	1-1/8 DI HS FOR 1-1/4 TAP	50
904068	1-3/8 CUTTER FOR 1-1/2 DI TAP	50
904069	1-7/8 CUTTER FOR 2" DI TAP	50
908098	CENTER DRILL W/ COUPON RETAINER	50



WHEELER-REX 3744 Jefferson Rd. Ashtabula, OH USA 44004

Toll Free: 1-800-321-7950 Fax: 440-992-2925

E-mail: wheeler@wheelerrex.com

wheelerrex.com

© Rex International USA Inc.

Printed in U.S.A.

