Low Pressure Switch Bypass, Low Ambient Startups, 18-240 VAC

• Knob adjustable from 10-1,000 seconds

• Ideal for "winterstart" kits

CONTROLS

MODE OF OPERATION

When power is applied to the input, regardless of the state of the pressure switch, the load is energized and timing begins. After the timing delay is complete, the pressure switch will control the load. The control is reset by removing power during or after the time delay.

SPECIFICATIONS

Input

- Voltage: 18-240 VAC
- Frequency: 50-60 Hz

Output

- Output Ratings:
 - Maximum: 1 amp
 - *Minimum:* 40 mÅ
 - Inrush: 10 amps

Time Delay

• 10-1,000 seconds

WIRING DIAGRAM

INSTALLATION

- 1. Disconnect power.
- 2. Connect terminals as shown in the wiring diagram below.
- 3. Select the desired time delay.
- 4. Reapply power, check operation.

TIMING DIAGRAM



