

EP flow-through multi-port horizontal tees

Submittal information

Date submitted:

Project Information	
Job name :	Location:
Engineer:	Date submitted:
Contractor:	Submitted by:
Manufacturer's representative :	Approved by :

Technical Data

 Material
 Engineered Polymer

 Loop Cv
 2.9 Cv

 End type 1
 ProPEX 3/4"

 End type 2
 ProPEX 3/4"


 End type 3
 ProPEX 3/4"

 End type 4
 ProPEX 1/2"

 Temp./pressure ratings
 73°F (23°C) at 160 psi (11 bar)

180°F (82°C) at 100 psi (11 par) 180°F (82°C) at 100 psi (6.9 bar) 200°F (93°C) at 80 psi (5.5 bar)

Product information and application use



Part name	Part no.	A [inch]	B [inch]	C [inch]	D [inch]	E [inch]	F [inch]	G [inch]	H [inch]	l [inch]	J [inch]
EP Flow-through Multi-port Horizontal Tee, 4 outlets, 3/4" x 3/4" x 3/4" ProPEX	Q2247577	8.66	0.955	6.75	0.955	0.688	1.25	0.467	0.719	1.87	1.18

Part name	Part no.	Cv Through	Weight per UOM [lbs/UOM]	Equivalent length branch [ft]	Equivalent length through [ft]
EP Flow-through Multi-port Horizontal Tee, 4 outlets, 3/4"	Q2247577	13.8	0.12	8.34	1.91

ation Related applications

Use any product designed to mount 1" copper pipe as a mounting bracket. For more information,

refer to the Uponor Piping Systems Installation Guide

PEX-a Plumbing Systems

Codes	Standards	Listings
UPC IBC IRC IPC NPC of Canada UMC NSPC IMC	ASTM E814/ULC S115 ASTM F877 ASTM F1960 CSA B137.5 ULC S102.2 ASTM E119/UL 263 NSF-61 ULC S101 NSF-14	IAPMO-ES HUD MR 1269 ICC-ES-PMG cNSFus- pw UL U.P.Code cQAlus P321

 Trademark Information
 Contact Information

 Uponor Inc.
 Uponor Ltd.

 5925 148th Street West
 6510 Kennedy Road

ProPEX® is a registered trademark of Uponor Inc. ProPEX™ is a trademark of Uponor Ltd.

Apple Valley, MN 55124

T 800.321.4739

F 952.891.2008

Uponor Ltd. 6510 Kennedy Road Mississauga, ON L5T 2X4 T 888.594.7726 F 800.636.9517