
Fieldpiece

Pipe Clamp Type K Thermocouple (3/8" to 1 3/8")

OPERATOR'S MANUAL



WARNING

Do not remove the clamp from a pipe by pulling on the cord. Doing so may damage the sensor. The entire TC24 may become hot when testing hot pipes or cylinders. Use caution handling.

Quick Start

- 1. Plug your TC24 into any type K thermocouple jack.
- 2. Perform a field calibration for best accuracy.
- 3. Clamp onto suction or liquid line.
- 4. Take the measurement when the reading stabilizes.

Field Calibration


Due to variances in the thermocouple wire and other parts of the system, a field calibration to a known temperature (ice water) should be conducted before use. Depending on the meter, field calibration typically gives ±1°F (±0.5°C) overall accuracy. Refer to your meter's operating manual for calibration instructions.

Description

Use your new TC24 Pipe Clamp Type KThermocouple to take temperatures of pipes or any other cylindrical surface between 3/8" and 1 3/8".

The clamping range covers most sizes seen in residential and light commercial cooling systems. Connect to any thermometer with a Type K thermocouple jack.

The sensor is specifically designed for pipe temperature readings. Readings are extremely accurate and fast. Easily measure temperatures of pipes that are fixed, at any angle, to walls or other surfaces.



Specifications

Pipe Size Compatibility: 3/8" to 13/8" OD (9.5mm to 34.9mm OD)

Sensor Type: Type K thermocouple (nickel chromium/nickel aluminum)

Plug Type: Type K male mini plug Cable Length: 6 feet (1.8 m) **Measurement Range:**

-50°F to 257°F (-46°C to 125°C) Plastic body and wire insulation are designed to withstand a maximum continuous temperature of

257°F (125°C).

Stabilization Time: 30 seconds typical **Accuracy:** $\pm 4.0^{\circ}$ F ($\pm 2.2^{\circ}$ C) thermocouple only ± 1.0 °F (± 0.6 °C) after field calibration* *Meets California's Title 24 Specifications Dimensions: 135mm(H) x 72mm(W) x 35mm(D)

Weight: Approx. 140g **Certifications**

CE CE

RoHS compliant

Limited Warranty

This product is warranted against defects in material or workmanship for one year from date of purchase from an authorized Fieldpiece dealer. Fieldpiece will replace or repair the defective unit, at its option, subject to verification of the defect.

This warranty does not apply to defects resulting from abuse, neglect, accident, unauthorized repair, alteration, or unreasonable use of the instrument.

Any implied warranties arising from the sale of a Fieldpiece product, including but not limited to implied warranties of merchantability and fitness for a particular purpose, are limited to the above. Fieldpiece shall not be liable for loss of use of the instrument or other incidental or consequential damages, expenses, or economic loss, or for any claim of such damage, expenses, or economic loss.

State laws vary. The above limitations or exclusions may not apply to you.

For Service

Email Fieldpiece warranty department at fpwarranty@fieldpiece.com for current fixed price repair service. Send check or money order made out to Fieldpiece Instruments for the amount quoted. If your meter is under warranty there will be no cost for the repair/replacement. Send your meter, freight prepaid, to Fieldpiece Instruments. Send proof of date and location of purchase for in-warranty service. The meter will be repaired or replaced, at the option of Fieldpiece, and returned via least cost transporta-

For international customers, warranty for products purchased outside of the U.S. should be handled through local distributors. Visit our website to find your local distributor.




© Fieldpiece Instruments, Inc 2016; v08

Fieldpiece

Pipe Clamp Type K Thermocouple (3/8" to 1 3/8")

OPERATOR'S MANUAL



WARNING

Do not remove the clamp from a pipe by pulling on the cord. Doing so may damage the sensor. The entire TC24 may become hot when testing hot pipes or cylinders. Use caution handling.

Quick Start

- 1. Plug your TC24 into any type K thermocouple jack.
- 2. Perform a field calibration for best accuracy.
- 3. Clamp onto suction or liquid line.
- 4. Take the measurement when the reading stabilizes.

Field Calibration


Due to variances in the thermocouple wire and other parts of the system, a field calibration to a known temperature (ice water) should be conducted before use. Depending on the meter, field calibration typically gives ±1°F (±0.5°C) overall accuracy. Refer to your meter's operating manual for calibration instructions.

Description

Use your new TC24 Pipe Clamp Type KThermocouple to take temperatures of pipes or any other cylindrical surface between 3/8" and 1 3/8".

The clamping range covers most sizes seen in residential and light commercial cooling systems. Connect to any thermometer with a Type K thermocouple jack.

The sensor is specifically designed for pipe temperature readings. Readings are extremely accurate and fast. Easily measure temperatures of pipes that are fixed, at any angle, to walls or other surfaces.



Specifications

Pipe Size Compatibility: 3/8" to 13/8" OD (9.5mm to 34.9mm OD) **Sensor Type:** Type K thermocouple

(nickel chromium/nickel aluminum) Plug Type: Type K male mini plug

Cable Length: 6 feet (1.8 m) **Measurement Range:**

> -50°F to 257°F (-46°C to 125°C) Plastic body and wire insulation are designed to withstand a maximum continuous temperature of 257°F (125°C).

Stabilization Time: 30 seconds typical **Accuracy:** $\pm 4.0^{\circ}$ F ($\pm 2.2^{\circ}$ C) thermocouple only ± 1.0 °F (± 0.6 °C) after field calibration* *Meets California's Title 24 Specifications Dimensions: 135mm(H) x 72mm(W) x 35mm(D) Weight: Approx. 140g

Certifications

(€ CE

RoHS compliant

Limited Warranty

This product is warranted against defects in material or workmanship for one year from date of purchase from an authorized Fieldpiece dealer. Fieldpiece will replace or repair the defective unit, at its option, subject to verification of the defect.

This warranty does not apply to defects resulting from abuse, neglect, accident, unauthorized repair, alteration, or unreasonable use of the instrument.

Any implied warranties arising from the sale of a Fieldpiece product, including but not limited to implied warranties of merchantability and fitness for a particular purpose, are limited to the above. Fieldpiece shall not be liable for loss of use of the instrument or other incidental or consequential damages, expenses, or economic loss, or for any claim of such damage, expenses, or economic loss.

State laws vary. The above limitations or exclusions may not apply to

For Service

Email Fieldpiece warranty department at fpwarranty@fieldpiece.com for current fixed price repair service. Send check or money order made out to Fieldpiece Instruments for the amount quoted. If your meter is under warranty there will be no cost for the repair/replacement. Send your meter, freight prepaid, to Fieldpiece Instruments. Send proof of date and location of purchase for in-warranty service. The meter will be repaired or replaced, at the option of Fieldpiece, and returned via least cost transporta-

For international customers, warranty for products purchased outside of the U.S. should be handled through local distributors. Visit our website to find your local distributor.



© Fieldpiece Instruments, Inc 2016; v08