


RIDGID SeeSnake 1/1/200 Camera Reel Series with TruSense



The new RIDGID® SeeSnake® rM200 Camera Reel Series now features TruSense® technology for superior image clarity and camera functionality. Already known for its built-in versatility and portability, the rM200 series, now also has enhanced transportation and storage features. The interchangeable D2 Series Drums (D2A) & D2B) provide various combinations of cable stiffness and spring flexibility to tackle any inspection job.

- Enhanced camera functionality TruSense technology with High Dynamic Range (HDR) sensor and TiltSense™ inclinometer give crisp, always upright images and feedback on camera angle in-pipe
- Interchangeability Easily interchangeable D2 drums for on-the-job flexibility and compatible with all SeeSnake monitors
- Pushability Drums feature different push cable lengths, diameters, stiffness and springs for customized jobs
- Portability Multi-functional pull handle and smooth wheels for easy transport and positioning
- Increased storage New taller stow bins with increased internal capacity to store



rM200B Reel Catalog No. 63663

Catalog No. 63658

rM200A Reel

SPECIFICATIONS

	rM200A	rM200B
• Length	. 21.0" (535 mm)	21.0" (535 mm)
• Width	. 13.6" (345 mm)	13.6" (345 mm)
Height	. 24" (610 mm)	24" (610 mm)
Drum Diameter	. 17" (432 mm)	17" (432 mm)
• Camera	411. (0.5	411 (O.F)
Diameter		1" (25 mm)
Туре	. Self-leveling w/TruSense	Self-leveling w/TruSense
Resolution	. 640 x 480	640 x 480
 Spring Assembly 		
Туре	. Single	Dual Nested
Length	. 12.4" (316 mm)	17.1" (435 mm)
• Line Capacity	. 1.5" — 8" (38 mm — 203 mm)	2" – 8" (51 mm – 203 mm)
Push Cable		
Length	. 200' (61 m)	165' (50 m)
Diameter	. 0.3" (7.5 mm)	0.35" (8.9 mm)
Minimum Bend Radius		3.5" (89 mm)
• Sonde	.512 Hz, FleXmitter®	512 Hz, FleXmitter®

ORDER INFORMATION

CATALOG NO.	MODEL NO.	DESCRIPTION	WEI (lb.)	GHT (kg)
63658	rM200A	Reel, SeeSnake rM200A w/D2A Drum, TruSense	37.0	16.7
63663	rM200B	Reel, SeeSnake rM200B w/D2B Drum, TruSense	40.2	18.2
70758	D2A	Drum, rM200 D2A, TruSense	16.3	7.4
70763	D2B	Drum, rM200 D2B, TruSense	19.2	8.7













Scan for more information on HQx Live





rM200 D2A Drum Catalog No. 70758



rM200 D2B Drum Catalog No. 70763