

# Zero-Flex® Rigid Coupling

## STYLE 07




The unique angle-pad design of the Zero-Flex® Style 07 coupling adjusts to standard pipe and roll or cut groove tolerances, positively clamping the pipe to resist flexural and torsional loads. The wider key section fills more of the groove area.

The Victaulic standard rigid coupling offering for grade “EHP” or “T” gaskets is the Style 107 installation-ready rigid coupling. For all available sizes, the Style 107 is the standard rigid coupling Victaulic supplies in North America for piping systems using Grade “EHP” or “T” gaskets. Contact Victaulic for further details.

Style 07 couplings are rated up to 750psi/5175kPa, dependant on size, for 1 – 12”/25 – 300mm piping systems. Rigid couplings provide rigidity for valve connections, machinery rooms, fire mains, and long straight runs. Support and hanging requirements correspond to ASME B31.1 Power Piping Code, ASME B31.9 Building Services Code and NFPA 13 Sprinkler Systems. Angle-pad design permits assembly by removing one nut/bolt and scissoring housing over gasket. This reduces the number of components to handle during assembly, speeds and eases installation.

For 14 – 24”/350 – 600mm sizes Victaulic offers the Advanced Groove System (AGS) line of products. Request publication 20.02 for information on the rigid W07 AGS coupling.



*Exaggerated for clarity*

### MATERIAL SPECIFICATIONS

**Housing:** Ductile iron conforming to ASTM A-536, grade 65-45-12. Ductile iron conforming to ASTM A-395, grade 65-45-15, is available upon special request.

**Housing Coating:** Orange enamel.

- **Optional:** Hot dipped galvanized and others.

**Coupling Gasket:** (specify choice‡)

- **Grade “E” EPDM**

EPDM (Green color code). Temperature range –30°F to +230°F/–34°C to +110°C. Recommended for cold and hot water service within the specified temperature range plus a variety of dilute acids, oil-free air and many chemical services. UL classified in accordance with ANSI/NSF 61 for cold +86°F/+30°C and hot +180°F/+82°C potable water service. NOT RECOMMENDED FOR PETROLEUM SERVICES.

- **Grade “T” nitrile**

Nitrile (Orange color code). Temperature range –20°F to +180°F/–29°C to +82°C. Recommended for petroleum products, air with oil vapors, vegetable and mineral oils within the specified temperature range. Not recommended for hot water services over +150°F/+66°C or for hot dry air over +140°F/+60°C.

‡ Services listed are General Service Recommendations only. It should be noted that there are services for which these gaskets are not recommended. Reference should always be made to the latest Victaulic Gasket Selection Guide for specific gasket service recommendations and for a listing of services which are not recommended.

NOTE: Additional gasket styles are available. Contact Victaulic for details.

**Bolts/Nuts:** Heat-treated plated carbon steel, trackhead meeting the physical and chemical requirements of ASTM A-449 and physical requirements of ASTM A-183.

### JOB/OWNER

System No. \_\_\_\_\_

Location \_\_\_\_\_

### CONTRACTOR

Submitted By \_\_\_\_\_

Date \_\_\_\_\_

### ENGINEER

Spec Sect \_\_\_\_\_ Para \_\_\_\_\_

Approved \_\_\_\_\_

Date \_\_\_\_\_

[www.victaulic.com](http://www.victaulic.com)

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

REV\_K




06.02\_1

## Zero-Flex® Rigid Coupling

## STYLE 07

## DIMENSIONS



TYPICAL 1 – 12"

Size		Max. Work Pressure *	Max. End Load *	Allow. Pipe End Sep. †	Bolt/Nut@ No – Size	Dimensions – Inches/mm			Approx. Wgt. Each
Nominal Size Inches mm	Actual Outside Diameter Inches mm	psi kPa	Lbs. N	Inches mm	Inches	X	Y	Z	Lbs. kg
1 25	1.315 33.7	750 5175	650 2890	0.05 1.2	2 – 3/8 x 2	2.36 60	4.22 107	1.84 47	1.6 0.7
1 1/4 32	1.660 42.4	750 5175	1,620 7210	0.05 1.2	2 – 3/8 x 2	2.69 68	4.62 117	1.84 47	1.6 0.7
1 1/2 40	1.900 48.3	750 5175	2,130 9480	0.05 1.2	2 – 3/8 x 2	2.94 75	5.81 148	1.84 47	1.6 0.7
2 50	2.375 60.3	750 5175	3,320 14775	0.07 1.7	2 – 1/2 x 2 1/2	3.35 85	5.78 147	1.84 47	2.3 1.0
2 1/2 65	2.875 73.0	750 5175	4,875 21695	0.07 1.7	2 – 1/2 x 2 3/4	3.88 98	6.38 162	1.84 47	2.6 1.2
76.1 mm	3.000 76.1	750 5175	5,300 23585	0.07 1.7	2 – 12 x 70.0	4.21 107	6.61 168	1.84 47	3.6 1.6
3 80	3.500 88.9	750 5175	7,215 32105	0.07 1.7	2 – 1/2 x 2 1/2	4.54 115	6.81 173	1.84 47	3.0 1.4
4 100	4.500 114.3	750 5175	11,925 53065	0.16 4.1	2 – 1/2 x 2 3/4	5.81 148	8.21 209	2.07 53	5.3 2.4
108.0mm	4.250 108.0	750 5175	10,635 47325	0.16 4.1	2 – 12 x 70.0	5.56 141	7.98 203	2.07 53	5.2 2.4
5 125	5.563 141.3	750 5175	18,225 81100	0.16 4.1	2 – 5/8 x 3 1/4	7.03 179	9.89 251	2.07 53	7.4 3.4
133.0mm	5.250 133.0	700 4825	15,145 67395	0.16 4.1	2 – 16 x 82.5	6.69 170	9.60 244	2.07 53	7.4 3.4
139.7 mm	5.500 139.7	700 4825	16,625 73980	0.16 4.1	2 – 16 x 82.5	6.94 176	9.82 249	2.07 53	7.6 3.4
6 150	6.625 168.3	700 4825	24,130 107380	0.16 4.1	2 – 5/8 x 3 1/4	8.26 210	10.83 275	2.07 53	8.3 3.8
159.0mm	6.250 159.0	700 4825	21,465 95520	0.16 4.1	2 – 16 x 82.5	7.84 199	10.54 268	2.07 53	9.2 4.2
165.1 mm	6.500 165.1	700 4825	23,225 103305	0.16 4.1	2 – 5/8 x 3 1/4	8.13 207	10.84 275	2.07 53	8.3 3.8
8 § 200	8.625 219.1	600 4130	35,000 155750	0.19 4.8	2 – 3/4 x 4 1/4	10.54 268	13.74 349	2.51 64	15.1 6.8
10 § 250	10.750 273.0	500 3450	45,400 202030	0.13 3.3	2 – 7/8 x 6 1/2	12.86 327	16.98 431	2.56 65	23.5 10.7
12 § 300	12.750 323.9	400 2750	51,000 226950	0.13 3.3	2 – 7/8 x 6 1/2	14.86 377	18.88 480	2.56 65	28.2 12.8
14 – 24 350 – 600	<b>AGS</b> For 14 – 24"/350 – 600 mm sizes Victaulic offers the Advanced Groove System (AGS) line of products. Request publication 20.02 for information on the rigid W07 AGS coupling.								

§ Couplings 8, 10, 12"/200, 250, 300 mm sizes available to JIS standard. Refer to section 06.17 for details.

\* Working Pressure and End Load are total, from all internal and external loads, based on standard weight (ANSI) steel pipe, standard **roll** or **cut** grooved in accordance with Victaulic specifications. Contact Victaulic for performance on other pipe.

WARNING: FOR ONE TIME FIELD TEST ONLY, the Maximum Joint Working Pressure may be increased to 1 1/2 times the figures shown.

† For field installation only on roll grooved pipe or cut grooved pipe. Zero-Flex Style 07 couplings are essentially rigid and do not permit expansion/contraction.

@ Number of bolts required equals number of housing segments.

Metric thread size bolts are available (color coded gold) for all coupling sizes upon request. Contact Victaulic for details.

Style 07 couplings must **not** be used to join PVC pipe.

---

## Zero-Flex® Rigid Coupling

STYLE 07

---

## Zero-Flex® Rigid Coupling

### STYLE 07

---

#### INSTALLATION

Reference should always be made to the I-100 Victaulic Field Installation Handbook for the product you are installing. Handbooks are included with each shipment of Victaulic products for complete installation and assembly data, and are available in PDF format on our website at [www.victaulic.com](http://www.victaulic.com).

---

#### WARRANTY

Refer to the Warranty section of the current Price List or contact Victaulic for details.

---

#### NOTE

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

---

For complete contact information, visit [www.victaulic.com](http://www.victaulic.com)

06.02 1482 REV K UPDATED 3/2009

VICTAULIC IS A REGISTERED TRADEMARK OF VICTAULIC COMPANY. © 2009 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

06.02

